

97 53 18

KNIPEX Twistor16 Self-Adjusting Crimping Pliers for End Sleeves

(ferrules)

With rotatable die head



- For crimping end sleeves (ferrules) according to DIN 46228 parts 1 + 4
- Square crimp profile, high capacity range of 0.14 to 16 mm²
- 360° rotatable crimping die; with 8 tactile locking positions
- Self-adjustment to the desired size of end sleeve (ferrule): no crimping errors due to using the wrong crimping die or to an incorrect setting
- Crimping of twin end sleeves (ferrules) up to 2 x 6 mm² possible
- Slim head for ideal accessibility
- Repetitive, high crimping quality due to integral lock (self-releasing mechanism)
- Favourable lever ratio due to toggle lever
- Crimping pressure has been set precisely (calibrated) in the factory, re-adjustable
- Handy shape and low weight provide high operation comfort
- Chrome vanadium electric steel in special quality, oil-hardened

| | |
|--|----------------------------|
| Article No. | 97 53 18 |
| EAN | 4003773082729 |
| Pliers | chrome plated |
| Handles | with multi-component grips |
| Applications | End Sleeves (ferrules) |
| Capacity in square millimetres mm² | 0,14 - 16,0 |
| Number of crimping positions | 1 |
| AWG | 26 - 5 |
| Length mm | 200 |
| Net weight g | 478 |



Crimp head can be rotated 360° for optimal accessibility, even in confined spaces



Twin end sleeves (ferrules) up to 2 x 6 mm² can be crimped without adjustment



Uniquely flexible: connectors can be inserted in the rotatable crimp head from almost any position



technical change and errors excepted