



**Part Number: 2200ENH**

**Enhanced Category 6A Nonbonded-Pair F/UTP LSZH Cable**

**Product Description**

Category 6A (500MHz), 4-Pair, F/UTP-Foil shielded, Premise Horizontal Cable, 23 AWG Solid Bare Copper Conductors, Polyethylene Insulation, Beldfoil® shield, AWG 26 solid tinned copper drainwire, LSZH Jacket, CPR Euroclass Eca

**Technical Specifications**

**Product Overview**

Environmental Space:	Indoor - Euroclass Eca
Suitable Applications:	Horizontal and building backbone cable; Support current and future Category 6A and 6 applications, such as: 10GBase-T (10 Gigabit Ethernet), 1000Base-T (Gigabit Ethernet), 100 Base-T, 10 Base-T, FDDI, ATM

**Physical Characteristics (Overall)**

**Conductor**

Element	AWG	Stranding	Material	No. of Pairs
Individual pair	23	Solid	BC - Bare Copper	4

Conductor Count:	8
Total Number of Pairs:	4
Conductor Size:	23 AWG

**Insulation**

Element	Type	Material	Nominal Diameter
Individual pair	Dielectric	Polyethylene	1.18 mm

**Color Chart**

Number	Color
Pair 1	White/Blue & Blue
Pair 2	White/Orange & Orange
Pair 3	White/Green & Green
Pair 4	White/Brown & Brown

**Outer Shield Material**

Type	Material	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Position
Tape	Aluminum/Polyester	100 %	Solid tinned copper	26	outside aluminum foil

**Outer Jacket Material**

Material	Nominal Diameter	Diameter +/- Tolerance	Ripcord
LSZH / FRNC	7.2 mm	0.3 mm	Yes

**Construction and Dimensions**

Min Elongation at Breakof Conductors:	10 %
Min Elongation at Breakof Insulation:	100 %

**Cabling**

Description	
4 pairs twisted together	
Min Elongation at Breakof Jacket:	100 %
Min Tensile Strength of Jacket:	9 MPa

## Electrical Characteristics

### Conductor DCR

Max. Conductor DCR	Max DCR Unbalanced Between Pairs [%]	Max. DCR Unbalanced Within Pair [%]
95 Ohm/km	4 %	2 Ohm

### Capacitance

Max. Capacitance Unbalance	Max. Mutual Capacitance
1,600 pF/m	56 pF/m

Shielding: F/UTP - Overall Foil

### Impedance

Nominal Characteristic Impedance
100 Ohm

### Delay

Max. Delay Skew	Min. Velocity of Propagation
45 ns/100m	67 %

### High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Min. PSANEXT	Min. PSAACRF	Min. TCL [dB]	Min. ELTCTL [dB]
1 MHz	2.1 dB/100m	75.3 dB	72.3 dB	73.2 dB	70.2 dB	68 dB	65 dB	20 dB	67 dB	67 dB	40 dB	35 dB
4 MHz	3.8 dB/100m	66.3 dB	63.3 dB	62.5 dB	59.5 dB	56 dB	53 dB	23 dB	67 dB	66.2 dB	34 dB	23 dB
10 MHz	5.9 dB/100m	60.3 dB	57.3 dB	54.4 dB	51.4 dB	48 dB	45 dB	25 dB	67 dB	58.2 dB	30 dB	15 dB
16 MHz	7.5 dB/100m	57.2 dB	54.2 dB	49.8 dB	46.8 dB	43.9 dB	40.9 dB	25 dB	67 dB	54.1 dB	28 dB	10.9 dB
31.2 MHz	10.5 dB/100m	52.9 dB	49.9 dB	42.4 dB	39.4 dB	38.1 dB	35.1 dB	23.6 dB	67 dB	48.3 dB	25.1 dB	5.1 dB
62.5 MHz	15 dB/100m	48.4 dB	45.4 dB	33.4 dB	30.4 dB	32.1 dB	29.1 dB	21.5 dB	65.6 dB	42.3 dB	22 dB	
100 MHz	19.1 dB/100m	45.3 dB	42.3 dB	26.2 dB	23.2 dB	28 dB	25 dB	20.1 dB	62.5 dB	38.2 dB	20 dB	
125 MHz	21.5 dB/100m	43.8 dB	40.8 dB	22.3 dB	19.3 dB	26.1 dB	23.1 dB	19.4 dB	61 dB	36.3 dB	19 dB	
200 MHz	27.6 dB/100m	40.8 dB	37.8 dB	13.2 dB	10.2 dB	22 dB	19 dB	18 dB	58 dB	32.2 dB	17 dB	
250 MHz	31.1 dB/100m	39.3 dB	36.3 dB	8.3 dB	5.3 dB	20 dB	17 dB	17.3 dB	56.5 dB	30.2 dB	16 dB	
300 MHz	34.3 dB/100m	38.1 dB	35.1 dB	3.9 dB	0.9 dB	18.5 dB	15.5 dB	17.3 dB	55.3 dB	28.7 dB		
500 MHz	45.3 dB/100m	34.8 dB	31.8 dB	-10.4 dB	-13.4 dB	14 dB	11 dB	17.3 dB	52 dB	24.2 dB		

High Freq Table Note: Limits below 4MHz are for information only.

Coupling Attenuation Class: Type II

### Transfer Impedance

Frequency [MHz]	Description	Transfer Impedance
1 Mhz	Grade 2	Max. 50 mOhm/m
10 Mhz		Max. 100 mOhm/m
30 Mhz		Max. 200 mOhm/m
100 Mhz		Max. 1000 mOhm/m

### Current

Max. Recommended Current [A]
1.5 A

### Voltage

Voltage Rating [V]
72 V

## Temperature Range

Installation Temp Range:	0°C To +50°C
Operating Temp Range:	-30°C To +60°C

## Mechanical Characteristics

Bulk Cable Weight:	50 kg/km
Max Recommended Pulling Tension:	80 N
Min Bend Radius During Installation:	58 mm
Min Bend Radius During Operation:	29 mm

## Standards

ISO/IEC Compliance:	ISO/IEC 11801 Ed. 2.2:2002/A2:2010/C1:2011
CPR Euroclass:	Eca
CENELEC Compliance:	EN 50173-1 Ed. 3:2011
Data Category:	Category 6A
ANSI Compliance:	ANSI/TIA/EIA 568-B.2-1 (2002)

## Applicable Environmental and Other Programs

EU RoHS Compliance Date (yyyy-mm-dd):	2018-01-03
---------------------------------------	------------

## Flammability, LSOH, Toxicity Testing

ISO/IEC Flammability:	IEC 60332-1
Burning Load:	745 kJ/m
Amount of Halogen acc. to IEC 60754-1 & EN50267-1:	Zero

## Part Number

Patent:	<a href="https://www.belden.com/resources/patents">https://www.belden.com/resources/patents</a>
---------	---

## History

Revision Number:	1
------------------	---

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.