

PHOTOCENTRIC 3D RESIN (PRO FIRM)

Page: 1

Compilation date: 22/02/2017

Revision No: 2

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: PHOTOCENTRIC 3D DAYLIGHT PRO FIRM RESIN

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: PC30: Photo-chemicals for 3D printing.

1.3. Details of the supplier of the safety data sheet

Company name: Photocentric Ltd

Cambridge house

Oxney Road

Peterborough

Cambridgeshire

PE1 5YW

England

Tel: +44 (0) 1733 349937

Email: info@photocentric.co.uk

1.4. Emergency telephone number

Emergency tel: +44 (0) 1733 349937

(office hours only)

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: Aquatic Chronic 3: H412; Eye Irrit. 2: H319; Skin Irrit. 2: H315; Skin Sens. 1A: H317; STOT

SE 3: H335

Most important adverse effects: Causes skin irritation. May cause an allergic skin reaction. Causes serious eye irritation.

May cause respiratory irritation. Harmful to aquatic life with long lasting effects.

2.2. Label elements

Label elements:

Hazard statements: H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation. H335: May cause respiratory irritation.

, , ,

H412: Harmful to aquatic life with long lasting effects.

Hazard pictograms: GHS07: Exclamation mark





PHOTOCENTRIC 3D RESIN (PRO FIRM)

Page: 2

Signal words: Warning

Precautionary statements: P280: Wear protective gloves/protective clothing/eye protection/face protection.

P302+352: IF ON SKIN: Wash with plenty of water/soap and water.

P304+340: IF INHALED: Remove person to fresh air and keep comfortable for breathing. P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove

contact lenses, if present and easy to do. Continue rinsing.
P312: Call a POISON CENTER/doctor if you feel unwell.
P321: Specific treatment (see instructions on this label).

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

BISPHENOL A ETHOXYLATE DIMETHACRYLATE

EINECS	CAS	PBT / WEL	CLP Classification	Percent
-	Proprietary	-	Skin Irrit. 2: H315; Skin Sens. 1A: H317; Eye Irrit. 2: H319; STOT SE 3: H335	50-70%
DIACRYLATE				
-	Proprietary	-	Eye Irrit. 2: H319; Skin Irrit. 2: H315; Skin Sens. 1: H317	10-30%
ACRYLATE				
-	Proprietary	-	Skin Irrit. 2: H315; Eye Irrit. 2: H319	1-10%
ACRYLATE				
-	Proprietary	-	Eye Irrit. 2: H319; Skin Irrit. 2: H315; Skin Sens. 1: H317	1-10%
ACRYLATE				
-	Proprietary	-	Acute Tox. 4: H302; Skin Sens. 1A: H317; Aquatic Chronic 1: H410	1-10%
PHOTOINITIAT	ΓOR			
-	Proprietary	-	Flam. Sol. 1: H228; Repr. 2: H361f; STOT RE 2: H373; Aquatic Chronic 2: H411	1-2.5%

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash immediately with plenty of soap and water.



PHOTOCENTRIC 3D RESIN (PRO FIRM)

Page: 3

Eye contact: Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Wash out mouth with water. Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a

doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may

cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Eye bathing equipment should be available on the premises.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used. Use water spray

to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact

with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. If outside do not approach from

downwind. If outside keep bystanders upwind and away from danger point. Mark out the

contaminated area with signs and prevent access to unauthorised personnel. Turn

leaking containers leak-side up to prevent the escape of liquid.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for

disposal by an appropriate method.



PHOTOCENTRIC 3D RESIN (PRO FIRM)

Page: 4

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area.

Do not handle in a confined space. Avoid the formation or spread of mists in the air.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Workplace exposure limits: No data available.

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area.

Respiratory protection: Self-contained breathing apparatus must be available in case of emergency.

Hand protection: Protective gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquid

Colour: Various colours

Odour: Characteristic odour

Evaporation rate: Negligible

Oxidising: No data available.

Solubility in water: No data available.

Also soluble in: Most organic solvents.

Viscosity: Viscous

Kinematic viscosity: 200-300cPs

Viscosity test method: Brookfield Spindle L2 @ 25 C

Boiling point/range°C: No data available. Melting point/range°C: No data available.

Flammability limits %: lower: No data available. upper: No data available.

Flash point°C: >93

[cont...]



PHOTOCENTRIC 3D RESIN (PRO FIRM)

Page: 5

Part.coeff. n-octanol/water: No data available.

Autoflammability°C: No data available. Relative density: No data available.

pH: No data available. VOC g/I: No data available.

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.

Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

DIACRYLATE

IPR	RAT	LD50	760	mg/kg
ORL	RAT	LD50	5	gm/kg

ACRYLATE

IPR	RAT	LD50	55	mg/kg
ORL	RAT	LD50	5190	μl/kg

Relevant hazards for product:

Hazard	Route	Basis
--------	-------	-------



PHOTOCENTRIC 3D RESIN (PRO FIRM)

Page: 6

Skin corrosion/irritation	DRM	Hazardous: calculated
Serious eye damage/irritation	OPT	Hazardous: calculated
Respiratory/skin sensitisation	-	Hazardous: calculated
STOT-single exposure	INH	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may

cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: Biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Readily absorbed into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Negligible ecotoxicity.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal

company.

NB: The user's attention is drawn to the possible existence of regional or national

regulations regarding disposal.

Section 14: Transport information

Transport class: This product does not require a classification for transport.

PHOTOCENTRIC 3D RESIN (PRO FIRM)

Page: 7

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture

by the supplier.

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No

2015/830.

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and s.3: H228: Flammable solid.

H302: Harmful if swallowed.

H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H335: May cause respiratory irritation.

H361f: Suspected of damaging fertility.

H373: May cause damage to organs <or state all organs affected, if known> through prolonged or repeated exposure <state route of exposure if it is conclusively proven that

no other routes of exposure cause the hazard>.

H410: Very toxic to aquatic life with long lasting effects.

H411: Toxic to aquatic life with long lasting effects.

H412: Harmful to aquatic life with long lasting effects.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive

and shall be used only as a guide. This company shall not be held liable for any

damage resulting from handling or from contact with the above product.