



6351 / 6352 Industrial Panel Meters

Metal Cased Sealed Meters

- Equivalent to Yokogawa 3.5" Tough Meters (Model: 271-3)



3-1/2"
6351 ■ D.C. Moving Coil
6352 ■ A.C. Repulsion

FEATURES

- The 6351 and 6352 Industrial Panel Meters are designed for extreme duty applications where a high degree of resistance to the environment is required.
- They are dustproof and waterproof, meeting NEMA 4 and ANSI C39.1 specifications and performance standards.
- These meters have $\pm 2\%$ accuracy, $\pm 1\%$ repeatability and a resistance of $\pm 20\%$.
- Response time is 1.5 seconds and a temperature range of -50°F to 150°F .
- Custom meter ranges and scales are available

SPECIFICATIONS

- Case and Composition: Thermo plastic window, brass case, ruggedized, gasket sealed.
- Movement: DC Moving Coil, AC Repulsion or Rectified, Pivot and Jewel Movements, Heavy Damping.

DIMENSIONS

MODELS	A	B	C	D	E	F	G	H
6351/6352	3.53	1.12	.38	2.50	-	.84	.97	.48

MODELS	I	J	K	L	M	N	O
6351/6352	+.25	1.58	.79	2.73	1.36	.800	3.65

