5PEEUV RJ45 Category 6 STP Plug



Shielded Plug for Category 6

Our FIFE PJ45 plugs are designed to simplify twisted pair terminations by allowing the wire pairs to be easily inserted through the plug and out of the front. This allows the installer to easily check the wiring order before crimping the connector. Twist is maintained more easily enabling a better performing crimp. Waste is minimised and the plugs are suitable for either stranded or solid wires.

Features

- Each plug allows twisted pair wires to be inserted through the body and pulled out of the front to ensure the correct wiring order before crimping
- By pulling the cores into the plug, twists can easily be maintained up to the contacts, enabling fully rated category performance
- Contact blades are suitable for stranded or solid wire cores from 24-26 AWG (0.51 0.40mm), with insulation up to 1.0mm O.D.
- Perfect solution for rapid termination
- Suitable for termination of solid or stranded STP cables with sheath O.D. of 5.0 6.0mm
- Faults and failures minimised



CE



- Simple one piece design
- Less cable scrap and wastage
- N.B. Must be used with suitable crimp tool (e.g., our code TRCSPDY or TRCSPDY3)

Specifications

• Material:

Housing: Polycarbonate UL94V-0 Shielding: Nickel plated brass

- Gold plating: 1.27μm/50μ"
- 3 prong contact for solid or stranded cores
- Housing colour: silver (shielded)
- Operating temperature: -10°C to 60°C

Packaging

Supplied in polybags of 10 then 100 then 500

10: PXSPDY6S#10100: PXSPDY6S#100500: PXSPDY6S#500


Note: Not permitted for sale in the USA








ROHS Compliant Code: PXSPDY6S







1. Housing material: Polycarbonate

Flammability rating: UL 94V-0, RoHS Compliant

2. Contacts type: Three prong pin fits solid/stranded wires

3. Gold plating: 50µ"/1.27µm

4. Packaging quantity: #500 = 500 pcs

#100 = 100 pcs

#10 = 10 pcs

5. Housing colour: Transparent

6. Operating temperature: -10°C to 60°C

7. Shielding material: Nickel plated brass

