SAFETY DATA SHEET PEST-STOP SUPER MOUSE KILLER PASTA

According to Regulation (EC) No 1907/2006, Annex II, as amended.Commission Regulation (EU) No 2015/830 of 28 May 2015.

SECTION 1: Identification of the substance/mixture and of the company/undertaking		
1.1. Product identifier		
Product name	PEST-STOP SUPER MOUSE KILLER PASTA	
1.2. Relevant identified uses o	f the substance or mixture and uses advised against	
Identified uses	Ready for use Rodenticide bait containing 25ppm Difenacoum.	
Uses advised against	No specific uses advised against are identified.	
1.3. Details of the supplier of the	he safety data sheet	
Supplier	Pest-Stop Systems Ltd Sterling House Grimbald Crag Close Knaresborough North Yorkshire HG5 8PJ Tel: 0800 652 5521 Fax: 01423 863 497 info@peststopsystems.com	
1.4. Emergency telephone nur	nber	
Emergency telephone	+44 (0) 1423 796630	
SECTION 2: Hazards identification	ation	
2.1. Classification of the subst	ance or mixture	
Classification (EC 1272/2008)		
Physical hazards	Not Classified	
Health hazards	STOT RE 2 - H373	
Environmental hazards	Not Classified	
2.2. Label elements		
Pictogram		
Signal word	Warning	

Hazard statements

H373 May cause damage to organs (Blood) through prolonged or repeated exposure.

Supplemental label information	 EUH401 To avoid risks to human health and the environment, comply with the instructions for use. P102 Keep out of reach of children. P103 Read label before use. P220 Keep / Store away from foodstuffs, beverages and animal feeding stuffs. P262 Do not get on skin. P270 Do not eat, drink or smoke when using this product. P273 Avoid release to the environment. P280 Wear protective gloves [Professional users]. P301 + P310 IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician. P404 Store in a closed container.
	P404 Store in a closed container. P405 Store locked up. P501 Dispose of contents/container in accordance with local regulations.
	Pour Dispose of contents/container in accordance with local regulations.

2.3. Other hazards

This product does not contain any substances classified as PBT or vPvB.

SECTION 3: Composition/information on ingredients

3.2. Mixtures		
2,2'-Iminodiethanol		<0.1%
CAS number: 111-42-2	EC number: 203-868-0	
Classification		
Acute Tox. 4 - H302		
Skin Irrit. 2 - H315		
Eye Dam. 1 - H318		
STOT RE 2 - H373		
DIFENACOUM (EU)		0.0025%
CAS number: 56073-07-5	EC number: 259-978-4	
M factor (Acute) = 10	M factor (Chronic) = 10	
Classification		
Acute Tox. 1 - H300		
Acute Tox. 1 - H310		
Acute Tox. 1 - H330		
Repr. 1B - H360D		
STOT RE 1 - H372		
Aquatic Acute 1 - H400		
Aquatic Chronic 1 - H410		
Denatonium Benzoate		0.001%
CAS number: 3734-33-6	EC number: 223-095-2	
Classification		
Acute Tox. 4 - H302		
Acute Tox. 4 - H332		
Skin Irrit. 2 - H315		
Eye Irrit. 2 - H319		
Aquatic Chronic 3 - H412		

The full text for all hazard statements is displayed in Section 16.

SECTION 4: First aid measures

4.1. Description of first aid mea	asures	
General information	In case of accident or if you feel unwell, seek medical advice immediately (show the label where possible). Advice for Medical Doctors: Difenacoum is an indirect anti-coagulant. Phytomenadione, Vitamin K, is antidotal. Determin prothrombin time not less than 18 hours after consumption. If elevated, administer Vitamin K1 until prothrombin time normalises. Continue determination of prothrombin time for two weeks after withdrawal of antidote and resume treatment if elevation occurs in that time.	
Inhalation	Due to the physical nature of this product, exposure by this route is unlikely. IF INHALED: Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Get medical attention if symptoms are severe or persist.	
Ingestion	Rinse mouth thoroughly with water. Do not induce vomiting. Get medical attention immediately.	
Skin contact	May cause irritation to susceptible persons. Immediately take off all contaminated clothing. Wash skin thoroughly with soap and water. Get medical attention if symptoms are severe or persist after washing.	
Eye contact	May cause eye irritation to susceptible persons. Rinse immediately with plenty of water and seek medical advice.	
Protection of first aiders	First aid personnel should wear appropriate protective equipment during any rescue.	
4.2. Most important symptoms and effects, both acute and delayed		
General information	The severity of the symptoms described will vary dependent on the concentration and the length of exposure.	
Inhalation	Unlikely to present an inhalation hazard. If symptoms develop move the exposed person to fresh air. Immediately obtain medical advice.	
Ingestion	Rinse mouth. Do NOT induce vomiting. Call a doctor immediately.	
Skin contact	May cause irritation.	
Eye contact	May be slightly irritating to eyes.	
4.3. Indication of any immediat	e medical attention and special treatment needed	
Notes for the doctor	Treat symptomatically.	
SECTION 5: Firefighting meas	ures	
5.1. Extinguishing media		
Suitable extinguishing media	The product is not flammable. Extinguish with alcohol-resistant foam, carbon dioxide, dry powder or water fog. Use fire-extinguishing media suitable for the surrounding fire.	
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.	
5.2. Special hazards arising fro	om the substance or mixture	
Specific hazards	None known.	
Hazardous combustion products	Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.	
5.3. Advice for firefighters		

Protective actions during firefighting	Avoid breathing fire gases or vapours. Evacuate area. Cool containers exposed to heat with water spray and remove them from the fire area if it can be done without risk. Cool containers exposed to flames with water until well after the fire is out.	
Special protective equipment for firefighters	Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing. Firefighter's clothing conforming to European standard EN469 (including helmets, protective boots and gloves) will provide a basic level of protection for chemical incidents.	
SECTION 6: Accidental release	e measures	
6.1. Personal precautions, prot	ective equipment and emergency procedures	
Personal precautions	Wear protective clothing as described in Section 8 of this safety data sheet.	
6.2. Environmental precautions		
Environmental precautions	Avoid discharge into drains or watercourses or onto the ground.	
6.3. Methods and material for c	containment and cleaning up	
Methods for cleaning up	Wear protective clothing as described in Section 8 of this safety data sheet. Clear up spills immediately and dispose of waste safely. Collect spillage with a shovel and broom, or similar and reuse, if possible. Collect and place in suitable waste disposal containers and seal securely. Flush contaminated area with plenty of water. Wash thoroughly after dealing with a spillage. For waste disposal, see Section 13.	
6.4. Reference to other section	<u>s</u>	
Reference to other sections	For personal protection, see Section 8. See Section 11 for additional information on health hazards. See Section 12 for additional information on ecological hazards. For waste disposal, see Section 13.	
SECTION 7: Handling and stor	age	
7.1. Precautions for safe handl	ing	
Usage precautions	As the product is a paste it is unlikely to produce dust. Read and follow manufacturer's recommendations. Wear protective clothing as described in Section 8 of this safety data sheet. Keep away from food, drink and animal feeding stuffs. Keep container tightly sealed when not in use.	
Advice on general occupational hygiene	Wash promptly if skin becomes contaminated. Take off contaminated clothing. Wash contaminated clothing before reuse. Wash after use and before eating, smoking and using the toilet.	
7.2. Conditions for safe storage	e, including any incompatibilities	
Storage precautions	Keep out of the reach of children. Keep away from food, drink and animal feeding stuffs. Keep only in the original container. Keep container tightly closed, in a cool, well ventilated place. Protect containers from damage. Keep away from oxidising materials, heat and flames.	
Storage class	Unspecified storage.	
7.3. Specific end use(s)		
Specific end use(s)	The identified uses for this product are detailed in Section 1.2.	
Usage description	Ready to use Rodenticide bait containing 25ppm Difenacoum.	
SECTION 8: Exposure Controls/personal protection		

8.1. Control parameters

Occupational exposure limits

Propane-1,2-diol (Propane-1,2-diol Particulates) WEL 8-Hr limit mg/M3: 10 Propane-1,2-diol (Propane-1,2-diol total vapour and particulates) WEL 8-Hr limit ppm: 150 WEL 8Hr limit mg/M3: 474

Flour WEL 8-Hr limit mg/M3: 10 WEL 15 min limit mg/M3: 30

8.2. Exposure controls	
Appropriate engineering controls	Provide adequate ventilation.
Personal protection	Keep away from food stuffs.
Eye/face protection	Avoid contact with eyes.
Hand protection	Suitable chemical resistant gloves are recommended for professional users.
Other skin and body protection	Personal protective equipment for the body should be selected based on the task being performed and the risks involved.
Hygiene measures	Wash hands thoroughly after handling. Do not eat, drink or smoke when using this product. Wash contaminated clothing before reuse.
Respiratory protection	Provide adequate ventilation.
Environmental exposure controls	Keep container tightly sealed when not in use. Avoid release to the environment.

SECTION 9: Physical and Chemical Properties

9.1. Information on basic physical and chemical properties

9.1. Information on basic phys	ical and chemical properties
Appearance	Paste.
Colour	Red.
Odour	Characteristic.
Odour threshold	No information available.
рН	No information available.
Melting point	Not relevant.
Initial boiling point and range	No information available.
Flash point	No information available.
Evaporation rate	No information available.
Evaporation factor	No information available.
Flammability (solid, gas)	combustible
Upper/lower flammability or explosive limits	No information available.
Other flammability	No information available.
Vapour pressure	Not relevant.
Vapour density	Not relevant.
Relative density	No information available.
Bulk density	No information available.
Solubility(ies)	No information available.

PEST-STOP SUPER MOUSE KILLER PASTA

Partition coefficient	Not relevant.
Auto-ignition temperature	No information available.
Decomposition Temperature	No information available.
Viscosity	No information available.
Explosive properties	Not considered to be explosive.
Explosive under the influence of a flame	Not considered to be explosive.
Oxidising properties	Not oxidising.
9.2. Other information	
SECTION 10: Stability and rea	activity
10.1. Reactivity	
Reactivity	There are no known reactivity hazards associated with this product.
10.2. Chemical stability	
Stability	Stable at normal ambient temperatures and when used as recommended. Stable under the prescribed storage conditions.
10.3. Possibility of hazardous	reactions
Possibility of hazardous reactions	No potentially hazardous reactions known.
10.4. Conditions to avoid	
Conditions to avoid	There are no known conditions that are likely to result in a hazardous situation.
10.5. Incompatible materials	
Materials to avoid	Keep away from oxidising materials, heat and flames.
10.6. Hazardous decompositio	on products
Hazardous decomposition products	Does not decompose when used and stored as recommended. Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.
SECTION 11: Toxicological int	formation
11.1. Information on toxicologi	cal effects
Acute toxicity - oral Notes (oral LD ₅₀)	>2000 mg/kg
Acute toxicity - dermal Notes (dermal LD₅₀)	>2000 mg/kg
Acute toxicity - inhalation Notes (inhalation LC ₅₀)	>5 mg/l (Dust)
Skin corrosion/irritation Animal data	Based on available data the classification criteria are not met.
Serious eye damage/irritation Serious eye damage/irritation	Based on available data the classification criteria are not met.
Respiratory sensitisation Respiratory sensitisation	Based on available data the classification criteria are not met.

Skin sensitisation		
Skin sensitisation	Based on available data the classification criteria are not met.	
Germ cell mutagenicity		
Genotoxicity - in vitro	Based on available data the classification criteria are not met.	
Carcinogenicity		
Carcinogenicity	Based on available data the classification criteria are not met.	
IARC carcinogenicity	None of the ingredients are listed or exempt.	
Reproductive toxicity		
Reproductive toxicity - fertility	Based on available data the classification criteria are not met.	
Reproductive toxicity - development	Contains an ingredient listed as: Reprotoxic	
Specific target organ toxicity -	single exposure	
STOT - single exposure	Not classified as a specific target organ toxicant after a single exposure.	
Specific target organ toxicity -	repeated exposure	
STOT - repeated exposure	STOT RE 2 - H373 May cause damage to organs through prolonged or repeated exposure.	
Aspiration hazard Aspiration hazard	Not relevant. Solid.	
General information	The severity of the symptoms described will vary dependent on the concentration and the length of exposure.	
Inhalation	No specific symptoms known.	
Ingestion	See section 4 - First Aid	
Skin contact	Prolonged contact may cause dryness of the skin.	
Eye contact	No specific symptoms known.	
Route of entry	Ingestion Inhalation Skin and/or eye contact	
Toxicity of ingredients	Denatonium Benzoate Oral (Rat) LD50 = 584 mg/kg Difenacoum Acute Oral ≤5mg/kg Acute Dermal ≤50mg/kg Acute Inhalation ≤0.05mg/kg (Commission Regulation 2016/1179)	
SECTION 12: Ecological Inform	nation	
Ecotoxicity	Not regarded as dangerous for the environment. However, large or frequent spills may have hazardous effects on the environment.	
12.1. Toxicity		
Toxicity	Based on available data the classification criteria are not met.	
12.2. Persistence and degradability		
Persistence and degradability	The degradability of the product is not known.	
12.3. Bioaccumulative potentia		
Bioaccumulative potential	No data available on bioaccumulation.	
Partition coefficient	Not relevant.	
12.4. Mobility in soil		

Mobility	No data available.	
12.5. Results of PBT and vPv	3 assessment	
12.6. Other adverse effects		
Other adverse effects	Toxic to mammals, including domesticated animals and birds if ingested. Exposure of non- target animals should be prevented.	
Toxicity of ingredients	Difenacoum Daphnia EC50/48Hr = 0.91 mg/l Rainbow trout LC50/96Hr = 0.33 mg/l	
SECTION 13: Disposal consid	lerations	
13.1. Waste treatment method	ls	
General information	This material and its container must be disposed of in a safe way.	
Disposal methods	Dispose of in accordance with applicable regional, national, and local laws and regulations. Dispose of Contaminated packaging as unused product unless fully cleaned.	
Waste class	Waste disposal key number from EWC is 20 01 19 (Pesticides)	
SECTION 14: Transport inform	nation	
General	The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, ADR/RID).	
14.1. UN number		
Not applicable.		
14.2. UN proper shipping nam	e	
Not applicable.		
14.3. Transport hazard class(e	es)	
No transport warning sign requ	uired.	
14.4. Packing group		
Not applicable.		
14.5. Environmental hazards		
Environmentally hazardous su No.	ibstance/marine pollutant	
14.6. Special precautions for u	iser	
Not applicable.		
14.7. Transport in bulk accord	ing to Annex II of MARPOL and the IBC Code	
Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code	Not applicable.	
SECTION 15: Regulatory info	mation	
15.1. Safety, health and enviro	onmental regulations/legislation specific for the substance or mixture	
National regulations	Health and Safety at Work etc. Act 1974 (as amended). The Carriage of Dangerous Goods and Use of Transportable Pressure Equipment Regulations 2009 (SI 2009 No. 1348) (as amended) ["CDG 2009"].	

Regulations 2009 (SI 2009 No. 1348) (as amended) ["CDG 2009"].

EH40/2005 Workplace exposure limits.

EU legislation

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (as amended). Commission Regulation (EU) No 2015/830 of 28 May 2015. Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures (as amended).

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

Inventories

EU - EINECS/ELINCS

SECTION 16: Other information

None of the ingredients are listed or exempt.

Abbreviations and acronyms used in the safety data sheet	 ADR: European Agreement concerning the International Carriage of Dangerous Goods by Road. ADN: European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways. RID: European Agreement concerning the International Carriage of Dangerous Goods by Rail. IATA: International Air Transport Association. ICAO-TI: Technical Instructions for the Safe Transport of Dangerous Goods by Air. IMDG: International Maritime Dangerous Goods. CAS: Chemical Abstracts Service. ATE: Acute Toxicity Estimate. LC₅₀: Lethal Concentration to 50 % of a test population. LD₅₀: Lethal Dose to 50% of a test population (Median Lethal Dose). EC₅₀: 50% of maximal Effective Concentration. PBT: Persistent, Bioaccumulative and Toxic substance. vPvB: Very Persistent and Very Bioaccumulative.
Classification abbreviations and acronyms	STOT RE = Specific target organ toxicity-repeated exposure
Classification procedures according to Regulation (EC) 1272/2008	STOT RE 2 - H373: Commission Regulation (EU) 2016/1179
Revision date	11/07/2017
Revision	1
Supersedes date	14/12/2016
SDS number	21143

Hazard statements in full	 H300 Fatal if swallowed. H302 Harmful if swallowed. H310 Fatal in contact with skin. H315 Causes skin irritation. H318 Causes serious eye damage. H319 Causes serious eye irritation. H330 Fatal if inhaled. H332 Harmful if inhaled. H360D May damage the unborn child. H372 Causes damage to organs (Blood) through prolonged or repeated exposure. H373 May cause damage to organs (Blood) through prolonged or repeated exposure. H373 May cause damage to organs (Blood) through prolonged or repeated exposure. H410 Very toxic to aquatic life.
	H400 Very toxic to aquatic life. H410 Very toxic to aquatic life with long lasting effects. H412 Harmful to aquatic life with long lasting effects.

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.