

# 454 T-handle hexdriver, Hex-Plus, 2.5 x 200 mm

Series 400 T-Handle



|                        |               |                               |              |
|------------------------|---------------|-------------------------------|--------------|
| <b>EAN:</b>            | 4013288096463 | <b>Size:</b>                  | 227x61x14 mm |
| <b>Part number:</b>    | 05013303001   | <b>Weight:</b>                | 21 g         |
| <b>Article number:</b> | 454           | <b>Country of origin:</b>     | CZ           |
|                        |               | <b>Customs tariff number:</b> | 82054000     |

- T-handle hexagonal screwdriver for socket head screws
- Single-component, ergonomic T-shaped handle
- T-shaped design - ideal for the transfer of particularly high tightening or loosening forces
- Very robust and wear-resistant thanks to special alloy blade steel
- Bevelled, chrome-plated

T-handle hexagonal screwdriver for socket head screws. Hex-Plus offers a greater contact surface in the head of the screw. The notching effect is therefore reduced to a minimum and damage to the screw head more or less eliminated. The ideal handle shape makes the transfer of higher tightening and loosening torque possible. The ergonomic design of the handle fills the palm of the hand and the fingers rest in the soft, rounded recesses. The whole hand is in contact with the handle so there is no frictional loss between the hand and the handle.

## Web link

[http://products.wera.de/en/screwdrivers\\_series\\_400\\_t-handle\\_454.html](http://products.wera.de/en/screwdrivers_series_400_t-handle_454.html)

Wera - 454  
05013303001 - 4013288096463

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

### Ergonomic design




The T-handle is useful whenever higher tightening or loosening torque need to be applied. The exclusive use of hard material in combination with the large contact surface area in the hand ensures an efficient, positive transfer of power.




The ergonomic design of the T-handle fills the palm of the hand. The fingers rest in the soft, rounded recess, and the whole hand is in contact with the handle – so there is no friction loss between the hand and handle.

### High torque transfer



By using the blade as an extension of your lower arm you can transfer particularly high torque.

### Superior wear resistance



The blades guarantee superior wear resistance and robustness.

### Hex-Plus



Hexagon screws can endure a problem because the contact surfaces delivering the power from the conventional tool, is transferred to the screw via very small surface areas. The consequence: the screw can become damaged (rounding out). Hex-Plus tools have a greater contact surface that prevents this from happening! At the same time, as much as 20 % more torque can be applied. Good to know: Hex-Plus tools fit into every standard hexagon socket screw!

### Web link






[http://products.wera.de/en/screwdrivers\\_series\\_400\\_t-handle\\_454.html](http://products.wera.de/en/screwdrivers_series_400_t-handle_454.html)

Wera - 454  
05013303001 - 4013288096463

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

## Series 400 T-Handle

Further versions in this product family:

|                    |  |  |  |  |  |
|--------------------|---|---|---|---|---|
|                    |   | mm  | mm  | mm  | inch  |
| 05013300001        | 2   | 100   | 27  | 61  | 4   |
| 05013301001        | 2   | 200   | 27  | 61  | 8   |
| 05013302001        | 2.5   | 100   | 27  | 61  | 4   |
| <b>05013303001</b> | <b>2.5</b>  | <b>200</b>  | <b>27</b>   | <b>61</b>   | <b>8</b>  |
| 05013304001        | 3   | 100   | 33  | 70  | 4   |
| 05013305001        | 3   | 150   | 33  | 70  | 6   |
| 05013330001        | 3   | 200   | 33  | 70  | 8   |
| 05013331001        | 3   | 350   | 33  | 70  | 14  |
| 05013332001        | 4   | 100   | 33  | 70  | 4   |
| 05013306001        | 4   | 150   | 33  | 70  | 6   |
| 05013307001        | 4   | 200   | 33  | 70  | 8   |
| 05013333001        | 4   | 350   | 33  | 70  | 14  |
| 05013334001        | 5   | 100   | 44  | 87  | 4   |
| 05013308001        | 5   | 150   | 44  | 87  | 6   |
| 05013309001        | 5   | 200   | 44  | 87  | 8   |
| 05013335001        | 5   | 350   | 44  | 87  | 18  |
| 05013337001        | 6   | 100   | 44  | 87  | 4   |
| 05013338001        | 6   | 150   | 44  | 87  | 6   |
| 05013310001        | 6   | 200   | 44  | 87  | 8   |
| 05013339001        | 6   | 350   | 44  | 87  | 14  |
| 05013311001        | 7   | 200   | 44  | 87  | 8   |
| 05013341001        | 8   | 150   | 44  | 87  | 6   |
| 05013312001        | 8   | 200   | 44  | 87  | 8   |
| 05013314001        | 10  | 200   | 44  | 87  | 8   |

## Web link

[http://products.wera.de/en/screwdrivers\\_series\\_400\\_t-handle\\_454.html](http://products.wera.de/en/screwdrivers_series_400_t-handle_454.html)

Wera - 454

05013303001 - 4013288096463

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)