



MPN - **GJM03-KIT-TTOL-J**

Description - **0603M HIGH Q**

Murata P/N	Size (mm/inch)	TC Code	Rated Voltage	Capacitance	Tolerance	Thickness (mm)	Qty
GJM0334C1HR20WB01	0603M/0201	CK	50Vdc	0.2pF	±0.05pF	0.33max	20
GJM0334C1HR30WB01	0603M/0201	CK	50Vdc	0.3pF	±0.05pF	0.33max	20
GJM0334C1HR40WB01	0603M/0201	CK	50Vdc	0.4pF	±0.05pF	0.33max	20
GJM0334C1HR50WB01	0603M/0201	CK	50Vdc	0.5pF	±0.05pF	0.33max	20
GJM0334C1HR60WB01	0603M/0201	CK	50Vdc	0.6pF	±0.05pF	0.33max	20
GJM0334C1HR70WB01	0603M/0201	CK	50Vdc	0.7pF	±0.05pF	0.33max	20
GJM0334C1HR80WB01	0603M/0201	CK	50Vdc	0.8pF	±0.05pF	0.33max	20
GJM0334C1HR90WB01	0603M/0201	CK	50Vdc	0.9pF	±0.05pF	0.33max	20
GJM0334C1E1R0BB01	0603M/0201	CK	25Vdc	1.0pF	±0.1pF	0.33max	20
GJM0334C1E1R1BB01	0603M/0201	CK	25Vdc	1.1pF	±0.1pF	0.33max	20
GJM0334C1E1R2BB01	0603M/0201	CK	25Vdc	1.2pF	±0.1pF	0.33max	20
GJM0334C1E1R3BB01	0603M/0201	CK	25Vdc	1.3pF	±0.1pF	0.33max	20
GJM0334C1E1R4BB01	0603M/0201	CK	25Vdc	1.4pF	±0.1pF	0.33max	20
GJM0334C1E1R5BB01	0603M/0201	CK	25Vdc	1.5pF	±0.1pF	0.33max	20
GJM0334C1E1R6BB01	0603M/0201	CK	25Vdc	1.6pF	±0.1pF	0.33max	20
GJM0334C1E1R7BB01	0603M/0201	CK	25Vdc	1.7pF	±0.1pF	0.33max	20
GJM0334C1E1R8BB01	0603M/0201	CK	25Vdc	1.8pF	±0.1pF	0.33max	20
GJM0334C1E1R9BB01	0603M/0201	CK	25Vdc	1.9pF	±0.1pF	0.33max	20
GJM0334C1E2R0BB01	0603M/0201	CK	25Vdc	2.0pF	±0.1pF	0.33max	20
GJM0333C1E2R1BB01	0603M/0201	CJ	25Vdc	2.1pF	±0.1pF	0.33max	20
GJM0333C1E2R2BB01	0603M/0201	CJ	25Vdc	2.2pF	±0.1pF	0.33max	20
GJM0333C1E2R3BB01	0603M/0201	CJ	25Vdc	2.3pF	±0.1pF	0.33max	20
GJM0333C1E2R4BB01	0603M/0201	CJ	25Vdc	2.4pF	±0.1pF	0.33max	20
GJM0333C1E2R5BB01	0603M/0201	CJ	25Vdc	2.5pF	±0.1pF	0.33max	20
GJM0333C1E2R6BB01	0603M/0201	CJ	25Vdc	2.6pF	±0.1pF	0.33max	20
GJM0333C1E2R7BB01	0603M/0201	CJ	25Vdc	2.7pF	±0.1pF	0.33max	20
GJM0333C1E2R8BB01	0603M/0201	CJ	25Vdc	2.8pF	±0.1pF	0.33max	20
GJM0333C1E2R9BB01	0603M/0201	CJ	25Vdc	2.9pF	±0.1pF	0.33max	20
GJM0333C1E3R0BB01	0603M/0201	CJ	25Vdc	3.0pF	±0.1pF	0.33max	20
GJM0333C1E3R1BB01	0603M/0201	CJ	25Vdc	3.1pF	±0.1pF	0.33max	20
GJM0333C1E3R2BB01	0603M/0201	CJ	25Vdc	3.2pF	±0.1pF	0.33max	20

GJM0333C1E3R3BB01	0603M/0201	CJ	25Vdc	3.3pF	±0.1pF	0.33max	20
GJM0333C1E3R4BB01	0603M/0201	CJ	25Vdc	3.4pF	±0.1pF	0.33max	20
GJM0333C1E3R5BB01	0603M/0201	CJ	25Vdc	3.5pF	±0.1pF	0.33max	20
GJM0333C1E3R6BB01	0603M/0201	CJ	25Vdc	3.6pF	±0.1pF	0.33max	20
GJM0333C1E3R7BB01	0603M/0201	CJ	25Vdc	3.7pF	±0.1pF	0.33max	20
GJM0333C1E3R8BB01	0603M/0201	CJ	25Vdc	3.8pF	±0.1pF	0.33max	20
GJM0333C1E3R9BB01	0603M/0201	CJ	25Vdc	3.9pF	±0.1pF	0.33max	20
GJM0332C1E4R0BB01	0603M/0201	CH	25Vdc	4.0pF	±0.1pF	0.33max	20
GJM0332C1E4R1BB01	0603M/0201	CH	25Vdc	4.1pF	±0.1pF	0.33max	20
GJM0332C1E4R2BB01	0603M/0201	CH	25Vdc	4.2pF	±0.1pF	0.33max	20
GJM0332C1E4R3BB01	0603M/0201	CH	25Vdc	4.3pF	±0.1pF	0.33max	20
GJM0332C1E4R4BB01	0603M/0201	CH	25Vdc	4.4pF	±0.1pF	0.33max	20
GJM0332C1E4R5BB01	0603M/0201	CH	25Vdc	4.5pF	±0.1pF	0.33max	20
GJM0332C1E4R6BB01	0603M/0201	CH	25Vdc	4.6pF	±0.1pF	0.33max	20
GJM0332C1E4R7BB01	0603M/0201	CH	25Vdc	4.7pF	±0.1pF	0.33max	20
GJM0332C1E4R8BB01	0603M/0201	CH	25Vdc	4.8pF	±0.1pF	0.33max	20
GJM0332C1E4R9BB01	0603M/0201	CH	25Vdc	4.9pF	±0.1pF	0.33max	20
GJM0332C1E5R0BB01	0603M/0201	CH	25Vdc	5.0pF	±0.1pF	0.33max	20
GJM0332C1E5R1BB01	0603M/0201	CH	25Vdc	5.1pF	±0.1pF	0.33max	20
GJM0332C1E5R6BB01	0603M/0201	CH	25Vdc	5.6pF	±0.1pF	0.33max	20
GJM0332C1E6R2BB01	0603M/0201	CH	25Vdc	6.2pF	±0.1pF	0.33max	20
GJM0332C1E6R8BB01	0603M/0201	CH	25Vdc	6.8pF	±0.1pF	0.33max	20
GJM0332C1E7R5BB01	0603M/0201	CH	25Vdc	7.5pF	±0.1pF	0.33max	20
GJM0332C1E8R2BB01	0603M/0201	CH	25Vdc	8.2pF	±0.1pF	0.33max	20
GJM0332C1E9R1BB01	0603M/0201	CH	25Vdc	9.1pF	±0.1pF	0.33max	20
GJM0332C1E100GB01	0603M/0201	CH	25Vdc	10pF	±2%	0.33max	20
GJM0332C1E110GB01	0603M/0201	CH	25Vdc	11pF	±2%	0.33max	20
GJM0332C1E120GB01	0603M/0201	CH	25Vdc	12pF	±2%	0.33max	20
GJM0332C1E130GB01	0603M/0201	CH	25Vdc	13pF	±2%	0.33max	20
GJM0332C1E150GB01	0603M/0201	CH	25Vdc	15pF	±2%	0.33max	20
GJM0332C1E160GB01	0603M/0201	CH	25Vdc	16pF	±2%	0.33max	20
GJM0332C1E180GB01	0603M/0201	CH	25Vdc	18pF	±2%	0.33max	20
GJM0332C1E200GB01	0603M/0201	CH	25Vdc	20pF	±2%	0.33max	20
GJM0332C1E220GB01	0603M/0201	CH	25Vdc	22pF	±2%	0.33max	20
GJM0332C1E240GB01	0603M/0201	CH	25Vdc	24pF	±2%	0.33max	20
GJM0332C1E270GB01	0603M/0201	CH	25Vdc	27pF	±2%	0.33max	20
GJM0332C1E300GB01	0603M/0201	CH	25Vdc	30pF	±2%	0.33max	20
GJM0332C1E330GB01	0603M/0201	CH	25Vdc	33pF	±2%	0.33max	20