



SINGLE INSULATED TPE OM PROBE Ø 5 X 20MM

SPECIFICATIONS

- IP 67 Rated
- TPE Overmolded probe with probe head dimensions of Ø 5 x 20mm
- 24 AWG Zipcord cable
- Ideal from ambient air sensing in building management applications, heater controls, air conditioning
- Available in a variety of connector types
- RoHS Compliant

This assembly consists of a NTC thermistor soldered to a single insulated TPE extension cable. The sensor and the extension cable are moulded together as one hot vulcanised unit to give a high degree of protection against water/moisture ingress.



FEATURES

- 24AWG Zipcord TPE cable
- IP 67 Rated
- Insulation Resistance 100MΩ @ 500VDC
- Available in a variety of connector types
- Customized tolerances and resistances available on request
- Temperature range -35°C to +105°C

APPLICATIONS


- Building Management Applications
- Heater Control
- Air Conditioning

SINGLE INSULATED TPE OM PROBE Ø 5 X 20MM

PERFORMANCE SPECS

Parameters	Units	Value
Nominal Resistance at +25°C	Ohms	10,000
Tolerance at +25°C	%	± 1
Beta Value 25/85	K	3435
Tolerance on Beta Value	%	± 1
Max power (probe in still air at +25°C)	mW	400
Time Response +25°C to 70°C. (63.2% Span)	Seconds	Approx. 15
Temperature range	°C	-35 to +105

MECHANICAL DETAILS



	Dimension			
	A	B	C	D
	5 ± 1mm	35 ± 3mm	Ø 5mm	20 ± 1mm
Note 1	NTC encapsulated using Black TPE over-mold material (Temp. Rating +125°C)			
Note 2	24AWG (7/32) Tin plated Zipcord cable with Black TPE jacket (Temp. Rating +125°C)			

Figure 1: TPE Overmoulded Probe Ø 5 x 20mm

SINGLE INSULATED TPE OM PROBE Ø 5 X 20MM

RESISTANCE V TEMPERATURE TABLE

Temp °C	KOhms
---------	-------

-35°C	144.30
-34°C	136.92
-33°C	129.96
-32°C	123.39
-31°C	117.19
-30°C	111.34
-29°C	105.81
-28°C	100.58
-27°C	95.64
-26°C	90.97
-25°C	86.55
-24°C	82.37
-23°C	78.42
-22°C	74.68
-21°C	71.13
-20°C	67.77
-19°C	64.59
-18°C	61.58
-17°C	58.72
-16°C	56.01
-15°C	53.44
-14°C	51.01
-13°C	48.69
-12°C	46.50
-11°C	44.41
-10°C	42.43
-9°C	40.55
-8°C	38.76
-7°C	37.06
-6°C	35.44
-5°C	33.91
-4°C	32.44
-3°C	31.05
-2°C	29.73
-1°C	28.47

Temp °C	KOhms
---------	-------

0°C	27.27
1°C	26.12
2°C	25.03
3°C	23.99
4°C	23.00
5°C	22.06
6°C	21.16
7°C	20.30
8°C	19.48
9°C	18.70
10°C	17.95
11°C	17.24
12°C	16.56
13°C	15.91
14°C	15.29
15°C	14.69
16°C	14.12
17°C	13.58
18°C	13.06
19°C	12.56
20°C	12.09
21°C	11.63
22°C	11.20
23°C	10.78
24°C	10.38
25°C	10.00
26°C	9.63
27°C	9.28
28°C	8.95
29°C	8.62
30°C	8.31
31°C	8.02
32°C	7.73
33°C	7.46
34°C	7.20
35°C	6.95

Temp °C	KOhms
---------	-------

36°C	6.70
37°C	6.47
38°C	6.25
39°C	6.04
40°C	5.83
41°C	5.63
42°C	5.44
43°C	5.26
44°C	5.08
45°C	4.92
46°C	4.75
47°C	4.60
48°C	4.45
49°C	4.30
50°C	4.16
51°C	4.03
52°C	3.90
53°C	3.77
54°C	3.66
55°C	3.54
56°C	3.43
57°C	3.32
58°C	3.22
59°C	3.12
60°C	3.02
61°C	2.93
62°C	2.84
63°C	2.75
64°C	2.67
65°C	2.59
66°C	2.51
67°C	2.44
68°C	2.37
69°C	2.30
70°C	2.23

Temp °C	KOhms
---------	-------

71°C	2.16
72°C	2.10
73°C	2.04
74°C	1.98
75°C	1.93
76°C	1.87
77°C	1.82
78°C	1.77
79°C	1.72
80°C	1.67
81°C	1.62
82°C	1.58
83°C	1.53
84°C	1.49
85°C	1.45
86°C	1.41
87°C	1.37
88°C	1.34
89°C	1.30
90°C	1.27
91°C	1.23
92°C	1.20
93°C	1.17
94°C	1.14
95°C	1.11
96°C	1.08
97°C	1.05
98°C	1.02
99°C	1.00
100°C	0.97
101°C	0.95
102°C	0.92
103°C	0.90
104°C	0.88
105°C	0.86

SINGLE INSULATED TPE OM PROBE Ø 5 X 20MM

ORDERING INFORMATION

Part Number	Description	Ω @25°C	MOQ
10K3435STM010	TPE OM Probe Ø 5 x 20mm Length 1 meter	10,000	1,000*
10K3435STM020	TPE OM Probe Ø 5 x 20mm Length 2 meters	10,000	1,000*
10K3435STM030	TPE OM Probe Ø 5 x 20mm Length 3 meters	10,000	1,000*

* For quantities less than Minimum Order Quantity – contact distribution

NORTH AMERICA

Measurement Specialties, Inc.,
a TE Connectivity Company
1711 139th Lane NW
Andover, MN 55304
Tel: +1 763 689 4870
Fax: +1 763 689 5033
customercare.ando@te.com

EUROPE

Measurement Specialties (Europe), Ltd.,
a TE Connectivity Company
Ballybrit Business Park
Galway Ireland
Tel : +353-91-753238
Fax : +353-91-770789
Email: customercare.glwy@te.com

ASIA

Measurement Specialties (China), Ltd.,
a TE Connectivity Company
No. 368 Wulian 1st Road
Gongxing Town
Shuangliu, Chengdu
Sichuan, 610200
China
Tel: +86 (0) 28 8573 9088
Fax: +86 (0) 28 8573 9070
Email: customercare.chdu@te.com

te.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties (MEAS), American Sensor Technologies (AST), TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2016 TE Connectivity Ltd. family of companies All Rights Reserved.