



















Features

- 5"x3" compact size
- Medical safety approved (2 x MOPP) accroding to ANSI/AAMI ES60601-1 and IEC/EN60601-1
- Suitable for BF application with appropriate system consideration
- · 200W convection,300W force air
- No load power consumption<0.5W by PS-ON control
- · Extremely low leakage current
- 5Vdc standby output, 12Vdc fan supply, Power Good, Power Fail and remote sense
- Protections: Short circuit / Overload / Over voltage / Over temperature
- Typical Lifetime > 40K hours
- · 3 years warranty


Applications

- Oral irrigator
- Hemodialysis machine
- Medical computer monitors
- · Sleep apnea devices
- · Pump machine
- · Electric bed

Description

RPS-300 is a 300W highly reliable green PCB type medical power supply with a high power density on the 5" by 3" footprint. It accepts $90\sim264$ VAC input and offers various output voltages between 12V and 48V. The working efficiency is up to 93% and the extremely low no load power consumption is down below 0.5W. The extremely low leakage current is less than 150 μ A. In addition, it conforms to international medical regulations (2*MOPP) and EMC EN55011, perfectly fitting all kinds of BF rated "patient contact" medical system equipment. RPS-300 series also offers the enclosed style model (RPS-300-C).

■ Model Encoding



Туре	Description	Note
Blank	PCB Type	In stock
С	Enclosed casing Type	In stock



SPECIFICATION

MODEL		RPS-300-12	RPS-300-15	RPS-300-24	RPS-300-27	RPS-300-48	
	DC VOLTAGE		12V	15V	24V	27V	48V
	RATED CURRENT (20.5CFM)		25A	20A	12.5A	11.12A	6.25A
		Convection	0 ~ 16.67A	0 ~ 13.33A	0 ~ 8.33A	0 ~ 7.4A	0 ~ 4.17A
	CURRENT	20.5CFM	0 ~ 25A	0 ~ 20A	0 ~ 12.5A	0 ~ 11.12A	0 ~ 6.25A
	RATED	Convection	200W	200W	200W	200W	200.2W
OUTDUT	POWER	20.5CFM	300W	300W	300W	300W	300W
OUTPUT	RIPPLE & NOISE (max.) Note.2		120mVp-p	120mVp-p	150mVp-p	200mVp-p	250mVp-p
	VOLTAGE ADJ. RANGE (main output)		11.4 ~ 12.6V	14.25 ~ 15.75V	22.8 ~ 25.2V	25.65 ~ 28.35V	45.6 ~ 50.4V
	VOLTAGE TO	DLERANCE Note.3	±3.0%	±3.0%	±2.0%	±2.0%	±2.0%
	LINE REG	ULATION	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%
	LOAD REC	GULATION	±1.0%	±1.0%	±1.0%	±1.0%	±1.0%
	SETUP, RI	SE TIME	2500ms, 30ms/230	VAC 3000ms,	30ms/115VAC at full	load	
	HOLD UP	TIME (Typ.)	13ms/230VAC/115\	/AC at full load			
	VOLTAGE RANGE Note.4		90 ~ 264VAC 127 ~ 370VDC				
	FREQUENCY RANGE		47 ~ 63Hz				
	POWER FACTOR (Typ.)		PF>0.93/230VAC PF>0.98/115VAC at full load				
INPUT	EFFICIENCY (Typ.)		90%	90%	92.5%	93%	93%
	AC CURRENT (Typ.)		3.5A/115VAC 1.8A/230VAC				
	INRUSH CURRENT (Typ.) COLD START 35A/115VAC 70A/230VAC						
	LEAKAGE CURRENT(max.) Note.5		PCB Type: Earth leakage current <150 µA / 264VAC, Touch current <70 µA / 264VAC				
			Enclosed Type: Earth leakage current <200 µA / 264 VAC, Touch current <70 µA / 264 VAC				
OVERLOAD		105 ~ 135% rated output power					
			Protection type : Hiccup mode, recovers automatically after fault condition is removed				oved
	PROTECTION OVER VOLTAGE		13.5 ~ 15V	16.2 ~ 18.5V	26 ~ 30V	29.5 ~ 33.5V	52 ~ 59.5V
PRUIECTION			Protection type : Shut down o/p voltage, re-power on to recover				
	OVER TEN	/IPERATURE	Protection type : (TSW1)Shut down o/p voltage, recovers automatically after temperature goes down				
			Protection type: (TSW2)Shut down o/p voltage, re-power on to recover				
	5V STAND		5Vsb : 5V@0.6A without fan, 1A with fan 20.5CFM ; tolerance ± 2%, ripple : 150mVp-p(max.)				
	FAN SUPP		12V@0.5A for driving a fan ; Tolerance -15% ~ +10%				
FUNCTION	PS-ON INF	PUT SIGNAL		·		"Low" or " < 0 ~ 0.5V	
	POWER F					•	wer set up ;
	WORKING	TEMP.	-30 ~ +70°C (Refer to "Derating Curve")				
	WORKING HUMIDITY		20 ~ 90% RH non-condensing				
ENVIDONMENT	STORAGE TEMP., HUMIDITY		-				
ENVIRONMENT	TEMP. COEFFICIENT		±0.03%/°C (0~50°C)				
	VIBRATIO		10 ~ 500Hz, 2G 10min./1cycle, 60min. each along X, Y, Z axes				
	OPERATING ALTITUDE Note.6						
OF LIVATING ALTITUDE NOIS.0			2000 HIOLOID				




	SAFETY STANDARDS	IEC60601-1, TUV EN60601-1,E	AC TP TC 004,			
		UL ANSI/AAMI ES60601-1 (3.1 version),				
	SAI LIT STANDARDS	CAN/CSA-C22.2 No. 60601-1:14	4 - Edition 3 approved;			
		Design refer to EN60335-1				
	ISOLATION LEVEL	Primary-Secondary: 2xMOPP, Primary-Earth:1xMOPP, Secondary-Earth:1xMOPP				
		I/P-O/P:4KVAC I/P-FG:2KVAC O/P-FG:1.5KVAC				
		I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH				
	ISSEMINATE NEEDS IN MINE	Parameter	Standard	Test Level / Note		
		Conducted emission	EN55011 (CISPR11)	Class B		
	EMC EMISSION	Radiated emission	EN55011 (CISPR11)	Class B		
		Harmonic current	EN61000-3-2	Class A		
CAFETY		Voltage flicker	EN61000-3-3			
SAFETY & EMC		EN60601-1-2	2.110.1000.0.0			
(Note 7)		Parameter	Standard	Test Level / Note		
		ESD	EN61000-4-2	Level 4, 15KV air ; Level 4, 8KV contact		
		E3D	LIN01000-4-2			
	EMC IMMUNITY	RF field susceptibility	EN61000-4-3	Level 3, 10V/m(80MHz~2.7GHz) Table 9, 9~28V/m(385MHz~5.78GHz)		
		EFT bursts	EN61000-4-4	Level 3, 2KV		
		Surge susceptibility	EN61000-4-5	Level 4, 4KV/Line-FG; 2KV/Line-Line		
		Conducted susceptibility	EN61000-4-6	Level 3, 10V		
		Magnetic field immunity	EN61000-4-8	Level 4, 30A/m		
		Voltage dip, interruption	EN61000-4-11	100% dip 1 periods, 30% dip 25 periods, 100% interruptions 250 periods		
	MTBF	160Khrs min. MIL-HDBK-217F (25° C)				
OTHERS	DIMENSION /I *\M*LI\	PCB type:127*76.2*35mm or 5"*	3"*1.37"inch			
	DIMENSION (L*W*H)	Enclosed type:130*86*43mm or 5.11"*3.39"*1.69"inch				
	PACKING	PCB type:0.37Kg; 36pcs/14.3Kg/1.03CUFT				
		Enclosed type:0.563Kg; 24pcs/14.5Kg/0.77CUFT				
NOTE	Ripple & noise are me Tolerance: includes se Derating may be need. Touch current was me The ambient temperatithan 2000m(6500ft). The power supply is consequently and the power supply is consequently.	pecially mentioned are measured at 230VAC input, rated load and 25 of ambient temperature. assured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1µf & 47µf parallel capacitor. But up tolerance, line regulation and load regulation. Bed under low input voltages. Please check the derating curve for more details. Such assured from primary input to DC output. For derating of 3.5°C/1000m with fanless models and of 5°C/1000m with fan models for operating altitude higher considered a component which will be installed into a final equipment. All the Class I (with FG) EMC tests are the unit on a 360mm*360mm metal plate with 1mm of thickness. The final equipment must be re-confirmed that it vess. For guidance on how to perform these EMC tests, please refer to "EMI testing of component power supplies."				

PFC fosc : 65KHz PWM fosc : 70KHz




■ Block Diagram




■ Derating Curve

300W With 20.5CFM Fan for RPS-300/RPS-300-C Convection for RPS-300 Convection for RPS-300-C Convection for RPS-300-C Convection for RPS-300-C AMBIENT TEMPERATURE (°C)


■ Output Derating VS Input Voltage













RPS-300 series

AC Input Connector (CN1): JST B5P-VH or equivalent

Pin No.	Assignment	Mating Housing	Terminal
1	AC/N		
2,4	No Pin	JST VHR	JST SVH-21T-P1.1
3	AC/L	or equivalent	or equivalent
5	FG ≟		

Function Connector(CN100):HRS DF11-4DP-2DS or equivalent

Pin No.	Status	Mating Housing	Terminal
1	-S		
2	+S	HRS DF11-4DS or equivalent	HRS DF11-**SC or equivalent
3	DC COM		
4	PG		

DC Output Connector (CN2,CN3)

Pin No.	Assignment	Output Terminals
CN2	-V	M3.5 Pan HD screw in 2 positions
CN3	+V	Torque to 8 lbs-in(90cNm)max.

1.HS1,HS2 cannot be shorted.

Function Connector(CN951):HRS DF11-4DP-2DS or equivalent

	,	,	
Pin No.	Status	Mating Housing	Terminal
1	5VSB		11D0 D544 ##00
2,4	DC COM	HRS DF11-4DS or equivalent	HRS DF11-**SC or equivalent
3	PS-ON	or equivalent	or equivalent

FAN Connector(CN952): JST S2B-XH or equivalent

Pin No.	Assignment	Mating Housing	Terminal
1	DC COM	JST XHP	JST SXH-001T-P0.6
2	+12V	or equivalent	or equivalent

- Note: 1. The FAN supply is designed to serve as the source of the additive external fan for the cooling of the power supply, enabling the full load delivery and assuring the best life span of the product. Please do not use this FAN supply to drive other devices.
 - 2. The PCB type (Blank type) model delivers EMI Class B for both conducted emission and radiated emission for power supply, when configured into either Class I (with FG).
 - 3. The enclosed type (-C type) model is not suitable for configuration within a Class $\, {
 m II} \,$ (no FG) system but suggested within a Class $\, {
 m II} \,$ (with FG) system.

■ Installation Manual

Please refer to: http://www.meanwell.com/manual.html