

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0474910001](#)
Status: **Active**
Overview: [USB Products and Solutions](#)
Description: Micro-USB B Receptacle, Mid-Mount, Matte Tin Plated Shell, Lead-Free


Documents:
[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

General
Product Family I/O Connectors
Series [47491](#)
Application Wire-to-Board
Comments Signal contacts 1.0A, Power contacts 1.8A
Component Type Receptacle
Overview [USB Products and Solutions](#)
Product Name USB 2.0
Type Micro-B
UPC 822350728454

Physical
Boot Color N/A
Circuits (Loaded) 5
Circuits (maximum) 5
Color - Resin Black
Durability (mating cycles max) 10000
Gender Female
Keying to Mating Part Yes
Lock to Mating Part No
Material - Metal Copper Alloy
Material - Plating Mating Gold
Material - Plating Termination Gold
Material - Resin High Temperature Thermoplastic
Net Weight 0.321/g
Number of Rows 1
Orientation Right Angle
PCB Retention None
Packaging Type Embossed Tape on Reel
Panel Mount No
Pitch - Mating Interface 0.65mm
Pitch - Termination Interface 0.65mm
Polarized to Mating Part Yes
Ports 1
Surface Mount Compatible (SMC) No
Temperature Range - Operating -30° to +85°C
Termination Interface: Style N/A
Waterproof / Dustproof No

Electrical
Current - Maximum per Contact 1.8A, 1.0A
Grounding to Panel Yes
Shield Type Full Shield
Shielded Yes
Voltage - Maximum 30V AC (RMS)

Solder Process Data
Duration at Max. Process Temperature (seconds) 020



Series image - Reference only

EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/61/2018 (27 June 2018)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[47491 Series](#)

Lead-free	Process Capability	REFLOW
Max. Cycles at Max. Process Temperature		001
Process Temperature max. C		245

Material Info

This document was generated on 10/11/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION