

AC-DC Power Supplies CUS100ME 100W



TDK-Lambda

Produkt-Merkmale

- Raffreddamento a convezione naturale 2 x 4 inch
- Approvazioni IEC60601-1 3rd Edition (2 x MoPP Isolation) & IEC60950-1
- Opzioni : U channel, cover, baseplate
- 5 anni di garanzia

Spezifikationen

- Potenza di uscita 100W fino a 70°C con modelli U channel o baseplate
- Condotte e radiate EMI Classe B
- Tensioni di uscita 12, 15, 18, 24, 28, 36 e 48VDC
- Adatto per applicazioni in Classe I e Classe II

Typische Einsatzbereiche

- Apparecchiature medicali (ospedaliere, dentali, cliniche e sanitarie)
- Broadcast e sistemi audio professionali
- Test & Misurazioni
- Display e segnaletica a LED

Product Highlights

- 2 x 4 inch Convection Cooled Design
- IEC60601-1 3rd Edition (2 x MoPP Isolation) & IEC60950-1 Approvals
- Options for U channel, cover, baseplate
- 5 Year Warranty

Key Specifications

- Output Power 100W up to 70°C with U channel or Baseplate option
- Curve B Conducted and Radiated EMI
- Outputs 12, 15, 18, 24, 28, 36 and 48VDC
- Suitable for Class I and Class II Installations

Typical Applications

- Medical including Hospital, Dental, Clinical and Healthcare Equipment
- Broadcast and Professional Audio
- Test and Measurement
- LED Displays and Signage

For more information about TDK-Lambda: www.emea.tdk-lambda.com