

SGS15 Power Supply



Features:

- Low Cost, High Reliability
- Overload and Short Circuit Protection
- Free air cooling convection
- High operating temperature up to 60°C



Model		SGS15-5	SGS15-12	SGS15-15	SGS15-24	SGS15-48
Output	DC Voltage	5V	12V	15V	24V	48V
	Rated Current	3A	1.3A	1A	0.7A	0.35A
	Current Range	0~3A	0~1.3A	0~1A	0~0.7A	0~0.35A
	Rated Power	15W	15.6W	15W	16.8W	16.8W
	Ripple & Noise	100mVp-p	120mVp-p	150mVp-p	200mVp-p	240mVp-p
	Voltage Regulation Range	4.5~5.5V	10.8~13.2V	13.5~16.5V	21.6~26.4V	44~52V
	Voltage Accuracy	+/- 1.0%				
	Line Regulation	+/- 0.5%				
	Load Regulation	+/- 2.0 %	+/- 1.0%	+/- 1.0%	+/- 1.0%	+/- 1.0%
	Rise Time	2000ms, 50ms / 230Vac at 100% Load				
Hold Up Time	20ms / 230Vac at 100% Load					
Input	Full Input Voltage Range	88-264Vac				
	Full Frequency Range	47-63Hz				
	AC Current	0.4A / 115Vac	0.4A / 230Vac			
	In Rush Current	40A / 230Vac				
	Leakage Current	<3.5mA / 230Vac				
Protection	Over Load	110~150% rated output power				
	Short Circuit	Hiccup Mode, auto-recovery after fault condition is removed				
Environment	Working Temp	-10°C ~ +60°C (230Vac) (Refer to output derating curve)				
	Working Humidity	20~90%RH non-condensing				
	Storage Temp	-20°C ~ +45°C				
	Storage Humidity	10 ~ 95%RH non-condensing				
	Temp. Coefficiency	+/-0.03% / °C (0 ~ 50°C)				
	Vibration Resistance	10 ~ 500Hz, 2G, 10 minute cycle, X, Y, Z 60 minute in each direction				
Safety	Safety Standards	EN60950-1, UL60950-1, CSA-C22.2 No. 60950-1 Approved				
	Withstand Voltage	I/P-O/P: 3KVac I/P-FG: 1.5KVac O/P-FG: 0.5KVac				
	Isolation Resistance	I/P-O/P, I/P-FG, O/P-FG: >50M Ω / 500VDC / 25 °C / 70%RH				
	EMC Emission	Compliance to EN55022 Class B, EN61000-3-2, -3				
	EMC Immunity	Compliance to EN55024, EN61000-4-2, -3, -4, -5, -6, -8, -11				
Others	Lifetime	50,000 Hours (25 °C)				
	Size	85mm x 58.5mm x 36.5mm (L x W x H)				
	Package	80pcs/ctn, 20KG, 0.25Kg/piece				
Notes	1) All parameters NOT specially mentioned are measured at 230Vac input, rated load and 25°C of ambient temperature. 2) Ripple Test method: 20MHz oscilloscope in power output terminal test, oscilloscope probe wire length is not more than 12mm and input parallel 47uF electrolytic capacitors and 0.1uF high frequency capacitance probe. 3) The power supply is considered a component which must be installed into final equipment. The final equipment must be re-confirmed that it meets all applicable directives.					

Stadium Stontronics Ltd

Chancerygate Business Centre, Cradock Road, Reading, Berkshire, RG2 0AH.

Tel: +44 (0) 118 931 1199 • Fax: +44 (0) 118 931 1145 • Email: info@stontronics.co.uk • Web: www.stontronics.com

Please Note: Image shown is representative of entire range. Individual PSU image &/or drawings or data sheets available on request.

Stontronics Ltd accepts no responsibility for typographical errors in the production of this leaflet. Product specifications are subject to change without notice.

