

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0857271003](#)
Status: **Active**
Overview: Magnetic Modular Jacks
Description: Gigabit Magnetic Jack 2X4, LEDs Green/Yellow

Documents:

[3D Model](#) [Packaging Specification PK-85727-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-85728-001-001 \(PDF\)](#)

General

Product Family	Modular Jacks/Plugs
Series	85727
Comments	With LED
Component Type	PCB Jack
Magnetic	Yes
Overview	<u>Magnetic Modular Jacks</u>
Performance Category	5, 5e
Power over Ethernet (PoE)	Non-PoE
Product Name	Magnetic Jack, Modular Jack 8/8, RJ45
UPC	887191095585

Physical

Durability (mating cycles max)	750
Inverted / Top Latch	Yes
Jack Height	25.43mm
Lightpipes/LEDs	LEDs
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	PBT
Net Weight	42.060/g
Orientation	Right Angle (Side Entry)
PCB Retention	N/A
PCB Thickness - Recommended	2.20mm
Packaging Type	Tray
Pitch - Mating Interface	1.02mm
Plating min - Mating	0.762µm
Ports	8
Positions / Loaded Contacts	8/8
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	0° to +70°C
Termination Interface: Style	Through Hole
Wire/Cable Type	CAT 5, CAT 6

Electrical


Current - Maximum per Contact	1.5A
Grounding to PCB	Yes
Grounding to Panel	Panel Ground Tab
Shielded	Yes
Voltage - Maximum	125V AC (RMS)

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 7(c)-I

REACH SVHC

Contained Per - ED/30/2017 (7 July 2017)
 2,4-Di-tert-butyl-6-(5-chlorobenzotriazol-2-yl)p

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[85727 Series](#)

Mates With

[95043](#) , [44915](#) Plugs according to IEC 60603-7

This document was generated on 09/24/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION