ACmaxx axial fans

□ 80 x 32 mm



Housing: GRP1) (PBTP) Material: Impeller: GRP1) (PA)

Direction of air flow: Exhaust over struts

Direction of rotation: Clockwise, looking towards

rotor

Connection: Via single wires AWG 22,

TR 64

Highlights: Universally usable for all

power voltages between

85 and 265 VAC

Weight: 325 g

1) Fiberglass-reinforced plastic

- Possible special versions:

(See chapter DC fans - specials)

- Speed signal

- Go / NoGo alarm

- Alarm with speed limit

- External temperature sensor

- Internal temperature sensor

- PWM control input

- Analog control input


- Moisture protection


- Salt spray protection

- Degree of protection: IP 54

Series AC 8300			/oltage	>	nge	pressure level	power level	leeve bearings rings	onsumption	peed	ıre range	L ₁₀ (40 °C) standard L ₁₀ (T _{max}) standard	pectancy L _{10IPC} see page 17		
Nominal data	Air flow	Air flow	Nominal v	Frequency	Voltage range	Sound pre	Sound pov	Sintec slee Ball bearir	Power cor	Nominal s	Temperature	Service life ebm-papst: Service life ebm-papst	Life expect: (40 °C) see	Curve	
Туре	m³/h	cfm	VAC	Hz	VAC	dB(A)	Bel(A)	■/■	Watts	rpm ⁻¹	°C	Hours	Hours		
AC 8300 H	80	47	115 / 230	50 / 60	85 265	48	6.2	-	8.3	5 000	-20+75	55 000 / 20 000	92 500	ن	
Subject to change															

Speed variants available on request.






Air performance measured according to: ISO 5801. Installation category A, without contact protection. Noise: Total sound power level L_WA ISO 103002 measured on a hemisphere with a radius of 2 m. Sound pressure level LpA measured at 1 m distance

from fan axis.

The values given are applicable only under the specified measuring conditions and may differ depending on the installation conditions.

In the event of deviation from the standard configuration, the parameters must be checked after installation For detailed information see

http://www.ebmpapst.com/general conditions



2016-01