



CSA rating data

AWG conductor, min. (CSA)	26
AWG conductor, max. (CSA)	12

DIN IEC rating data

Rated current, min. No. pins(Tu=40°C)	32 A
Short-time withstand current resistance	3 x 1s with 120 A
Rated current, min. No. pins (Tu=20°C)	32 A

Material specification

Contact surface	tinned
Contact base material	Cu alloy
Insulating material group	I
Insulation material	PA
CTI	>= 600
UL 94 combustibility class	V-2
Colour	orange

System parameters

Fitting hole tolerance	+ 0.1 mm
L1 in inch	0,400 inch
L1 in mm	10,16 mm
Pitch in inch	0,200 inch
Stripping length	6 mm
Electric shock protection to DIN VDE 0470	IP 20
Electric shock protection to DIN VDE 0470	Safe from finger touch
Volume resistance	1,2 mΩ
Dia. of fitting hole	1,3 mm
Clamping screw	M 3
Fitted by customer	yes
Fitted to PCB	Soldered connection
Pitch	5,08 mm
Type of screwdriver	SD 0.8 x 4.0 - DIN 5264
Number of poles	3
Length of soldering post	3,2 mm

UL 1059 rating data

Rated voltage, user group D	300 V
AWG conductor, min. (UL 1059)	26
AWG conductor, max. (UL 1059)	12

Connectable conductors

AWG, max.	12
Gauge to EN 60999 a x b; ø	2.8 mm x 2.4 mm; 3.0 mm
Clamping range, min.	0,13 mm ²
Clamping range, max.	6 mm ²
fine-stranded, min. H05(07) V-U	0,5 mm ²
fine-stranded, max. H05(07) V-U	4 mm ²
Solid, min. H05(07) V-U	0,5 mm ²
Solid, max. H05(07) V-U	6 mm ²
AWG, min.	26
w. plastic collar ferrule, DIN 46228 pt 4, min.	0,5 mm ²
w. plastic collar ferrule, DIN 46228 pt 4, max.	2,5 mm ²
Wire end ferrule , DIN 46 228/1, min.	0,5 mm ²
Wire end ferrule , DIN 46 228/1, max.	2,5 mm ²

Approvals

Approvals



Classifications

ETIM 2.0	NK
eClass 4.1	NK
eClass 5.0	NK
eClass 5.1	NK

General ordering data

Order No.	1640920000
Short text for material	LP1H5.08/3 3.2 OR
EAN	4008190449872

- Additional colours on request
- Rated current related to rated cross-section and min. No. of poles.
- Wire end ferrule without plastic collar to DIN 46228 pt 1
- Wire end ferrule with plastic collar to DIN 46228 pt 4
- P on drg. = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.

Related products

Order No.	Short text for material	Number of poles
1640910000	LP1H5.08/2 3.2 OR	2