

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0348250124](#)  
**Status:** **Active**  
**Overview:** [Mini50 Connection Systems](#)  
**Description:** Mini50 Unsealed Vertical Header, Dual Row, 12 Circuit, Polarization Option A, Black, Tray

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification AS-34791-020-CH-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Application Specification AS-34791-020-FR-001 (PDF)</a>
<a href="#">Product Specification PS-34791-020-001 (PDF)</a>	<a href="#">Packaging Specification PK-31301-440 (PDF)</a>
<a href="#">Application Specification AS-34791-020 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification AS-34791-020-001 (PDF)</a>	<a href="#">Product Literature (PDF)</a>

**General**


Product Family	PCB Headers
Series	34825
Application	Power, Signal, Wire-to-Board
Overview	<a href="#">Mini50 Connection Systems</a>
Product Literature Order No	987650-5442
Product Name	Mini50
UPC	887191338668

**Physical**

Breakaway	No
Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Black
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin over Nickel
Material - Plating Termination	Tin over Nickel
Material - Resin	High Temperature Thermoplastic
Net Weight	2.068/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	2.87mm
PCB Locator	Yes
Packaging Type	Tray
Pitch - Mating Interface	2.00mm
Plating min - Mating	2.500µm
Plating min - Termination	2.500µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole

**Electrical**

Current - Maximum per Contact	4.0A
Voltage - Maximum	500V DC



**EU ELV**  
**Compliant**

**EU RoHS**  
**Compliant**  
**REACH SVHC**

Not Contained Per -  
ED/61/2018 (27 June  
2018)

**Halogen-Free**  
**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

[34825 Series](#)

**Mates With**

[34824 Mini50 Unsealed Dual Row Receptacle](#)

**Solder Process Data**

Lead-free Process Capability

N/A

**Material Info****Reference - Drawing Numbers**

Application Specification

AS-34791-020, AS-34791-020-001, AS-34791-020-  
CH-001, AS-34791-020-FR-001

Packaging Specification

PK-31301-440

Product Specification

PS-34791-020-001

This document was generated on 10/29/2018

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**