



## Safety Data Sheet according to Regulation (EC) No 1907/2006

Page 1 of 12

LOCTITE LB 8150 SV A/S known as Silver Grade Anti-Seize Lubric

SDS No. : 153549  
V005.0

Revision: 06.03.2018

printing date: 05.03.2019

Replaces version from: 05.08.2014

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

LOCTITE LB 8150 SV A/S known as Silver Grade Anti-Seize Lubric

#### Contains:

Calcium oxide

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:  
Antiseize

#### 1.3. Details of the supplier of the safety data sheet

Henkel Ltd  
Wood Lane End  
HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 1442 278000  
Fax-no.: +44 1442 278071

ua-productsafety.uk@henkel.com

#### 1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification (CLP):

Skin irritation	Category 2
H315 Causes skin irritation.	
Serious eye damage	Category 1
H318 Causes serious eye damage.	

#### 2.2. Label elements

##### Label elements (CLP):

Hazard pictogram:



Signal word:

Danger

**Hazard statement:** H318 Causes serious eye damage.  
H315 Causes skin irritation.

**Precautionary statement:** P280 Wear eye protection/face protection.  
**Prevention**

**Precautionary statement:** P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
**Response** P302+P352 IF ON SKIN: Wash with plenty of soap and water.

### 2.3. Other hazards

None if used properly.

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

## SECTION 3: Composition/information on ingredients

### 3.2. Mixtures

#### General chemical description:

Antiseize

#### Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Calcium oxide 1305-78-8	215-138-9 01-2119475325-36	10- < 20 %	Skin Irrit. 2; Dermal H315 Eye Dam. 1 H318 STOT SE 3; Inhalation H335
Distillates (petroleum), hydrotreated light naphthenic < 3% DMSO 64742-53-6	265-156-6 01-2119480375-34	10- 20 %	Asp. Tox. 1 H304

For full text of the H - statements and other abbreviations see section 16 "Other information".

Substances without classification may have community workplace exposure limits available.

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

#### Inhalation:

Move to fresh air. If symptoms persist, seek medical advice.

#### Skin contact:

Rinse with running water and soap.

Seek medical advice.

#### Eye contact:

Rinse immediately with plenty of running water (for 10 minutes). Seek medical attention if necessary.

#### Ingestion:

Rinse out mouth, drink 1-2 glasses of water, do not induce vomiting.

Seek medical advice.

### 4.2. Most important symptoms and effects, both acute and delayed

SKIN: Redness, inflammation.

After eye contact: Corrosive, may cause permanent damage to eyes (impairment of vision).

### 4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

#### Suitable extinguishing media:

Carbon dioxide, foam, powder

#### Extinguishing media which must not be used for safety reasons:

None known

### 5.2. Special hazards arising from the substance or mixture

In the event of a fire, carbon monoxide (CO), carbon dioxide (CO<sub>2</sub>) and nitrogen oxides (NO<sub>x</sub>) can be released.  
Oxides of carbon.

### 5.3. Advice for firefighters

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

#### Additional information:

In case of fire, keep containers cool with water spray.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

Avoid contact with skin and eyes.

Wear protective equipment.

Ensure adequate ventilation.

### 6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

### 6.3. Methods and material for containment and cleaning up

For small spills wipe up with paper towel and place in container for disposal.

For large spills absorb onto inert absorbent material and place in sealed container for disposal.

### 6.4. Reference to other sections

See advice in section 8

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Avoid skin and eye contact.

See advice in section 8

Use only in well-ventilated areas.

#### Hygiene measures:

Good industrial hygiene practices should be observed.

Do not eat, drink or smoke while working.

Wash hands before work breaks and after finishing work.

### 7.2. Conditions for safe storage, including any incompatibilities

Store in a cool, well-ventilated place.

Keep away from heat and direct sunlight.

Refer to Technical Data Sheet

### 7.3. Specific end use(s)

Antiseize

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

#### Occupational Exposure Limits

Valid for  
Great Britain

Ingredient [Regulated substance]	ppm	mg/m <sup>3</sup>	Value type	Short term exposure limit category / Remarks	Regulatory list
Graphite 7782-42-5 [GRAPHITE, INHALABLE DUST]		10	Time Weighted Average (TWA):		EH40 WEL
Graphite 7782-42-5 [GRAPHITE, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		EH40 WEL
Graphite 7782-42-5 [DUST, INHALABLE DUST]		10	Time Weighted Average (TWA):		EH40 WEL
Graphite 7782-42-5 [DUST, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		EH40 WEL
Calcium oxide 1305-78-8 [CALCIUM OXIDE]		2	Time Weighted Average (TWA):		EH40 WEL
Calcium oxide 1305-78-8 [CALCIUM OXIDE (RESPIRABLE FRACTION)]		1	Time Weighted Average (TWA):	Indicative	ECTLV
Calcium oxide 1305-78-8 [CALCIUM OXIDE (RESPIRABLE FRACTION)]		4	Short Term Exposure Limit (STEL):	Indicative	ECTLV

#### Occupational Exposure Limits

Valid for  
Ireland

Ingredient [Regulated substance]	ppm	mg/m <sup>3</sup>	Value type	Short term exposure limit category / Remarks	Regulatory list
Distillates (petroleum), hydrotreated heavy naphthenic 64742-52-5 [MINERAL OIL, PURE, HIGHLY & SEVERELY REFINED, INHALABLE FRACTION]		5	Time Weighted Average (TWA):		IR_OEL
Graphite 7782-42-5 [GRAPHITE, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		IR_OEL
Graphite 7782-42-5 [GRAPHITE, TOTAL INHALABLE DUST]		10	Time Weighted Average (TWA):		IR_OEL
Graphite 7782-42-5 [DUSTS, NON-SPECIFIC, RESPIRABLE]		4	Time Weighted Average (TWA):		IR_OEL
Graphite 7782-42-5 [DUSTS, NON-SPECIFIC, TOTAL INHALABLE]		10	Time Weighted Average (TWA):		IR_OEL
Calcium oxide 1305-78-8 [CALCIUM OXIDE]		2	Time Weighted Average (TWA):		IR_OEL
Calcium oxide 1305-78-8 [CALCIUM OXIDE (RESPIRABLE FRACTION)]		1	Time Weighted Average (TWA):	Indicative	ECTLV
Calcium oxide 1305-78-8 [CALCIUM OXIDE (RESPIRABLE FRACTION)]		4	Short Term Exposure Limit (STEL):	Indicative	ECTLV

Distillates (petroleum), hydrotreated light naphthenic < 3% DMSO 64742-53-6 [MINERAL OIL, PURE, HIGHLY & SEVERELY REFINED, INHALABLE FRACTION]		5	Time Weighted Average (TWA):		IR_OEL
--	--	---	------------------------------	--	--------

**Predicted No-Effect Concentration (PNEC):**

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
Calcium oxide 1305-78-8	aqua (freshwater)		0,37 mg/l				
Calcium oxide 1305-78-8	aqua (marine water)		0,24 mg/l				
Calcium oxide 1305-78-8	aqua (intermittent releases)		0,37 mg/l				
Calcium oxide 1305-78-8	sewage treatment plant (STP)		2,27 mg/l				
Calcium oxide 1305-78-8	soil				817,4 mg/kg		
Calcium oxide 1305-78-8	sediment (freshwater)						
Calcium oxide 1305-78-8	sediment (marine water)						
Calcium oxide 1305-78-8	Air						
Calcium oxide 1305-78-8	Predator						
Distillates (petroleum), hydrotreated light naphthenic < 3% DMSO 64742-53-6	oral				9,33 mg/kg		

**Biological Exposure Indices:**

None

**8.2. Exposure controls:**

## Engineering controls:

Ensure good ventilation/extraction.

## Respiratory protection:

Use only in well-ventilated areas.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A (EN 14387)

## Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to &gt; 30 minutes permeation time as per EN 374):

nitrile rubber (NBR;  $\geq 0.4$  mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to &gt; 480 minutes permeation time as per EN 374):

nitrile rubber (NBR;  $\geq 0.4$  mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:  
Wear protective glasses.  
Protective eye equipment should conform to EN166.

Skin protection:  
Wear suitable protective clothing.  
Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

Advices to personal protection equipment:

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions. Personal protective equipment should conform to the relevant EN standard.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Appearance	paste silver
Odor	mild
Odour threshold	No data available / Not applicable
pH	Not applicable
Melting point	No data available / Not applicable
Solidification temperature	No data available / Not applicable
Initial boiling point	Not determined
Flash point	> 93 °C (> 199.4 °F)
Evaporation rate	No data available / Not applicable
Flammability	No data available / Not applicable
Explosive limits	No data available / Not applicable
Vapour pressure	< 5 mm hg
Relative vapour density:	Heavier than air
Density	1,25 g/cm <sup>3</sup>
( )	
Bulk density	No data available / Not applicable
Solubility	No data available / Not applicable
Solubility (qualitative)	Insoluble
(Solvent: Water)	
Partition coefficient: n-octanol/water	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Decomposition temperature	No data available / Not applicable
Viscosity	121.000 - 258.000 mPa.s
(; Instrument: RVT; speed of rotation: 5 min-1; Spindle No: TD)	
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Oxidising properties	No data available / Not applicable

### 9.2. Other information

No data available / Not applicable

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

Reacts with strong oxidants.

### 10.2. Chemical stability

Stable under recommended storage conditions.

### 10.3. Possibility of hazardous reactions

See section reactivity

### 10.4. Conditions to avoid

Stable

**10.5. Incompatible materials**

See section reactivity.

**10.6. Hazardous decomposition products**

Irritating organic vapours.  
carbon oxides.

**SECTION 11: Toxicological information****11.1. Information on toxicological effects****Acute oral toxicity:**

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
Calcium oxide 1305-78-8	LD50	> 2.000 mg/kg	rat	OECD Guideline 425 (Acute Oral Toxicity: Up-and-Down Procedure)
Distillates (petroleum), hydrotreated light naphthenic < 3% DMSO 64742-53-6	LD50	> 5.000 mg/kg	rat	not specified

**Acute dermal toxicity:**

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
Calcium oxide 1305-78-8	LD50	> 2.500 mg/kg	rabbit	OECD Guideline 402 (Acute Dermal Toxicity)
Distillates (petroleum), hydrotreated light naphthenic < 3% DMSO 64742-53-6	LD50	> 5.000 mg/kg	rabbit	not specified

**Acute inhalative toxicity:**

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Test atmosphere	Exposure time	Species	Method
Distillates (petroleum), hydrotreated light naphthenic < 3% DMSO 64742-53-6	LC50	> 5,53 mg/l	dust/mist	4 h	rat	OECD Guideline 403 (Acute Inhalation Toxicity)

**Skin corrosion/irritation:**

Solvent may remove essential oils from the skin making it susceptible to attack from other chemicals.

No substance data available.

**Serious eye damage/irritation:**

Expected to cause eye irritation by abrasive action of tiny metal particles

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
Calcium oxide 1305-78-8	Category 1 (irreversible effects on the eye)		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)

**Respiratory or skin sensitization:**

No data available.

**Germ cell mutagenicity:**

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
Calcium oxide 1305-78-8	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		EPA OPPTS 870.5265 (The Salmonella typhimurium Bacterial Reverse Mutation Test)
Calcium oxide 1305-78-8	negative	mitotic recombination in Sacch. cerevisiae	with and without		OECD Guideline 481 (Genetic Toxicology: Saccharomyces cerevisiae, Mitotic Recombination Assay)
Distillates (petroleum), hydrotreated light naphthenic < 3% DMSO 64742-53-6	negative	in vitro mammalian chromosome aberration test	with and without		OECD Guideline 473 (In vitro Mammalian Chromosome Aberration Test)

**Carcinogenicity**

No data available.

**Reproductive toxicity:**

No data available.

**STOT-single exposure:**

No data available.

**STOT-repeated exposure::**

No data available.

**Aspiration hazard:**

The mixture is classified based on Viscosity data.

Hazardous substances CAS-No.	Viscosity (kinematic) Value	Temperature	Method	Remarks
Distillates (petroleum), hydrotreated light naphthenic < 3% DMSO 64742-53-6	9 mm <sup>2</sup> /s	40 °C	not specified	



## SECTION 12: Ecological information

### General ecological information:

Do not empty into drains / surface water / ground water.

### 12.1. Toxicity

#### Toxicity (Fish):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Calcium oxide 1305-78-8	LC50	50,6 mg/l	96 h	Oncorhynchus mykiss	OECD Guideline 203 (Fish, Acute Toxicity Test)
Distillates (petroleum), hydrotreated light naphthenic < 3% DMSO 64742-53-6	LL50	> 100 mg/l	96 h	Pimephales promelas	OECD Guideline 203 (Fish, Acute Toxicity Test)

#### Toxicity (Daphnia):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Calcium oxide 1305-78-8	EC50	49,1 mg/l	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)
Distillates (petroleum), hydrotreated light naphthenic < 3% DMSO 64742-53-6	EC50	> 1.000 mg/l	48 h	Daphnia magna	not specified

#### Chronic toxicity to aquatic invertebrates

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Calcium oxide 1305-78-8	NOEC	32 mg/l	14 d	Crangon septemspinosa	OECD Guideline 202 (Daphnia sp. Chronic Immobilisation Test)

#### Toxicity (Algae):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Calcium oxide 1305-78-8	EC50	184,57 mg/l	72 h	Pseudokirchneriella subcapitata	OECD Guideline 201 (Alga, Growth Inhibition Test)
Calcium oxide 1305-78-8	NOEC	48 mg/l	72 h	Pseudokirchneriella subcapitata	OECD Guideline 201 (Alga, Growth Inhibition Test)

#### Toxicity to microorganisms

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Calcium oxide 1305-78-8	EC20	229,2 mg/l	3 h	activated sludge of a predominantly domestic sewage	OECD Guideline 209 (Activated Sludge, Respiration Inhibition Test)

**12.2. Persistence and degradability**

No data available for the product.

No substance data available.

**12.3. Bioaccumulative potential**

No data available.

No substance data available.

**12.4. Mobility in soil**

Cured adhesives are immobile.

No substance data available.

**12.5. Results of PBT and vPvB assessment**

Hazardous substances CAS-No.	PBT / vPvB
Calcium oxide 1305-78-8	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.
Distillates (petroleum), hydrotreated light naphthenic < 3% DMSO 64742-53-6	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

**12.6. Other adverse effects**

No data available.

**SECTION 13: Disposal considerations****13.1. Waste treatment methods**

Product disposal:

Dispose of in accordance with local and national regulations.

Collection and delivery to recycling enterprise or other registered elimination institution.

Disposal of uncleaned packages:

Disposal must be made according to official regulations.

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Waste code

14 06 03 - other solvents and solvent mixtures

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

**SECTION 14: Transport information****14.1. UN number**

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	Not dangerous goods
IATA	1910

**14.2. UN proper shipping name**

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	Not dangerous goods
IATA	Calcium oxide

**14.3. Transport hazard class(es)**

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	Not dangerous goods
IATA	8

**14.4. Packing group**

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	Not dangerous goods
IATA	III

**14.5. Environmental hazards**

ADR	not applicable
RID	not applicable
ADN	not applicable
IMDG	not applicable
IATA	not applicable

**14.6. Special precautions for user**

ADR	not applicable
RID	not applicable
ADN	not applicable
IMDG	not applicable
IATA	No dangerous good according to ADR/RID/ADN. Carriage in accordance with 1.1.4.2.1 ADR/RID/ADN.

**14.7. Transport in bulk according to Annex II of Marpol and the IBC Code**

not applicable

**SECTION 15: Regulatory information****15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

VOC content < 3 %  
(2010/75/EC)

**15.2. Chemical safety assessment**

A chemical safety assessment has not been carried out.

**SECTION 16: Other information**

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

H304 May be fatal if swallowed and enters airways.

H315 Causes skin irritation.

H318 Causes serious eye damage.

H335 May cause respiratory irritation.

**Further information:**

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

**Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.**