

WAFER-TWEEZERS



For positioning of flat and fine components, e.g. extremely sensitive and breakable wafer (glass-wafer etc.) fine PCB's and LCD's very smooth and non-reflective surface
high grade steel SA, anti-magnetic

No.	Length		Finish / Model	Weight g
	mm	inch		
5-411	130	5 1/8"	with graduated lower paddle and 3 teeth 3 DWF small <i>as before, with ESD coating</i>	14
5-411-13				
5-412	130	5 1/8"	with graduated lower paddle and 3 teeth 3 DWF <i>as before, with ESD coating</i>	14
5-412-13				
5-413	130	5 1/8"	with graduated lower paddle and 4 teeth 4 DWF <i>as before, with ESD coating</i>	17
5-413-13				
5-414	130	5 1/8"	with graduated lower paddle and 5 teeth 5 DWF <i>as before, with ESD coating</i>	20
5-414-13				
5-415	130	5 1/8"	with graduated lower paddle and 6 teeth 6 DWF <i>as before, with ESD coating</i>	20
5-415-13				
5-421	130	5 1/8"	with graduated lower paddle, no teeth 3 DW small <i>as before, with ESD coating</i>	14
5-421-13				
5-422	130	5 1/8"	with graduated lower paddle, no teeth 4 DW <i>as before, with ESD coating</i>	17
5-422-13				
5-423	130	5 1/8"	with graduated lower paddle, no teeth 5 DW <i>as before, with ESD coating</i>	20
5-423-13				
5-424	130	5 1/8"	with graduated lower paddle, no teeth 6 DW <i>as before, with ESD coating</i>	20
5-424-13	130	5 1/8"	<i>as before, with ESD coating</i>	



4-412-13



5-413



5-414-13



5-415



5-421-13



5-422




5-423-13



5-424



5-424-13



	Dimension					for Wafer Size Zoll
	A	B	C	D	E	
	mm	mm	mm	mm	mm	
5-411	6	6	4	4	3.2	2"
5-412	9	6	2.5	3	3.2	2"
5-413	12	8	4	5	3.2	3"
5-414	16	6	4	5	3.2	4" - 5"
5-415	20	8	4	5	3.2	6"
5-421	6	6	4	5	3	2"
5-422	12	8	4	5	3	3"
5-423	16	8	4	4	3	4" - 5"
5-424	20	8	4	5	3.5	6"

TITAN TWEEZERS

Tweezers made from titan are for the highest demands, have a light weight, immunity to corrosion, even to aggressive acids, they are antimagnetic, antibacterial, solder-repellent, and non-reflective. The melting point is 1677°C.

5-031	110	4 3/8"	matt-stainless, sharply pointed	9
5-035	120	4 3/4"	matt-stainless, sharply pointed	9
5-036	145	5 3/4"	matt-stainless, straight - round - wide, tips with fine serration	15
5-037	150	6"	matt-stainless, fine bent tips tips with fine serration	12

