

RoHS

COMPLIANT HALOGEN

FREE

GREEN

(5-2008)



Vishay Dale

Power Metal Plate Current Sense Resistors, Low Value (5 m Ω to 500 m Ω), Surface-Mount, High Power



FEATURES

- 2010 and 2512 size package
- Ideal for all types of current sensing and pulse applications including switching and linear power supplies, instruments, power amplifiers, shunts, power inverters and battery management
- Proprietary processing technique produces low resistance values (5 m Ω to 500 m Ω)
- Solid metal manganese-copper and nickelchromium-aluminum alloy resistive element with low TCR (< 20 ppm/°C)
- Very low inductance 0.5 nH to 5 nH
- Excellent frequency response to 50 MHz
- Low thermal EMF (< 3 μV/°C)
- AEC-Q200 qualified (1)
- PATENT(S): <u>www.vishay.com/patents</u>
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>


Note

⁽¹⁾ Flame retardance test may not be applicable for all resistance values

STANDARD ELECTRICAL SPECIFICATIONS						
GLOBAL MODEL	SIZE	POWER RATING ⁽¹⁾ W	TOLERANCE %	RESISTANCE VALUE RANGE Ω	WEIGHT (typical) g/1000 pieces	
WFMA2010	2010	2.0 at 110 °C	± 1.0	0.005 to 0.0329	32	
WFMB2010	2010	2.0 at 110 °C	± 1.0	0.033 to 0.500	32	
WFMA2512	2512	3.0 at 95 °C	± 1.0	0.010 to 0.0329	41	
WFMB2512	2512	3.0 at 95 °C	± 1.0	0.033 to 0.500	41	

Note

⁽¹⁾ Terminal temperature



Note

- ⁽¹⁾ Resistance values available according to WSL decade values (<u>www.vishay.com/doc?30117</u>)
- (2) Packaging code: EB (lead (Pb)-free) is a non-standard packaging code designating 1000 piece reels. This non-standard packaging code is identical to our standard EA (lead (Pb)-free), except that it has a package quantity of 1000 pieces

PATENT(S): <u>www.vishay.com/patents</u> This Vishay product is protected by one or more United States and international patents.

Revision: 15-Mar-2019

1

Document Number: 30387

For technical questions, contact: <u>ww2bresistors@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



Vishay Dale

TECHNICAL SPECIFICATIONS						
DADAMETER	UNIT	MODEL	RESISTOR CHARACTERISTICS			
PARAMETER			2010	2512		
Temperature coefficient (20 °C to 60 °C) (element only) ⁽¹⁾	ppm/°C	All	< 20			
Operating temperature range	°C	All	-65 to +170			
Maximum working voltage (3)	V	All	(P x R) ^{1/2}			
Maximum terminal temperature	°C	All	110 95			
Temperature coefficient (-55 °C to +150 °C)	ppm/°C	WFMA	± 110	± 110		
(including terminals) ⁽²⁾		WFMB	± 50	± 50		
Temperature coefficient (20 °C to 60 °C)	ppm/°C	WFMA	$\begin{array}{l} \pm 50 \leq 10 \mbox{ m}\Omega \\ \pm 30 > 10 \mbox{ m}\Omega \end{array}$	± 40		
(including terminals) ⁽²⁾		WFMB	± 20	± 20		


Notes


⁽¹⁾ Element TCR - only applies to the alloy used for the resistor element

⁽²⁾ Component TCR - total TCR that includes the TCR effects of the resistor element and the copper terminal

⁽³⁾ Maximum working voltage - the WFM is not voltage sensitive, but is limited by power / energy dissipation and is also not ESD sensitive

DIMENSIONS






-Typical sensing traces

CASE	RESISTANCE RANGE	DIMENSIONS in inches (millimeters)					SOLDER PAD DIMENSIONS in inches (millimeters)		
SIZE	(m Ω)	L	w	н	T1	T2	а	b	I
2010	5 to 500	0.200 ± 0.008 (5.08 ± 0.20)	0.100 ± 0.008 (2.54 ± 0.20)	0.020 ± 0.006 (0.50 ± 0.15)	0.028 ± 0.008 (0.70 ± 0.20)	0.016 ± 0.006 (0.40 ± 0.15)	0.049 (1.25)	0.118 (3.00)	0.138 (3.50)
2512	10 to 500	0.250 ± 0.012 (6.35 ± .30)	0.125 ± 0.008 (3.18 ± .20)	0.020 ± 0.006 (0.50 ± 0.15)	0.035 ± 0.008 (0.90 ± 0.20)	0.020 ± 0.008 (0.50 ± 0.20)	0.061 (1.55)	0.142 (3.60)	0.173 (4.40)

PRODUCT	RESISTANCE RANGE (Ω)	THERMAL RESISTANCE (°C/W)	ALLOY
WFMA2010	0.005 to 0.0329	< 30	Mn-Cu
WFMB2010	0.033 to 0.5	< 55	Ni-Cr
WFMA2512	0.01 to 0.0329	< 25	Mn-Cu
WFMB2512	0.033 to 0.5	< 40	Ni-Cr

VISHAY. www.vishay.com

DERATING



PERFORMANCE				
TEST	CONDITIONS OF TEST	TEST LIMITS		
Thermal shock	-55 °C to +150 °C, 2000 cycles, 15 min at each extreme	± 0.5 %		
Low temperature storage	-65 °C for 24 h	± 0.1 %		
High temperature exposure	2000 h at +170 °C	± 1.0 %		
Bias humidity	+85 °C, 85 % RH, 10 % power, 1000 h	± 0.5 %		
Mechanical shock	100 <i>g</i> 's for 6 ms, 5 pulses	± 0.2 %		
Vibration	Frequency varied 10 Hz to 2000 Hz in 1 min, 3 directions, 12 h	± 0.2 %		
Load life	2000 h at maximum terminal temperature at rated power	± 0.7 %		
Resistance to solder heat	+260 °C solder, 10 s to 12 s dwell, 25 mm/s emergence	± 0.3 %		
Moisture resistance	MIL-STD-202, method 106, 0 % power, 7b not required	± 0.3 %		

PACKAGING ⁽¹⁾						
MODEL	REEL					
	TAPE WIDTH	DIAMETER	PIECES/REEL	CODE		
WFMA2010	12 mm/embossed plastic	178 mm/7"	4000	EA		
WFMB2010	12 mm/embossed plastic	178 mm/7"	4000	EA		
WFMA2512	12 mm/embossed plastic	178 mm/7"	2000	EA		
WFMB2512	12 mm/embossed plastic	178 mm/7"	2000	EA		

Notes

• Embossed carrier tape per EIA-481

⁽¹⁾ Additional packaging details at <u>www.vishay.com/doc?20051</u>



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.