

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form	: Mixture
Trade name	: PEL Peststop Wasp&FlyingIK
Type of product	: Aerosol
Vaporizer	: Aerosol
Product group	: Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Intended for general public	
Main use category	: Consumer use
Use of the substance/mixture	: Insecticide

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

Denka International B.V.
 Gildeweg 37
 3771 NB BARNEVELD - NEDERLAND
 T +31.342.455455 - F +31.342.490587
denka.info@pelsis.com - www.denka.nl

1.4. Emergency telephone number

No additional information available

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Aerosol, Category 1	H222;H229
Hazardous to the aquatic environment — Chronic Hazard, Category 3	H412
Full text of H statements : see section 16	


Adverse physicochemical, human health and environmental effects

No additional information available

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP)



Signal word (CLP)	: Danger
Hazard statements (CLP)	: H222 - Extremely flammable aerosol. H229 - Pressurised container: May burst if heated. H410 - Very toxic to aquatic life with long lasting effects.
Precautionary statements (CLP)	: P102 - Keep out of reach of children. P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P251 - Do not pierce or burn, even after use. P273 - Avoid release to the environment. P410+P412 - Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F. P501 - Dispose of contents/container to hazardous or special waste collection point.
Security closing plug for children	: Not applicable
Tactile warning	: Not applicable

PEL Peststop Wasp&FlyingIK

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

2.3. Other hazards

No additional information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
propane	(CAS-No.) 74-98-6 (EC-No.) 200-827-9 (EC Index-No.) 601-003-00-5 (REACH-no) 01-2119486944-21	3 - 15	Flam. Gas 1, H220 Press. Gas (Comp.), H280
butane	(CAS-No.) 106-97-8 (EC-No.) 203-448-7 (EC Index-No.) 601-004-00-0 (REACH-no) 01-2119474691-32	3 - 15	Flam. Gas 1, H220 Press. Gas
isobutane	(CAS-No.) 75-28-5 (EC-No.) 200-857-2 (EC Index-No.) 601-004-00-0 (REACH-no) 01-2119485395-27	3 - 15	Flam. Gas 1, H220 Press. Gas (Comp.), H280
Hydrocarbons C12-C16 isoalkanes <2% aromatics	(CAS-No.) 64742-47-8 (EC-No.) 927-676-8 (REACH-no) 01-2119456377-30	6.371741292	Asp. Tox. 1, H304
Hydrocarbons, C11-C13, isoalkanes, < 2% aromatics	(CAS-No.) 90622-58-5 (EC-No.) 920-901-0 (REACH-no) 01-2119456810-40	2.123913764	Asp. Tox. 1, H304
1,R-trans Phenothrin	(CAS-No.) 188023-86-1 (EC-No.) 247-404-5	0.164627736	Aquatic Chronic 1, H410
Neo-Pynamin Forte	(CAS-No.) 1166-46-7 (EC-No.) 214-619-0	0.157755976	Not classified

Full text of H-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures after inhalation	: If breathing is difficult, remove victim to fresh air and keep at rest in a position comfortable for breathing. Get medical advice/attention if you feel unwell.
First-aid measures after skin contact	: Remove contaminated clothing and wash skin thoroughly with soap and water. If skin irritation or rash occurs: Get medical advice/attention.
First-aid measures after eye contact	: Rinse immediately with plenty of water for 15 minutes. Seek medical advice if irritation develops.

4.2. Most important symptoms and effects, both acute and delayed

No additional information available

4.3. Indication of any immediate medical attention and special treatment needed

Treatment is symptomatic and supportive. No specific antidote known.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	: Water spray. Foam. Dry powder. Carbon dioxide (CO2).
Unsuitable extinguishing media	: Heavy water stream.

5.2. Special hazards arising from the substance or mixture

Explosion hazard	: The heating of the product in closed container may cause an internal pressure growth, with fire and explosion risk.
Hazardous decomposition products in case of fire	: On heating/burning: release of harmful gases/vapours e.g.: carbon monoxide - carbon dioxide.

5.3. Advice for firefighters

Protection during firefighting	: Do not enter fire area without proper protective equipment, including respiratory protection.
--------------------------------	---

PEL Peststop Wasp&FlyingIK

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

General measures : Do not get in eyes, on skin, or on clothing. Remove any possible cause of fire. Gloves are recommended.

6.1.1. For non-emergency personnel

Protective equipment : Concerning personal protective equipment to use, see item 8.

6.1.2. For emergency responders

Protective equipment : Concerning personal protective equipment to use, see item 8.

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Contaminated surfaces: clean (treat) with an excess of water.

6.4. Reference to other sections

No additional information available

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling : Avoid contact with skin, eyes and clothes. Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50 °C. Do not pierce or burn, even after use.

Hygiene measures : Do not eat, drink or smoke when using this product. Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F. Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Store in dry, cool, well-ventilated area.

7.3. Specific end use(s)

No additional information available

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

No additional information available

8.2. Exposure controls

Materials for protective clothing:

No special clothing/skin protection equipment is recommended under normal conditions of use

Hand protection:

In case of repeated or prolonged contact wear gloves

Eye protection:

Not required for normal conditions of use

Respiratory protection:

Do not breathe spray

Environmental exposure controls:

Avoid release to the environment.

Other information:

Do not eat, drink or smoke when using this product. Wash hands after use.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state : Aerosol.
Colour : No data available
Odour : characteristic.
Odour threshold : No data available
pH : No data available

PEL Peststop Wasp&FlyingIK

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: No data available
Freezing point	: No data available
Boiling point	: No data available
Flash point	: No data available
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Flammability (solid, gas)	: No data available
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: No data available
Solubility	: No data available
Log Pow	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: No data available
Oxidising properties	: No oxidising properties.
Explosive limits	: No data available

9.2. Other information

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

No additional information available

10.2. Chemical stability

No additional information available

10.3. Possibility of hazardous reactions

No additional information available

10.4. Conditions to avoid

Do not expose to temperatures exceeding 50 °C/ 122 °F. Keep away from heat/open flames/hot surfaces- No smoking.

10.5. Incompatible materials

Strong acids. Strong bases. Strong oxidizing agents.

10.6. Hazardous decomposition products

On burning: release of carbon monoxide - carbon dioxide.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity (oral)	: Not classified
Acute toxicity (dermal)	: Not classified
Acute toxicity (inhalation)	: Not classified
Additional information	: Chronic toxicity: Not carcinogenic, mutagenic Not, Not teratogenic

PEL Peststop Wasp&FlyingIK

LD50 oral rat	> 2000 mg/kg
---------------	--------------

Skin corrosion/irritation	: Not classified
Serious eye damage/irritation	: Not classified
Respiratory or skin sensitisation	: Not classified
Germ cell mutagenicity	: Not classified
Carcinogenicity	: Not classified
Reproductive toxicity	: Not classified

STOT-single exposure	: Not classified
STOT-repeated exposure	: Not classified
Aspiration hazard	: Not classified

PEL Peststop Wasp&FlyingIK

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

PEL Peststop Wasp&FlyingIK

Vaporizer

Aerosol

SECTION 12: Ecological information

12.1. Toxicity

Ecology - general : Toxic to fauna.
Acute aquatic toxicity : Not classified
Chronic aquatic toxicity : Harmful to aquatic life with long lasting effects.

12.2. Persistence and degradability

PEL Peststop Wasp&FlyingIK

Persistence and degradability

Biodegradable.

12.3. Bioaccumulative potential

No additional information available

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

No additional information available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product/Packaging disposal recommendations : Dispose of this material and its container to hazardous or special waste collection point.

SECTION 14: Transport information

In accordance with ADR / RID / IMDG / IATA / ADN

ADR	IMDG	IATA
14.1. UN number		
1950	1950	1950
14.2. UN proper shipping name		
AEROSOLS (Propane, Butane, 1,R-Transphenothrin and Tetramethrin)	AEROSOLS (Propane, Butane, 1,R-Transphenothrin and Tetramethrin)	Aerosols, flammable (Propane, Butane, 1,R-Transphenothrin and Tetramethrin)
Transport document description		
UN 1950 AEROSOLS (Propane, Butane, 1,R-Transphenothrin and Tetramethrin), 2.1, (D), ENVIRONMENTALLY HAZARDOUS	UN 1950 AEROSOLS (Propane, Butane, 1,R-Transphenothrin and Tetramethrin), 2.1, MARINE POLLUTANT/ENVIRONMENTALLY HAZARDOUS	UN 1950 Aerosols, flammable (Propane, Butane, 1,R-Transphenothrin and Tetramethrin), 2.1, ENVIRONMENTALLY HAZARDOUS
14.3. Transport hazard class(es)		
2.1	2.1	2.1
 	 	 
14.4. Packing group		
Not applicable	Not applicable	Not applicable
14.5. Environmental hazards		
Dangerous for the environment : Yes	Dangerous for the environment : Yes Marine pollutant : Yes	Dangerous for the environment : Yes
No supplementary information available		

14.6. Special precautions for user

- Overland transport

Classification code (ADR) : 5F
Special provisions (ADR) : 190, 327, 344, 625
Limited quantities (ADR) : 11
Excepted quantities (ADR) : E0

PEL Peststop Wasp&FlyingIK

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Packing instructions (ADR)	: P207, LP02
Special packing provisions (ADR)	: PP87, RR6, L2
Mixed packing provisions (ADR)	: MP9
Transport category (ADR)	: 2
Special provisions for carriage - Packages (ADR)	: V14
Special provisions for carriage - Loading, unloading and handling (ADR)	: CV9, CV12
Special provisions for carriage - Operation (ADR)	: S2
Tunnel restriction code (ADR)	: D

- Transport by sea

Stowage and handling (IMDG)	: SW1, SW22
Segregation (IMDG)	: SG69

- Air transport

No data available

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No additional information available

SECTION 16: Other information

Full text of H- and EUH-statements:

Aquatic Chronic 1	Hazardous to the aquatic environment — Chronic Hazard, Category 1
Asp. Tox. 1	Aspiration hazard, Category 1
Flam. Gas 1	Flammable gases, Category 1
Press. Gas	Gases under pressure
Press. Gas (Comp.)	Gases under pressure : Compressed gas
H220	Extremely flammable gas.
H222	Extremely flammable aerosol.
H229	Pressurised container: May burst if heated.
H280	Contains gas under pressure; may explode if heated.
H304	May be fatal if swallowed and enters airways.
H410	Very toxic to aquatic life with long lasting effects.
H412	Harmful to aquatic life with long lasting effects.

SDS EU (REACH Annex II)

DISCLAIMER OF LIABILITY The information in this SDS was obtained from sources which we believe are reliable. However, the information is provided without any warranty, express or implied, regarding its correctness. The conditions or methods of handling, storage, use or disposal of the product are beyond our control and may be beyond our knowledge. For this and other reasons, we do not assume responsibility and expressly disclaim liability for loss, damage or expense arising out of or in any way connected with the handling, storage, use or disposal of the product. This SDS was prepared and is to be used only for this product. If the product is used as a component in another product, this SDS information may not be applicable