

20mm Bi-Metal Holesaw

| | |
|-------------------|----------------------------|
| Code | BS05 |
| Diameter | 20mm (25/32") |
| Cutting Depth | 35mm |
| Cutting Edge | HSS M3 |
| Tooth Pitch | 4 / 6 tpi Variable Pitch |
| Mount | 3/8"-20 UNF |
| Use With Arbor | Small Arbor - BA03 or BA04 |
| Packaging | Cardboard Box |
| Pack Qty (Weight) | 1 (38g) |
| Barcode | 5039197009591 |



Description

Heavy Duty Holesaw for Industrial Use
HSS M3 Bi-Metal Cutting Edge provides Long Life
4/6tpi Variable Pitch Teeth enable Fast, Easy Cutting

Recommended Operating Speeds

Mild Steel - **445rpm** Stainless - **220rpm** Cast Iron - **295rpm**
Brass - **590rpm** Alu - **675rpm**
Wood & Plastic - **3000rpm**

Always use Cutting oil / spray when cutting metals

Applications

For cutting holes in Cast Iron, Stainless steel, steel, non-ferrous metals, wood and plastic.
Ideal for electrical, plumbing and production work

Suitable For

For use with all makes of mains powered and cordless rotary drills.