

OT25F3



OT25F3 SWITCH-DISCONNECTOR



General Information

Extended Product Type	OT25F3
Product ID	1SCA104857R1001
EAN	6417019390000
Catalog Description	OT25F3 SWITCH-DISCONNECTOR
Long Description	3-pole, front operated, base mounted, DIN-rail mountable switch-diconnector / non-fusible disconnect switch with protected clamp terminals, handle and shaft are not included

Ordering

Minimum Order Quantity	10 piece
Customs Tariff Number	85365080

Popular Downloads

Data Sheet, Technical Information	1SCC301020C0201
Instructions and Manuals	1SCC301052M0006
Mechanical Drawings	1SCC301434F0001 1SCC301433F0001 OT16-40F3.stp OT16-40F3.igs

Dimensions

Product Net Width	35 mm
Product Net Height	68 mm
Product Net Depth / Length	56 mm
Product Net Weight	0.09 kg

Technical

Rated Operational Current AC-21A (I_e)	(380 ... 415 V) 25 A (500 V) 25 A (690 V) 25 A
Rated Operational Current AC-22A (I_e)	(380 ... 415 V) 25 A (500 V) 25 A (690 V) 25 A
Rated Operational Current AC-23A (I_e)	(380 ... 415 V) 20 A (500 V) 20 A (690 V) 11 A

Rated Operational Power AC-23A (P_e)	(220 ... 240 V) 4 kW (400 ... 415 V) 9 kW (500 V) 9 kW (690 V) 9 kW
Conventional Free-air Thermal Current (I_{th})	q = 40 °C 32 A
Conventional Thermal Current (I_{the})	Fully Enclosed 32 A
Rated Impulse Withstand Voltage (U_{imp})	8 kV
Rated Insulation Voltage (U_i)	acc. to IEC/EN 60664-1 750 V
Rated Operational Voltage	Main Circuit 750 V
Rated Short-Circuit Making Capacity (I_{cm})	(690 V) 0.71 kA
Rated Short-time Withstand Current (I_{cw})	for 1 s 0.5 kA
Power Loss	at Rated Operating Conditions per Pole 0.6 W
Pollution Degree	3
Handle Type	Knob Handle and shaft not included
Switches Operating Mechanism	Mechanism on Top of the Switch
Distance Between Phases	Standard
Position of Line Terminals	Top In - Bottom Out Bottom In - Top Out
Operating Mode	Front operated
Standards	IEC 60947-3 / UL 508 / CSA C22.2 No. 14
Special Functions	No
Mounting Type	Base mounting
Number of Poles	3
Cable Cross-Section	0.75...10 mm ²
Terminal Type	Screw Terminals
Tightening Torque	acc. IEC 60947-1 0.8 N·m

Technical UL/CSA

Maximum Operating Voltage UL/CSA	600 V
Horsepower Rating UL/CSA	(110 ... 120 V AC) Single Phase 1.5 Hp (240 V AC) Single Phase 3 Hp (440 ... 480 V AC) Single Phase 7.5 Hp (550 ... 600 V AC) Single Phase 10 Hp (220 ... 240 V AC) Three Phase 7.5 Hp (440 ... 480 V AC) Three Phase 15 Hp (550 ... 600 V AC) Three Phase 20 Hp
Ampere Rating UL/CSA	30 A
Tightening Torque UL/CSA	7 in·lb

Environmental

RoHS Status	Following EU Directive 2011/65/EU
Environmental Information	1SCC301183D0201

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	1SCC301166D2703
Environmental Information	1SCC301183D0201
Instructions and Manuals	1SCC301052M0006
RoHS Information	1SCC301183D0202

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	67 mm
Package Level 1 Depth / Length	79 mm
Package Level 1 Height	46 mm
Package Level 1 Gross Weight	0.1 kg
Package Level 1 EAN	6417019390000

Classifications

E-nummer	3170938
Object Classification Code	Q
ETIM 5	EC000216 - Switch disconnecter
ETIM 6	EC000216 - Switch disconnecter
ETIM 7	EC000216 - Switch disconnecter
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Switches → Switch Disconnectors

