

## 32mm Bi-Metal Holesaw

Code	BS13
Diameter	32mm (1 1/4")
Cutting Depth	35mm
Cutting Edge	HSS M3
Tooth Pitch	4 / 6 tpi Variable Pitch
Mount	7/16" - 5/8" UNF
Use With Arbor	Large Arbor - BA02 or BA05
Packaging	Cardboard Box
Pack Qty (Weight)	1 (86g)
Barcode	5039197009676



## Description

Heavy Duty Holesaw for Industrial Use

HSS M3 Bi-Metal Cutting Edge provides Long Life

4/6tpi Variable Pitch Teeth enable Fast, Easy Cutting

## Recommended Operating Speeds

Mild Steel - **275rpm**

Stainless - **140rpm**

Cast Iron - **180rpm**

Brass - **360rpm**

Alu - **410rpm**

Wood & Plastic - **2400rpm**

**Always use Cutting oil / spray when cutting metals**

## Applications

For cutting holes in Cast Iron, Stainless steel, steel, non-ferrous metals, wood and plastic.

Ideal for electrical, plumbing and production work

## Suitable For

For use with all makes of mains powered and cordless rotary drills.