




SCP Part Number: RG6/UQ-CCS-BK-5

REV.A

Cross Section



Description

HDTV CABLE, RG6/U QUAD SHIELD 18 AWG CCS, 75OHMS, 3.0GHz,

Marking

STRUCTURED CABLE PRODUCTS Exxxxx (UL) OR C(UL) CM 18 AWG CCS 75C MM/YY -- P/N: RG6/UQ-CCS -- RG6/U QUAD SHIELD SWEEP TESTED TO 3.0 GHz HDTV, 60%/40% AL BRAID CE EU RoHS EC ZONE/DEVICE A B C D E 0 1 2 3 4 5 6 7 8 9 xxxxFEET

Construction

Center Conductor:	Copper Clad Steel
Size	18AWG
Dia.(in/mm)	0.0403/1.02
Insulate	Skin Foam PE
Nom. Thickness(in/mm)	0.070/1.78
Insulation Dia.(in/mm)	0.0180/4.57
The First Shield	Bonded Aluminum Foil
Coverage Area (%)	100
The First Braid Shield	Aluminum Wire
Coverage Area(%)	60
The second Shield	Aluminum Foil
Coverage Area(%)	100
The Second Braid Shield	Aluminum Wire
Coverage Area(%)	40
Jacket	Black FR-PVC
Nom. Thickness(in/mm)	0.030/0.76
Min. Thickness(in/mm)	0.024/0.61
Cable Dia.(in/mm)	0.297/7.54
Packing	Pull Box
Length(ft/m)	500/152.5
Gross Weight(lbs/kg)	18.74/8.5

Performance

Electrical Characteristics:[@68°F.(20°C.)]

Frequency (MHz)	Attenuation (dB/100ft)	Attenuation (dB/100m)
5	0.79	2.57
10	0.82	2.66
50	1.47	4.79
100	2.05	6.72
200	2.84	9.28
400	4.06	13.28
700	5.60	18.36
900	6.24	20.43
1000	6.60	21.61
1200	7.50	24.59
1450	8.04	26.36
1800	8.84	28.98
2200	9.77	32.03
2500	11.13	36.47
2750	11.58	37.94
3000	12.06	39.54

Dielectric Strength (kV/min)		1
Impedance (ohms)		75±3.0
SRL (dB)	5~1000MHz	>=20
	1001~3000MHz	>=15
Capacitance (pF/ft)		16.2
Conductor DCR@ 20°C (ohms/kft)		31
DC Loop Resistance@ 20°C (ohms/kft)		38.52
Velocity Of Propagation (%)		85

Mechanical Characteristics:

Test Object:		Jacket
Test Material		
Before	Tensile strength (psi)	2000
Aging	Elongation (%)	200
Aging Condition	(°C_hrs)	100_168
After	Tensile strength (%)	>=85%unaged
Aging	Elongation (%)	>=50%unaged
Cold Bend	(-20±2°C/4hrs)	No Crack
Jacket Longitudinal Shrinkage	(%)	>=5
Center Conductor break Strength	(lbs)	85
Operating Temperature Range	(°C)	-20~75

Standards

UL, CE, RoHS