

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0430201600

Status:

Active

Overview:

Micro-Fit 3.0 Connector System Product Family

Description:

Micro-Fit 3.0 Plug Housing, Dual Row, 16 Circuits, UL 94V-0, Panel Mount Ears, Low-Halogen, Black

Documents:

- Drawing (PDF)

3D Model

Product Specification PS-43045 (PDF)

Product Specification PS-43045-001 (PDF)

Product Specification TS-43045-001-001 (PDF)
- Product Specification TS-46235-001-001 (PDF)

Packaging Specification PK-43020-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Product Literature (PDF)

Agency Certification

CSA

UL

LR19980

E29179

General

Product Family

Series

Application

Overview

Product Literature Order No

Product Name

UPC

Crimp Housings

43020

Power, Wire-to-Wire

Micro-Fit 3.0 Connector System Product Family

987650-5984

Micro-Fit 3.0

800754383684

Physical

Circuits (maximum)

Color - Resin

Flammability

Gender

Glow-Wire Capable

Keying to Mating Part

Lock to Mating Part

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Stackable

Temperature Range - Operating

16

Black

94V-0

Plug

No

None

Yes

Nylon

1.826/g

2

Bag

Yes

3.00mm

3.00mm

Yes

No

-40° to +105°C

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Reference - Drawing Numbers

Packaging Specification

Product Specification

Sales Drawing

PK-43020-001-001

PS-43045, PS-43045-001, TS-43045-001-001, TS-46235-001-001

SDA-43020-****



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

43020 Series

Mates With

Micro-Fit 3.0 Receptacle Housings 43025

Use With

Micro-Fit 3.0 Male Crimp Terminals 43031

This document was generated on 10/26/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION