

NO: FJOS1409117

CUSTOMER PN \_\_\_\_\_

承 认 书
SPECIFICATION FOR APPROVAL

MEGA PART NO MJSW1200500DU

MEGA MODEL NO FJ-SW1200500DU(716X UL)

DESCRIPTION 12V 500mA

DATE 2014-10-08



MANUFACTURE			CUSTOMER APPROVAL	
DESIGN	CHECKED	APPROVED		

**MEGA Electronics, Inc.**

4B Jules Lane

New Brunswick, NJ 08901

Tel: 732-249-2656 Fax: 732-249-7442

Email: [sales@megaelectronics.com](mailto:sales@megaelectronics.com) Website: [www.megaelectronics.com](http://www.megaelectronics.com)

**SPECIFICATION FOR APPROVAL**

DESCRIPTION 12V 500mA

DATE 2014-10-08

**Revision: 01**



**TABLE OF CONTENTS**  
目录

- 1 概述/SCOPE**
- 2 输入特性/INPUT CHARACTERISTICS**
- 3 输出特性/OUTPUT CHARACTERISTICS**
- 4 保护功能/ PROTECTION FUNCTION**
- 5 环境要求/ENVIRONMENTAL REQUIREMENTS**
- 6 机械特性 MECHANICAL CHARACTERISTICS**
- 7 安全标准 /SAFETY**
- 8.EMC 标准/ EMC STANDARD**
- 9 体积/VOLUME**
- 10 重量/WEIGHT**
- 11 外观图/OUTLOOK DRAWING**
- 12 铭牌/LABEL**
- 13 包装图示/PACKING**
- 14 样品测试报告 / SAMPLES TEST REPORT**

## 1 概述 /SCOPE

本规格书适合于 [MJSW1200500DU-1809](#) 认证型号的开关电源。

The purpose of the document is to specify the functional requirements of [MJSW1200500DU-1809](#) switching power supply.

## 2. 输入特性/ INPUT CHARACTERISTICS:

### 2.1 输入电压/ Input Voltage

额定输入电压/ Rated Input Voltage: 100-240Vac

可变输入电压/Variable input voltage : 90V—264Vac

### 2.2 输入电流/Input Current:

当输入额定电压 带额定负载时, 最大的输入交流电流 [0.25A](#)  
[0.25A](#) max when input rated voltage and output rated load.

### 2.3 输入频率/ Input Frequency

额定频率/Rate Frequency:50/60Hz

调整频率/ Variation Frequency: 47-63Hz

### 2.4 浪涌电流/In-rush Current:

当输出为额定负载, 环境温度为 25℃,输入 240Vac 冷启动时的最大浪涌电流为 60A。  
60 A mps Max Cold start at 240Vac input ,with rated load and 25℃ ambient.

### 2.5 AC 漏电流/ AC leakage Current:

当输入电压 240Vac 时, 最大的漏电流为 0.25mA  
0.25mA Max .At 240Vac input

## 3. 输出特性/OUTPUT CHARACTERISTICS:

### 3.1 额定输出功率/Rated Output Power [6W](#)

### 3.2 负载特性/调整率 (Combined Load/line Regulation)

电压 Voltage	最小负载 Min. Load	最大负载 Max Load	负载调整 Load Regulation	空载输出电压 Unload output voltage
<a href="#">+12V</a>	<a href="#">0A</a>	<a href="#">0.5A</a>	<a href="#">11.4V-12.6V</a>	<a href="#">12.0V-12.6V</a>

### 3.3 效率/Efficiency:

V 级平均工作效率  $\geq 73.42\%$

当输入 115VAC 时, 平均效率  $\geq 73.42\%$ 。是输出额定负载的 25%,50%,75%,100%4 种情况下平均效率,

115VAC input, the average efficiency  $\geq 73.42\%$ 。 output rated load is 25%,50%,75%,100% 4 situations of average efficiency

当输入 230VAC 时, 平均效率  $\geq 73.42\%$ 。是输出额定负载的 25%,50%,75%,100%4 种情况下平均效率,

230VAC input, the average efficiency  $\geq 73.42\%$ 。 output rated load is 25%,50%,75%,100% 4 situations of average efficiency

### 3.4 空载待机功率/Unload standby Power: 0.3W Max

### 3.5 纹波和噪音/ Ripple And Noise

纹波与噪声: 测量时示波器选用 20MHz 带宽限制,输出端要并联一颗 0.1uF 的陶瓷电容和一颗 47uF 的电解电容。(在额定输入及输出的条件下检测)

Ripple & Noise: Measurement is done by 20MHz bandwidth oscilloscope and the output paralleled a 0.1uF ceramic capacitor and a 47uF electrolysis capacitor. (test under the condition of rated input and rated output)

电压	电流	最大纹波最大噪音
Voltage	current	Ripple And Noise(Max)
<u>+12V</u>	<u>500mA</u>	120m Vp-p

### 3.6 启动延迟时间/ Turn On Delay Time:

当输入 100Vac 和输出最大负载时, 最大启动时间为 2S  
2 second Max .At 100Vac input and output Max. Load

### 3.7 上升时间/ Rise Time:

当输入 100Vac 和输出最大负载时最大时间为 100ms  
100ms Max. At 100Vac input and output Max. Load

### 3.8 保持时间/Hold Up Time :

当输入 100Vac 和输出最大负载时, 最小保持时间为 5ms  
5ms Min.at100Vac input and output Max .Load.

### 3.9 过充/ Overshoot:

在电源开启或关闭的时候, 最大 10%  
10% Max. When power supply on or turn off.

## 4. 保护功能/ PROTECTION FUNCTION:

### 4.1 短路电路保护/Short circuit protection:

电源供给器在短路解除后能正常恢复工作。

The Power Supply will be auto recovered when short circuit faults remove.

#### 4.2 过流保护/ Over current Protection:

过流故障排除后，电源将自动回复正常工作。

The power supply will be auto recovered when over current faults remove.

#### 4.3 过压保护/ Over Voltage Protection:

当输出电压超过额定电压的 120%-150%时，电源将保护，故障排除后能恢复正常工作。

The power supply will auto recovered when the voltage over 120%-150% rate voltage.

## 5. 环境要求/ENVIRONMENTAL REQUIREMENTS

### 5.1 工作温度/Operating Temperature

0°C -- +40°C,满载，正常工作。

0°C to +40°C ,Full Load, Normal Operation.

### 5.2 储存温度/Storage temperature

带外壳 :-10°C -- +55°C

With enclosure:-10°C to+55°C

### 5.3 工作湿度/Relative Humidity:

5%(0°C)~90%(40°C) ,72 小时，满载，正常工作。

5%(0°C)~90%(40°C) 72h Full Load , Normal operating.

### 5.4 振动/ Vibration:

#### 5.4.1 测试标准：国际电工电子委员会

Operating: IEC 721-3-3 3M3

5~9Hz,A=1.5mm

加速度 (9~200Hz,Acceleration 5m/s)

#### 5.4.2. 运输 (Transportation) :

IEC 721-3-2 2M2

5~9Hz, A=3.5mm

9~200Hz ,加速度 Acceleration=5 m/s<sup>2</sup>

200~500Hz ,加速度 acceleration=15 m/s<sup>2</sup>

#### 5.4.3. 轴向振动/ Axes,10 cycles per axis :

在测试过程中不能出现永久性损坏。

No permanent damage occur during testing.

在电源开启和关闭后，样机能够恢复到最初条件。

The product has to restore to its original situation after power off/on

## 6. 机械特性/ MECHANICAL CHARACTERISTICS

### 6.1 跌落实验/ Dropping Testing ,

产品从一米高处跌落到木板上无损伤。

The product to be dropped from 1 meter height to a concrete floor no breakage.

## 6.2 摇摆实验/Cable Flexing Testing

DC 引线吊重 200 克， 摇摆角 60 度， 最少能承受 2000 次， 弯曲速度每分 40 次， 不会出现损伤。

The DC cord shall with weight of 200g,it swings at angle 60 deg ,2000cycle  
Time min Bending speed: 40cycle per minute shall to be no breakage to the code

## 7. 安全标准 SAFETY STANDARD ,

7.1 安全:符合标准 EN60950, EN60065, GB8898。

Safety Accord with EN60950, EN60065, GB8898。

7.2 高压/ DIELECTRIC STRENGTH Hi-Pot

初级对次级/ Primary to secondary, 3000Vac/5mA/5s.

7.3 绝缘阻抗/ Insulation resistance:

初级对次级/ Primary to secondary :10M $\Omega$  Min at 500V DC

## 8. EMC 标准/EMC STANDARD


EMC---EN55022/EN55024/GB9254-1998 (CISPR 22)

## 9. 体积/VOLUME: L×W×H


长 60.7mm × 宽 26.5mm × 高 38.5mm

## 10. 重量/ Weight: 60g ±5g


**11 外观图/OUTLOOK DRAWING (公差/Common difference: +/-20mm)**







比例/Scale: 1:1




比例/Scale: 3:1

备注/Note:

1. 材料/Material : PVC 环保/ ROHS.
2. 印刷/Printing : 白底黑字/ White ground black character
3. 尺寸/Size:(W)19.8+/-0.2mm(H)13.2+/-0.2mm
4. 厚度/Thickness:0.15mm

### 13 包装图示 PACKING

PE-LD 04



备注/NOTE:

1. 每箱装 100 个，分 5 层，材质 **K=K**  
100PCS Per carton, Divided into 5 floor.  
Material **K=K**
2. PE 袋尺寸：130X170MM 带环保标志。  
PE bag size: 130X170MM , With the  
environmental protection symbol.



14 样品测试报告SAMPLES TEST REPORT											
客户 Customer		F13003ME02		客户编号 Customer No		FJOS1409117		室温 Ambient temp		25°C	
产品型号 Model NO		716X		产品编号 Part No				日期 Date		10月8日	
输入电压/频率 Input volt/Freq		100-240Vac 50/60HZ		输出电压/电流 Output volt/Amp		12V 0.5A					
测试内容 Test content			1#样机/Sample NO:				2#样机/Sample NO:				判定 judge PASS or NG
NO	测试项目 Test Item	测试标准 spec	115Vac	230Vac	115Vac	230Vac					
1	空载电压 Unload voltage	12.0-12.6V								Pass	
2	空载纹波与噪声 UnLoad ripple&noise	≤120mV P-P								Pass	
3	满载电压 Rated Load output Voltage	11.4-12.6V								Pass	
4	满载纹波&噪声 Rated load ripple&noise	≤120mV P-P								Pass	
5	额定输入电流 Rated input current	≤250mA								Pass	
6	短路保护 Shortcircuit protection	No damage and auto recovered OK/NG	OK	OK	OK	OK	OK	OK	OK	Pass	
7	介电强度测试 Hi-Pot test	AC3.0KV 5S	<5mA	泄漏电流/Leakage current ( mA ) ; 绝缘击穿/insulation breakdown: ■OK □NG						Pass	
8	绝缘阻抗测试 Insulation resistance	DC500V 5S	>10MΩ	绝缘阻抗/insulation resistance ( MΩ ) ; 绝缘击穿/insulation breakdown: ■OK □NG						Pass	
9	输入/Input		输出/Output				能源之星/Energy star				
	电压 Voltage	功率 Pin(W)	负载% Load%	电压 Vout(V)	电流 Iout(A)	功率 Watt(W)	效率 EFF(%)	平均效率 average Eff(%)	能效标准V SPEC	空载功耗 Standby Power(W)	Pass
	115Vac		100%			0.00	#DIV/0!	#DIV/0!	平均效率 AVG EFF ≥73.42% 空载功耗 Standby Power <0.3W		Pass
			75%			0.00	#DIV/0!				
			50%			0.00	#DIV/0!				
			25%			0.00	#DIV/0!				
	230Vac		100%			0.00	#DIV/0!	#DIV/0!			Pass
			75%			0.00	#DIV/0!				
		50%			0.00	#DIV/0!					
		25%			0.00	#DIV/0!					
10	100V/240V输入时满载开关机测试 Turn on/off test when rated load and input 100V/240Vac		10 times	正常开机 Normal turn on : ■OK □NG						Pass	
11	115-240V 满载老化/Rated load burn-in test at 115V-240Vac		≥4 hours	无损坏No damage : ■OK □NG						Pass	
测试/TESTED BY		黄高		核准/CHECKED BY				批准/APPROVAL BY			