

Han Full High Density Module, crimp-F



| | |
|--------------------|---|
| Part number | 09 14 036 3101 |
| Specification | Han Full High Density Module, crimp-F |
| HARTING eCatalogue | https://b2b.harting.com/09140363101 |

Identification

| | |
|----------------|-------------------------------|
| Category | Modules |
| Series | Han-Modular® |
| Type of module | Han® Full High Density module |

Version

| | |
|--------------------|---|
| Termination method | Crimp termination |
| Gender | Female |
| Number of contacts | 36 |
| Details | Please order crimp contacts separately. |

Technical characteristics

| | |
|-------------------------|-------------------------------|
| Conductor cross-section | 0.09 ... 0.52 mm ² |
| Rated current | 4 A |
| Rated voltage | 32 V |
| Rated impulse voltage | 0.8 kV |
| Pollution degree | 3 |
| Insulation resistance | > 10 ¹⁰ Ω |
| Limiting temperature | -40 ... +125 °C |
| Mating cycles | ≥500 |

Material properties

| | |
|-------------------|------------------------|
| Material (insert) | Polycarbonate |
| Colour (insert) | RAL 7032 (pebble grey) |



Pushing Performance

Material properties

| | |
|---|-----|
| Material flammability class acc. to UL 94 | V-0 |
|---|-----|

Specifications and approvals

| | |
|----------------|------------|
| Specifications | EN 60664-1 |
| | IEC 61984 |

Commercial data

| | |
|--------------------------------|---|
| Packaging size | 2 |
| Net weight | 6.2 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| eCl@ss | 27440217 Module for industrial connectors (power/signals) |