

Evaporative Coolers iKOOL

Presenting, a hip new range of air coolers from MasterKool, iKOOL Air Coolers. Sleek and stylish, iKOOL could be a cool addition to your décor. What's more, this modern design consumes bare minimum space and energy. Revved up with many power-packed features, iKOOL is the right choice for a cool summer and now a warm winter. Thanks to the new Heat & Cool iKool-10HOT.

FEATURES



Anion Function



Innovative Fan Blade Design




Remote Controlled



Removable Water Tank



Touch Panel



Heating Element



SPECIFICATIONS

Model	iKOOL-10HOT
EAN Barcode	1310001101002
Air volume	760 m3/hr
Area coverage	10 m2
Power	1443 W
Current	6.85 A
Water tank capacity	9.3 L
Water continuous u	10 - 13 Hours
Water evaporation r	0.7-0.9 L/hr
Fan speed	3 Speeds
Vent size	21.5 x 25 cm
Cooling pad type	5090
No. of cooling pad	1 Pcs
Cooling pad volume	2673 cm3
Product dimension	28 x 24 x 74 cm
Net weight	5.9 kg
Carton Dimensions	33 x 30 x 79 cm
Gross weight	7.3 kg
Operating weight	15.2 kg
Water level sensor	Yes
Remote control	Yes
Timer	No
Mosquito repellant	No
Humidity control	No
Direct water connec	No



**HEAT
COOL**



**also works
on inverter
power**



**delivers fresh,
filtered
cool air**

All ACC product's are guaranteed for 12 months (unless otherwise stated) from the date of original purchase.



airconditioningcentre®

Copyright © 2002 – 2011 Air Conditioning Centre / Martin Industries
Air Conditioning Centre is a registered trademark of Martin Industries Ltd. E&OE. Registered in England & Wales Co. No. 05436428

Martin Industries Ltd

Unit 8
Milton Business Centre
Wick Drive
New Milton
Hampshire
BH25 6RH

United Kingdom

Telephone: 0370 33 44 55 6

Fax: 0870 33 44 55 9

Email: info@airconditioningcentre.com
Website: www.airconditioningcentre.com