

INVERTIBLE VERTICAL DMX FOG MACHINE WITH LED & REMOTE CONTROL - 900W

FOG900-RGB

This fog machine projects the illuminated fog to ceiling and ground.

- 6 DMX channels
- 6 x 3W 3-in-1 RGB LED illuminate the fog
- Vertical upwards or downwards projection
- Manual, DMX or remote-controlled operation
- Reduced heat-up time (3 minutes)
- 433MHz wireless remote control included

**EAN
CODE**

**5420047136381
15-1309**

SPECIFICATIONS TECHNIQUES

Power supply	110-240Vac 50/60Hz
Consumption	
Heating element	900W
Tank capacity	3 liters
Dimensions	330 x 240 x 160mm
Weight	4kg



LOGISTICS VALUES

Packaging height	215 cm
Packaging width	300 cm
Packaging depth	400 cm
Packaging volume	0.026 m ³
Packaging gross weight	4850 kg
Qty per master carton	4
EAN14 code	54200471363814
Customs code	85437090

