

# PC BOARD MOUNTING CONNECTORS

## 720 SERIES (CRIMP TYPE CONNECTORS)

### ■ FEATURES


The 720 series connectors (crimp connector) are designed for a wide range of uses, and come in many shapes, two contact arrangements (one and two rows), and various pin types. The 720 series headers can be mated with 700 and 740 series sockets, and are lockable when a special cover is used. Female contacts are secured in the housing by a unique internal spring structure. High-pressure contacts are also available which prevent accidental disconnection in applications that use only a few contacts.

For W and S type headers, insulation molds can be cut to the necessary size.

### ■ SPECIFICATIONS

Item		Specification
Operating temperature range		-55°C to +85°C
Current rating		DC 3 A
Voltage rating		AC 250 V
Contact resistance		20 mΩ max. (DC 6 V, 0.1 A)
Insulation resistance		1000 MΩ max. (DC 500 V)
Dielectric strength		AC 500 V for 1 minute
Insertion force	Standard contacts	1.05 kg max. (3 pins), 25.2 kg max. (72 pins)
	High-pressure contacts	2.1 kg max. (3 pins), 50.4 kg max. (72 pins)
Withdrawal force	Standard contacts	0.09 kg min. (3 pins), 2.16 kg min. (72 pins)
	High-pressure contacts	0.18 kg min. (3 pins), 4.32 kg min. (72 pins)
Applicable wire		Wire-wrap: AWG #26 to #30 (solid) Crimping: AWG #20 to #32
Applicable PC board (standard)		1.6 mm (0.062 in.)

Note: For thin wire crimping, the crimp height must be adjusted for increased reliability. Please contact us for further information.



### ■ MATERIALS

Item		Materials
Insulating material	Header	Polyester (UL94V-0)
	Socket	PPO (UL94V-1)
	Cover	Nylon 6 (UL94V-2)
Conductor		Copper alloy
Plating	Contact	Gold
	Terminal	Palladium

Note: Tin-plated connectors are also available for 8- to 34-pin types.


### ■ MATERIALS (SMT CONNECTOR)

Item		Materials
Insulating material		66 Nylon (UL94V-0)
Conductor		Copper alloy
Plating	Contact	Gold
	Terminal	Palladium


# 720 Series (Crimp Type Connectors)

## COVER S TYPE (MOLD TYPE)


### ■ DIMENSIONS



### ■ EXPLODED VIEW



### ■ APPLICATION EXAMPLE



### ■ PART NUMBERS AND DIMENSIONS

Number of contacts	Part number	Dimensions: mm (in.)			
		X	Y	Z	Maximum cable outer diameter
16	FCN-720C016/2S	9.0 (0.354)	24.92 (0.981)	24.92 (0.981)	7 (0.272)
20	FCN-720C020/2S	10.0 (0.394)	24.0 (0.944)	30.0 (1.181)	8 (0.314)
26	FCN-720C026/2S	11.0 (0.433)	27.0 (1.063)	37.62 (1.481)	9 (0.354)
34	FCN-720C034/2S	12.0 (0.472)	30.0 (1.181)	47.78 (1.881)	10 (0.433)
50	FCN-720C050/2S	14.0 (0.551)	32.0 (1.260)	68.1 (2.680)	12 (0.472)

### ■ REMARKS

- Mating housing  
FCN-723J □□□ /2  
FCN-723B □□□ /2  
□□□ : Number of contacts
- Mating connector  
700 series headers (with M latch) can be connected.  
Example: FCN-705Q050-AU/M

# 720 Series (Crimp Type Connectors)

## **Fujitsu Components International Headquarter Offices**

### **Japan**

Fujitsu Component Limited  
Gotanda-Chuo Building  
3-5, Higashigotanda 2-chome, Shinagawa-ku  
Tokyo 141, Japan  
Tel: (81-3) 5449-7010  
Fax: (81-3) 5449-2626  
Email: [promothq@ft.ed.fujitsu.com](mailto:promothq@ft.ed.fujitsu.com)  
Web: [www.fcl.fujitsu.com](http://www.fcl.fujitsu.com)

### **North and South America**

Fujitsu Components America, Inc.  
250 E. Caribbean Drive  
Sunnyvale, CA 94089 U.S.A.  
Tel: (1-408) 745-4900  
Fax: (1-408) 745-4970  
Email: [marcom@fcai.fujitsu.com](mailto:marcom@fcai.fujitsu.com)  
Web: [www.fcai.fujitsu.com](http://www.fcai.fujitsu.com)

### **Europe**

Fujitsu Components Europe B.V.  
Diamantlaan 25  
2132 WV Hoofddorp  
Netherlands  
Tel: (31-23) 5560910  
Fax: (31-23) 5560950  
Email: [info.marketing@fceu.fujitsu.com](mailto:info.marketing@fceu.fujitsu.com)  
Web: [www.fceu.fujitsu.com](http://www.fceu.fujitsu.com)

### **Asia Pacific**

Fujitsu Components Asia Ltd.  
102E Pasir Panjang Road  
#04-01 Citilink Warehouse Complex  
Singapore 118529  
Tel: (65) 375-8560  
Fax: (65) 273-3021  
Email: [fcal@fcal.fujitsu.com](mailto:fcal@fcal.fujitsu.com)  
[www.fcal.fujitsu.com](http://www.fcal.fujitsu.com)

© 2001 Fujitsu Components America, Inc. All company and product names are trademarks or registered trademarks of their respective owners. Rev. 09/2001