



VT-8-6 MICROWAVE SENSOR WITH SAMSUNG CHIP

SKU:759



## Technical Information

Ambient Light: 3-2000Lux(Adjustable)

Hold Time: 5S, 30S, 90S, 3min, 30min

Detection Distance: 4M(3M mounting Height)

Detection Motion Speed: 0.6-1.5m/s

Rated Load: 100W

Detection Angle: 150(WALL) 360(CEILING)

Sensor Type: Microwave

LED Chip Type: Microwave Sensor - Samsung Batten

IP Rating: IP20

Dimmable: No

Input Power: AC:220-240V/50Hz

## Features

- ✓ Energy saving Microwave sensor compatible for TpA rated batten fitting
- ✓ Rated load of 300W (incandescent lamp) 100W(Energy saving lamp)
- ✓ Easy to Install

# Packaging

## Unit Details

Gross Weight(GW) Kgs	0.09
Unit CBM	0.000341

## Listing Details

EAN Code 3800157638227

## Master Box Packaging

Master Box Qty (Pcs Per Carton)	100
---------------------------------	-----

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER  
**70**  
COUNTRIES