

VW3A4506

DC choke - 2.2 mH - 19.2 A - for variable speed drive



Main

Product or component type	DC choke
Range compatibility	Altivar 61 Altivar 71
Device application	Reduction of current harmonics
Value of inductance	2.2 mH
[In] rated current	19.2 A
Thermal losses	33 W
Product compatibility	ATV61HU22M3 ATV61HU75N4 ATV71HU22M3 ATV71HU75N4 ATV71PU75N4Z ATV71WU75N4
Electrical connection	Earth circuit terminal, connection capacity: 10 mm ² (AWG 6) Power supply terminal, connection capacity: 4 mm ² (AWG 10)

Complementary

Network number of phases	3 phases
Supply frequency	50...60 Hz
Voltage drop at rated load	6 %
Max current	1.65 x nominal current for 60 s
Tightening torque	Earth circuit : 1.2...1.4 N.m Power supply : 0.5...0.8 N.m
Height	134 mm
Width	96 mm
Depth	120 mm
Product weight	2.5 kg

Environment

IP degree of protection	IP20
relative humidity	0...95 %
ambient air temperature for operation	> 50...60 °C with current derating 2.2 % per °C -10...50 °C without current derating
ambient air temperature for storage	-40...65 °C
operating altitude	<= 1000 m without current derating 1000...3000 m with current derating 1 % per 100 m

Contractual warranty

Warranty period	18 months
-----------------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.