

SlimFix VT SF 2/12 MC NE WS V0

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



Similar to illustration

SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	VT SF 2/12 MC NE WS V0
Order No.	1718480001
Version	SlimFix, Conductor and cable markers, 2.2 - 2.9 mm, 12 x 3.6 mm, white
GTIN (EAN)	4008190349530
Qty.	800 Stück
compatible printer	1324380000

SlimFix VT SF 2/12 MC NE WS V0

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Width	3.6 mm	Width (inches)	0.142 inch
Height	12 mm	Height (inches)	0.472 inch
Depth	3.65 mm	Depth (inches)	0.144 inch
Net weight	0.236 g		

General data

Colour code	white	Material	Polyamide 66
Material colour according to resistance code	9	Operating temperature range	-50...120 °C
Recommended industries	Transportation, Machinery	Size of labelling field	12x3.6 mm
Type of printing	blank	UL 94 flammability rating	V-0
Width	3.6 mm		

Conductor and cable markers

Conductor O.D.	2.2 - 2.9 mm	Conductor O.D., max.	2.9 mm
Conductor O.D., min.	2.2 mm	Conductor cross-section, max.	1.5 mm ²
Conductor cross-section, min.	0.75 mm ²	Halogen	No

Classifications

ETIM 3.0	EC001530	ETIM 4.0	EC001530
ETIM 5.0	EC001530	ETIM 6.0	EC001530
UNSPSC	44-12-17-08	eClass 5.1	27-14-91-03
eClass 6.2	27-40-04-01	eClass 7.1	27-14-91-03
eClass 8.1	27-14-91-03	eClass 9.0	27-40-04-01
eClass 9.1	27-40-04-01		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP
Software	M-Print PRO configuration file

Datenblatt

SlimFix
VT SF 2/12 MC NE WS V0

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

