

Accessories - PTCM-MP-P 0,34-0,75 - 1013780

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimp contact, type of contact: Female connector, connection method: Crimp connection, contact surface: Tin, type of packaging: packed in cardboard

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4055626492568
Weight per Piece (excluding packing)	0.400 g
Custom tariff number	85366990
Country of origin	Germany

Technical data

General

Range of articles	PTCM-MP-P
-------------------	-----------

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 5.1	27260700
eCl@ss 6.0	27260700
eCl@ss 7.0	27440309

Accessories - PTCM-MP-P 0,34-0,75 - 1013780

Classifications

eCl@ss

eCl@ss 8.0	27440204
eCl@ss 9.0	27440204

ETIM

ETIM 5.0	EC000796
ETIM 6.0	EC002638

Accessories

Accessories

Crimping tool

Crimping pliers - CRIMPFOX-P CC 0.75 L - 1064998



Crimping pliers, for COMBICON crimp connectors with cross section: 0.14 ... 0.75 mm². Unlockable pressure lock, precise parallel crimping, front entry, B crimp, incl. 2 positioning aids

Additional products

Printed-circuit board connector - PTCM 0,5/ 2-PL-2,5 WH - 1015464



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, number of positions: 2, pitch: 2.5 mm, connection method: Crimp connection, color: white

Printed-circuit board connector - PTCM 0,5/ 3-PL-2,5 WH - 1015463



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, number of positions: 3, pitch: 2.5 mm, connection method: Crimp connection, color: white

Accessories - PTCM-MP-P 0,34-0,75 - 1013780

Accessories

Printed-circuit board connector - PTCM 0,5/ 4-PL-2,5 WH - 1015462



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, number of positions: 4, pitch: 2.5 mm, connection method: Crimp connection, color: white

Printed-circuit board connector - PTCM 0,5/ 5-PL-2,5 WH - 1015461



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, number of positions: 5, pitch: 2.5 mm, connection method: Crimp connection, color: white

Printed-circuit board connector - PTCM 0,5/ 6-PL-2,5 WH - 1015460



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, number of positions: 6, pitch: 2.5 mm, connection method: Crimp connection, color: white

Printed-circuit board connector - PTCM 0,5/ 7-PL-2,5 WH - 1015459



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, number of positions: 7, pitch: 2.5 mm, connection method: Crimp connection, color: white

Printed-circuit board connector - PTCM 0,5/ 8-PL-2,5 WH - 1015458



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, number of positions: 8, pitch: 2.5 mm, connection method: Crimp connection, color: white
