




胶料	料号	模具	模号/AB端
内模料		内模	
中模料		中模	
外模料		外模	

ELECTRICAL TEST:
1.100% OPEN SHORT MIS WIRE TEST
2.CONTACT RESISTANCE:5 OHM MAX
3.INSULATION RESISTANCE:5M OHM MIN
4.HI-POT TEST:DC 300V/10ms

CONSUMER ITEM	LENGTH (mm)	ERP	Packing
/0.5M	500±20		
/1.0M	1000±30		
/2.0M	2000±30		
/3.0M	3000±30		
/5.0M	5000±50		



PIN Assignment



NO.	PART NAME	DESCRIPTION	UNIT
⑦	HDMI CABLE	HDMI 19+1 30AWG BC [(1/0.23BC+1P+D/1/0.23BC+AL/MY)*5P+1/0.23BC*4C]+AL+D/1/0.23BC+64/0.12AL Black PVC Jacket OD:6.0±0.15mm	m
④	MODEL	Black PVC	9
③	MODEL	PE:Nature color	9
②	PLUG	HDMI AF 19P Gold plated .INSULATOR COLOR:BLACK	1PCS
①	PLUG	HDMI AM 19P Gold plated .INSULATOR COLOR:BLACK	1PCS

DESCRIPTION	FINISHED PRODUCT'S FIGURE	SCALE	FIT	UNITS:	MM	1RD ANGLE
MODEL NO.		△				
APPROVED/CHECKED	DRAWING DESIGNED					
FINISHING	MATERIAL	△		2018/07/06		A1
		SYM		DATE		REVISION