


# HM8123, HM8123-X Programmable Counter Technical Data

**HAMEG®**  
Instruments  
A Rohde & Schwarz Company



## Key facts

- Measurement range: DC to 3GHz
- Input A/B (BNC): DC to 200MHz
- Input C (SMA): 100 MHz to 3GHz
- Input impedance A/B: 50Ω or 1MΩ (switchable), sensitivity 25mV
- Input impedance C: 50Ω, sensitivity 30mV
- 10-digit resolution (at 10s gate time)
- 9 measurement functions, external GATE and ARMING connectors (BNC)
- External Ref.-Input (10MHz) via BNC-connector
- HM8123: TCXO (temperature stability:  $\pm 0.5 \times 10^{-6}$ )  
HM8123-X: OCXO (temperature stability:  $\pm 1.0 \times 10^{-8}$ )
- RS-232/USB dual interface, IEEE-488 (GPIB) optional
- Fanless design

Test & Measurement

Technical Data

PD 5210.8695.32 - 04.00

# Technical Data

## HM8123 3GHz Programmable Counter

All data valid at 23°C after 30 minutes warm-up.

### Input characteristics (Input A and B)

Connection	BNC socket	
Frequency range		
0 to 200 MHz	DC coupled	
10Hz to 200 MHz	1MΩ, AC coupled	
500 kHz to 200 MHz	50Ω, AC coupled	
Input impedance	1MΩ    30pF or 50Ω (switchable)	
Attenuation	1:1, 1:10, 1:100 (selectable)	
Sensitivity (normal triggering)		
0 to 80 MHz	25mV <sub>rms</sub> (sine wave), 80mV <sub>ss</sub> (pulse)	
80 to 200 MHz	65mV <sub>rms</sub> (sine wave)	
20Hz to 80 MHz	50mV <sub>rms</sub> (sine wave, auto trigger)	
Trigger (programmable via encoder or software)		
Attenuation:	Trigger level	Resolution
1:1	0 to ±2V	1mV
1:10	0 to ±20V	10mV
1:100	0 to ±200V	100mV
Max. input voltage		
Input 1 MΩ	250V (DC + ACpeak) from 0 to 440Hz decreasing to 8V <sub>rms</sub> at 1MHz	
Input 50Ω	5V <sub>rms</sub>	
Minimum pulse duration	<5ns for single pulse	
Input noise	(typ.) 100µV	
Auto trigger (AC coupling)	trigger point: 50% of peak-to-peak value	
Trigger slope	Rising or falling	
Filter	50kHz low-pass filter (selectable)	

### Input characteristics (Input C)

Connection	SMA socket		
Frequency range:	100MHz to 3GHz		
Input sensitivity	to 1GHz: 30mV <sub>rms</sub> (typ. 20mV <sub>rms</sub> ) 1 to 2GHz: 100mV <sub>rms</sub> (typ. 80mV <sub>rms</sub> ) 2 to 2.5GHz: 150mV <sub>rms</sub> (typ. 100mV <sub>rms</sub> ) 2.5 to 3GHz: 200mV <sub>rms</sub> (typ. 150mV <sub>rms</sub> )		
Input impedance	50Ω nominal		
Max. Input voltage	5V (DC + AC <sub>peak</sub> )		

### Input characteristics

	External Reset	Reference	Gate/ Arming
Input impedance	5kΩ	500Ω	5kΩ
Max. Input voltage	±30V	±20V	±30V
Input sensitivity	-	typ. 2V <sub>pp</sub>	-
High level	>2V	-	>2V
Low level	<0,5V	-	<0,5V
Min. pulse duration	200ns	-	50ns
Input frequency	-	10MHz	-
Min. eff. gate time	-	-	20µs

### Measurement functions

Frequency A/B/C; period duration A; width A; totalize A; RPM A; frequency ratio A:B; time interval A:B; time interval A:B (average); phase A to B; Duty cycle A; burst measurements

### Frequency measurement (Inputs A, B, C)

Frequency range	0 to 200MHz (3GHz)
LSD	(1,25 × 10 <sup>-8</sup> s × frequency) / measurement time

Resolution	1 LSD
Accuracy	±(resolution/frequency ±time inaccuracy ±trigger error <sup>2)</sup> / measurement time)
<b>Period duration measurement</b>	
Range	5ns to 10,000s
LSD	(1,25 × 10 <sup>-8</sup> s × period) / measurement time
Resolution	1 LSD
Accuracy	±resolution / period ±(trigger error <sup>2)</sup> / measurement time)
<b>Totalization A</b>	
	manual control      external control
Range	0 to 200MHz
Min. pulse duration	10ns
LSD	1 count
Resolution	LSD
Accuracy	(resolution ±ext. gate time error x frequency A) / total)
Pulse resolution	10ns
Ext. gate error	-
<b>Time interval/Average time interval</b>	
(Input A = start; Input B = stop)	
LSD	10ns (0,1ps to 10ns im 'average' mode)
Resolution	1LSD
Accuracy	±(resolution + trigger error <sup>2)</sup> +system error) / time interval ±time base uncertainty (system error: ≤4ns)
Number of average	N = 1 to 25      LSD = 10ns N = 26 to 2,500      LSD = 1ns N = 2,501 to 250,000      LSD = 100ps N = 250,001 to 25,000,000      LSD = 10ps N = >25,000,000      LSD = 0.1ps
<b>Rpm measurement</b>	
NPR <sup>1)</sup> presetting	1 to 65.535 pulses per revolution
Gate time	330ms fixed
LSD	7.5 × 10 <sup>-8</sup> x revolution speed
Resolution	1 LSD
Accuracy	±(trigger error <sup>2)</sup> / 0.33) ±time base error
<b>Offset</b>	
Range	Covers the entire measurement range
Resolution	Same resolution as in normal measurement. If the gate time is changed in the offset mode, the offset resolution is the reference value resolution or the current reading resolution (whichever is less precise).
<b>Gate time</b>	
Range	1ms to 65s
Resolution	1ms
External gate time	min. 20µs
<b>Time base</b>	
Frequency	400MHz clock rate; 10MHz Quarz
Temperature stability (0 to 50°C)	TCXO (standard): ±0,5 × 10 <sup>-6</sup> OCXO (HO85): ±1,0 × 10 <sup>-8</sup>
Aging	TCXO: <0.27 ppm per month, 0.05 ppm per day OCXO: ≤ ±1 × 10 <sup>-9</sup> /day
External Reference	10MHz ±20 ppm
<b>Miscellaneous</b>	
Interface	Dual-Interface USB/RS-232 (HO820), optional HO880 IEEE-488 (GPIB)
Safety class	Safety class I (EN61010-1)
Display	LCD display (83 x 21 mm)

Power Supply	115 to 230V $\pm 10\%$ , 45 to 60 Hz, CAT II
Power consumption	approx. 20W
Operating temperature	+5 to +40°C
Storage temperature	-20 to +70°C
Rel. humidity	5 to 80% (without condensation)
Dimensions (W x H x D)	285 x 75 x 365mm
Weight	approx. 4kg

- 1) NPR=number of pulses per revolution  
 2) Trigger error=  $\pm$ noise input ( $V_{pp}$ )/slew rate of the input signal

**Accessories supplied:**

Line cord, Operating manual

**Recommended accessories:**

HO880 Interface IEEE-488 (GPIB), galvanically isolated  
 HZ20 Adapter, BNC to 4mm banana  
 HZ24 Attenuators 50Ω (3/6/10/20 dB)  
 HZ42 19" Rackmount kit 2RU  
 HZ72 GPIB-Cable 2 m