

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0346760001](#)  
**Status:** **Active**  
**Overview:** Stac64 Single, Multi-Pocket and Hybrid Header System  
**Description:** 1.62mm Cavity Plug

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Packaging Specification PK-31300-850 \(PDF\)](#)

**General**

|                |   |
|----------------|---|
| Product Family | Accessories   |
| Series         | <a href="#">34676</a>                                       |
| Component Type | Cavity Plug   |
| Overview       | <u>Stac64 Single, Multi-Pocket and Hybrid Header System</u> |
| Product Name   | N/A   |
| UPC            | 822350913119  |

**Physical**

|                               |           |
|-------------------------------|-----------|
| Circuits (Loaded)             | 0         |
| Circuits (maximum)            | 0         |
| Gender                        | Plug      |
| Lock to Mating Part           | Yes       |
| Material - Resin              | Polyester |
| Net Weight                    | 0.078/g   |
| Packaging Type                | Bag       |
| Temperature Range - Operating | N/A       |


**Solder Process Data**

|                             |     |
|-----------------------------|-----|
| Lead-freeProcess Capability | N/A |
|-----------------------------|-----|

**Material Info**

**Reference - Drawing Numbers**

|                         |              |
|-------------------------|--------------|
| Packaging Specification | PK-31300-850 |
| Sales Drawing           | SD-34676-000 |



**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/88/2018 (15  
January 2019)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

[34676 Series](#)

**Use With**

0.64mm "GET" Receptacle Terminal  
Cavities