Coated Stainless Steel Cable Ties Black

pro-**Power**



Features

- · Self-locking head design speeds installation and locks into place at any length along tie body
- · Provides a strong, durable method of cable bundling
- · Used in a wide range of indoor, outdoor, and underground (including direct burial)
- · Smooth surfaces and rounded edges assures cable protection and safety
- · Excellent ultraviolet and chemical resistance
- UL certified

Specifications

Operation Temperature: -40°C to +150°C (-40°F to +302°F)Min. Installation Temperature: -40°C (-40°F)Colour: BlackMaterial: 316 stainless steel for the most corrosive environments
Coated with polyester for insulation purpose

Dimensions Tensile Description Part Number Quantity (L×W) Strength BC46-100 100mm × 4.6mm 150mm × 4.6mm BC46-150 200mm × 4.6mm BC46-200 450N (100lb) 100PK 260mm × 4.6mm BC46-260 Coated Stainless Steel Cable Ties. 360mm × 4.6mm BC46-360 Black 520mm × 4.6mm BC46-520 150mm × 7.9mm BC76-150 200mm × 7.9mm 800N(175lb) **50PK** BC76-200 360mm × 7.9mm BC76-360

Part Number Table

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of Premier Farnel Limited 2019.

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands

