Surface Mount Type

Series: TQ Type: V

High temperature Lead-Free reflow (suffix : A*)




Features

- Endurance : 125 °C 2000 h
- 1 size smaller and same performance compare with V-TK series
- Low ESR (85 % low ESR in low temperature after endurance compare with V-TP series)
- Vibration-proof product (30G guaranteed) is available upon request
- RoHS compliant


Specifications										
Category temp. range		-40 ℃ to +	125 ℃							
Rated voltage range		35 V.D	C							
Capacitance range		47 µF to 1	00 µF							
Capacitance tolerance	±20 % (120 Hz / +20℃)									
Leakage current	$I \leq 0.01 \text{ CV} (\mu A) \text{ After 2 minutes}$									
Dissipation factor (tan δ)	Please see the attached characteristics list									
Endurance	After the life test with DC rated working voltage at +125 $^{\circ}$ C ± 2 $^{\circ}$ C for 2000 hours, the capacitors shall meet the limits specified below.									
	Capacitance change	Within ± 30 % of the initial value								
	Dissipation factor (tan δ) \leq 300 % of the initial limit									
Litutance	Leakage current Within the initial limit									
	ESR after	Size code	D8							
	endurance	Initial (20 ℃)	0.30							
	(Ω/100 kHz)	After 2000 h (−40 ℃)	6							
	After storage for 1000 hours at +125 $^{\circ}$ C ± 2 $^{\circ}$ with no voltage applied and then being									
Shelf life	stabilized at $+20$ °C, capacitors shall meet the limits specified in endurance. (With voltage treatment)									
	After reflow soldering and then being stabilized at +20 $^{\circ}$ C, capacitors shall meet the									
Resistance to	following limits.									
soldering heat	Capacitance change	Within ± 10 % of the initial value								
Solucing field	Dissipation factor (tan δ)	Within the initial limit								
	Leakage current	Within the initial limit								
AEC-Q200		AEC-Q200 cc	ompliant							

Frequency cor	rection factor for			
Frequency (Hz)	120	1 k	10 k	100 k to
Correction factor	0.65	0.85	0.95	1.00

Marking



Dimensions





Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.


Dimensions (Vibration-proof products)

* The size and shape are different from standard products. Please inquire details of our company.

< Size code : D, D8 >







*1 : E to G : L±0.3 H13 to K21 : L±0.5


Supportive Terminals Unit : mm

Size code	φD	L	А, В	H max.	F	Ι	W	Ρ	К	R	S	Т
D	6.3	6.1	6.6	7.8	0 to +0.15	2.4	0.65±0.1	2.2	0.35 +0.15 -0.20	1.1±0.2	3.3±0.2	1.05 ± 0.2
D8	6.3	8.0	6.6	7.8	0 to +0.15	2.4	0.65±0.1	2.2	0.35 +0.15 -0.20	1.1±0.2	3.3±0.2	1.05±0.2
E	8.0	6.5	8.3	9.5	0 to +0.15	3.4	0.7±0.1	2.2	0.35 +0.15 -0.20	0.70±0.2	5.3±0.2	1.7±0.2
F	8.0	10.5	8.3	10.0	0 to +0.15	3.4	1.2±0.2	3.1	0.70±0.2	0.70±0.2	5.3±0.2	1.3±0.2
G	10.0	10.5	10.3	12.0	0 to +0.15	3.5	1.2±0.2	4.6	0.70±0.2	0.70±0.2	6.9±0.2	1.3±0.2
H13	12.5	13.8	13.5	15.0	-0.1 to +0.15	4.7	1.2±0.2	4.4	0.70±0.3	2.2±0.2	7.1±0.2	2.4±0.2
J16	16.0	16.8	17.0	19.0	-0.1 to +0.15	5.5	1.4±0.2	6.7	0.70±0.3	3.0±0.2	9.0±0.2	1.9±0.2
K16	18.0	16.8	19.0	21.0	-0.1 to +0.15	6.7	1.4±0.2	6.7	0.70±0.3	3.0±0.2	11.0±0.2	1.9±0.2
K21	18.0	21.8	19.0	21.0	-0.1 to +0.15	6.7	1.4±0.2	6.7	0.70±0.3	3.0±0.2	11.0±0.2	1.9±0.2

Land / Pad pattern


The circuit board land/pad pattern size for chip capacitors is specified in the following table. The land pitch influences installation strength and consider it.


Standard products



Land space 0000


• Vibration-proof products





С





(Table of board land size vs. capacitor size) Unit : mm									
Size code	а	b	С						
Β (φ4)	1.0	2.5	1.6						
C (φ5)	1.5	2.8	1.6						
D (φ6.3)	1.8	3.2	1.6						
D8 (φ6.3x7.7L)	1.8	3.2	1.6						
E (φ8x6.2L)	2.2	4.0	1.6						
F (φ8x10.2L)	3.1	4.0	2.0						
G (φ10x10.2L)	4.6	4.1	2.0						
Η (φ12.5)	4.0	5.7	2.0						
J (φ16)	6.0	6.5	2.5						
Κ (φ18)	6.0	7.5	2.5						
When size #a# is wide heals fillet can be made decreasing fitting strength									

When size "a" is wide, back fi llet can be made, decreasing fi tting strength.

(Table of board land size vs. capacitor size) Unit : mm											
Size code	Α	В	С	D	E	F	G	Н			
D (φ6.3xL6.1)	1.2	3.6	3.2	2.0	0.95	0.65	1.0	1.2			
D8 (φ6.3xL8.0)	1.2	3.6	3.2	2.0	0.95	0.65	1.0	1.2			
E (φ8x6.5L)	1.8	4.2	5.0	1.3	1.5	1.4	1.5	2.0			
F (φ8x10.5L)	2.7	4.0	4.7	1.3	1.0	1.7	1.1	2.5			
G (φ10)	3.9	4.4	4.7	1.3	1.2	1.9	1.1	2.5			
Η (φ12.5)	3.9	6.0	6.9	2.8	1.3	1.9	2.2	2.5			
J (φ16)	5.8	6.8	6.2	3.6	1.3	1.9	1.7	2.8			
Κ (φ18)	5.8	7.3	6.2	3.6	1.8	1.9	1.7	2.8			

When size "A" is wide, back fi llet can be made, decreasing fi tting strength.

* Take mounting conditions, solderability and fi tting strength into consideration when selecting parts for your company's design.

The vibration-proof capacitors of size $\Phi 6.3$ has support terminals extending from the bottom side to the lead edge. Then, make sure to find appropriate soldering conditions to form fillet on the support terminals if required for appearance inspection.

Characteristics list

Endurance : 125 ℃ 2000 h

Rated Cap.	1	Case size (mm)		Specification		Part No.			Min. Packaging Q'ty			
volt. (V.DC)	(±20 %) (μF)	φD	L Standard	Vibration -proof		Ripple current *1 (mA r.m.s.)	ESR ^{*2} (Ω)	tan δ ^{*3}	Standard	Vibration-proof	L Reflo	Taping (pcs)
35	47	6.3	7.7	8.0	D8	197	0.30	0.16	EEETQV470XAP	EEETQV470XAV	(5)	900
35	100	6.3	7.7	8.0	D8	197	0.30	0.16	EEETQV101XAP	EEETQV101XAV	(5)	900

*1: Ripple current (100 kHz / +125 $^{\circ}\mathrm{C})$

*2: ESR (100 kHz / +20 ℃) *3: tan δ (120 Hz / +20 ℃)

- If Part number exceeds 12 digits, voltage code is abbreviated as follows; $1V \rightarrow V$

• Please refer to the page of "Reflow Profile" and "The Taping Dimensions".

Guidelines and precautions regarding the technical information and use of our products described in this online catalog.

- If you want to use our products described in this online catalog for applications requiring special qualities or reliability, or for applications where the failure or malfunction of the products may directly jeopardize human life or potentially cause personal injury (e.g. aircraft and aerospace equipment, traffic and transportation equipment, combustion equipment, medical equipment, accident prevention, anti-crime equipment, and/or safety equipment), it is necessary to verify whether the specifications of our products fit to such applications. Please ensure that you will ask and check with our inquiry desk as to whether the specifications of our products.
- The quality and performance of our products as described in this online catalog only apply to our products when used in isolation. Therefore, please ensure you evaluate and verify our products under the specific circumstances in which our products are assembled in your own products and in which our products will actually be used.
- If you use our products in equipment that requires a high degree of reliability, regardless of the application, it is recommended that you set up protection circuits and redundancy circuits in order to ensure safety of your equipment.
- The products and product specifications described in this online catalog are subject to change for improvement without prior notice. Therefore, please be sure to request and confirm the latest product specifications which explain the specifications of our products in detail, before you finalize the design of your applications, purchase, or use our products.
- The technical information in this online catalog provides examples of our products' typical operations and application circuits. We do not guarantee the non-infringement of third party's intellectual property rights and we do not grant any license, right, or interest in our intellectual property.
- If any of our products, product specifications and/or technical information in this online catalog is to be exported or provided to non-residents, the laws and regulations of the exporting country, especially with regard to security and export control, shall be observed.

<Regarding the Certificate of Compliance with the EU RoHS Directive/REACH Regulations>

- The switchover date for compliance with the RoHS Directive/REACH Regulations varies depending on the part number or series of our products.
- When you use the inventory of our products for which it is unclear whether those products are compliant with the RoHS Directive/REACH Regulation, please select "Sales Inquiry" in the website inquiry form and contact us.

We do not take any responsibility for the use of our products outside the scope of the specifications, descriptions, guidelines and precautions described in this online catalog.