ALUMINUM ELECTROLYTIC CAPACITORS SPECIFICATION SHEET

RoHS Compliance

CUSTOMER PART No.		
Rubycon PART No.	50 YXG 680 M EFC 16X20	
DRAWING No.	RER-208553	ISSUE No.1
ISSUE DATE	20 March 2019	



RUBYCON CORPORATION

ENGINEERING DIVISION ELECTROLYTIC CAPACITOR DESIGN DEPT.

1938-1, NISHIMINOWA, INA-SHI, NAGANO-KEN, JAPAN TEL No. 0265-72-7116 FAX No. 0265-73-3380

	YOSHIHIRO KITAHARA		
DESIGN	y. Hitahara		
	KAZUHIRO YONEYAMA		
CHECK	kyone		
	YOSHINORI SASAKI		
APPROVAL	7. Goegle		

Rubycon

Aluminum electrolytic capacitor Specification Sheet

50 YXG 680 M EFC 16X20

Drawing No. : RER-208553


1.Scope

This specification covers polarized aluminum electrolytic capacitors with non-solid electrolyte for use in electronic equipments. Style: CE 04 (Radial Leaded)

2. Numbering System

Rated Voltage	Series	Capacitance	Capacitance Tolerance	Option	Lead Forming	Size
<u>50</u>	<u>YXG</u>	<u>680</u>	<u>M</u>	<u>EFC</u>		<u>16X20</u>

3.Diagram of dimensions Unit: mm



		Dimension	s	
φD	L	F	φd	α
16	20	7.5	0.8	2

1	Sleeve	P.E.T.	
2	Case	Aluminum	
3	Lead Wire	Copper clad steel wire	Tin plated

A safety vent shall be provided.

4.Marking

Unless otherwise specified, capacitor shall be clearly marked the following items on its body. Sleeve color: Black, Lettering color: White

(1)Trade mark **Rubycon**

(2)Rated Voltage 50V(3)Nominal Capacitance 680μF

(4)Polarity (Negative Polarity)

(5)Series YXG

(6)Lot Number

(7)Maximum Operating
Temperature
(8)PET sleeve mark

105°C

PET

5. Electrical Performance

Table-1

Operating Temperature Range		-40 ~105	(°C)	
Nominal Capacitance	20°C, 120Hz	680	(µF)	
Capacitance Tolerance		-20 ~ 20	(%)	
Rated Voltage		50	(V.DC)	
Surge Voltage		63	(V.DC)	
Leakage Current	20°C, 2min.	340	(µA max.)	
Dissipation Factor (tanδ)	20°C, 120Hz	0.10	(max.)	
Rated Ripple Current	105°C, 100kHz	1840	(mAr.m.s.)	
Impedance Ratio 120Hz	Z-25°C/Z20°C	2	(max.)	
	Z-40°C/Z20°C	3	(max.)	
Impedance	20°C, 100kHz	0.034	(Ωmax.)	
	-10°C, 100kHz	0.1	(Ωmax.)	

Drawing No.: RER-208553

Rubycon YXG series

Aluminum electrolytic capacitor Specification Sheet

XG series Issue No. : 1

6. PERFORMANCE

able – 2					
1 Load Life Test	<condition> Capacitor under the test shall be applied the rated voltage continuously through 1000Ω series protective resistor (with rated ripple current) at following temperature and time. After the test and returned in standard condition for 1 to 2 hours, and the capacitor shall meet following requirements. Temperature: 105 ±2°C</condition>				
	<criteria></criteria>				
	Leakage Current Not more than the specified value				
	Capacitance Change Within ±25% of the initial value				
	Dissipation Factor Not more than 200% of the specified value				
	Appearance Notable changes shall not be found. (except sleeve Condition)				
2 Shelf Life Test	<condition> Capacitor shall be stored at following temperature and time with no voltage applied. After the test and returned in standard condition for 1 to 2 hours and the capacitor shall meet following requirements. (If any doubt arises on the judgment, the capacitors shall be subjected to voltage treatment specified.)</condition>				
	in JIS C 5141,5.2.)				
	Temperature: 105 ±2°C Time: 1000 ⁺⁴⁸ / ₀ h				
	Time: 1000 '60 h				
	<criteria></criteria>				
	Leakage Current Not more than the specified value				
	Capacitance Change Within ±25% of the initial value				
	Dissipation Factor Not more than 200% of the specified value				
	Appearance Notable changes shall not be found				
3 Rated ripple current	(1) The rated ripple current is the maximum A.C. current at 100kHz and can be applied at maximum operating temperature.				
	(2) The combined value of D.C. voltage and the peak A.C. voltage shall not exceed the rated voltage and shall not be reverse voltage. <frequency coefficient=""></frequency>				
	Frequency (Hz) 120 1k 100k≤ Capacitance (μF)				
	680 0.55 0.77 0.94 1				
	<temperature coefficient=""></temperature>				
	Temperature(°C) 105 85 65≥				
	Coefficient 1.0 1.7 2.1				

Drawing No.: RER-208553



Aluminum electrolytic capacitor Specification Sheet

YXG series Issue No. : 1

Notes on use of aluminum electrolytic capacitors

(1) Charge and discharge

Do not use for the circuit that repeats quick charge or discharge.

(2) External stress

Do not apply excessive force of pushing, pulling bending, and/or twisting to the main body, lead wire and terminals.

(3) Heat resistance at soldering process

In the soldering process of PC board with Capacitors mounted, secondary shrinkage or crack of sleeve may be observed when soldering temperature is too high and /or soldering time is too long.

If lead wire of other components or pattern of double sided PC board touches the capacitor, the similar failure may be also originated at pre-heating, heating at hardening process of adhesive and soldering process.

(4) Insulation and PC board mounting

Sleeve is for marking purpose only.

It is not recognized as insulation materials.

When double sided PC board is employed, note that it could cause a short circuit if lead wire of other components or pattern of double sided PC board touches capacitor. Please avoid circuit pattern runs underneath capacitor.

In addition, case and cathode terminal are not insulated.

(5) Adhesives and coating materials

Do not use the adhesives and coating materials that contain halogenated organic solvents or chloroprene as polymer.

(6) Storage

Keep at a normal temperature and humidity. During a long storage time, leakage current will be increased. To prevent heat rise or any trouble that high leakage current possibly causes, voltage treatment is recommended for the capacitors that have been stored for a long time.

(Storage Condition)

- *Aluminum electrolytic capacitors should not be stored in high temperatures or where there is a high level of humidity. The suitable storage condition is 5°C-35°C and less than 75% in relative humidity.
- *Aluminum electrolytic capacitors should not be stored in damp conditions such as water, saltwater spray or oil spray.
- *Do not store aluminum electrolytic capacitors in an environment full of hazardous gas (hydrogen sulfide, sulfurous acid gas, nitrous acid, chlorine gas, ammonia or bromine gas).
- *Aluminum electrolytic capacitors should not be stored under exposure to ozone, ultraviolet rays or radiation.

(7) Fumigation and halogenated flame retardant

It may cause corrosion of internal electrodes, aluminum cases and terminal surface when the following conditions exist.

- *Fumigation of wooden pallets before shipment to disinfect vermin.
- *Existence of components or parts that contain halogenated flame retardant agent (bromine etc.) together with capacitors.
- *When halogenated detergents of antiseptics for preventing infection of epidemic diseases contact directly to capacitors.

(8) PC board cleaning after soldering

Please consult us when cleaning is subjected.

*Guide to application except the above are described in our catalog and EIAJ RCR-2367C.

EIAJ RCR-2367C: "Safety Application Guide for fixed aluminum electrolytic capacitors for use in electronic equipment."

Published by Japan Electronics and Information Technology Industries Association.