

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0026202061

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK 396 Wire-to-Board Header, Vertical Round Pin, 6 Circuits, Tin (Sn) Plating, with Mating Pin Length of 11.43mm (.450")

Documents:

3D Model

Packaging Specification PK-3192-001 (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Product Specification PS-99020-0087-001 (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Overview

Product Name

UPC

PCB Headers

3192

Board-to-Board, Power, Wire-to-Board

KK® Interconnect System - Molex

KK 396

800753735248

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

First Mate / Last Break

Flammability

Glow-Wire Capable

Guide to Mating Part

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PC Tail Length

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Plating min - Termination

Polarized to Mating Part

Polarized to PCB

Shrouded

Stackable

Temperature Range - Operating

Termination Interface: Style

No

6

6

Natural

25

No

94V-2

No

No

None

None

Brass

Tin

Tin

Nylon

1.462/g

1

Vertical

4.45mm

No

None

1.60mm

Bag

3.96mm

3.96mm

5.080µm

5.080µm

No


No

No

Yes

See Product Specification

Through Hole



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/39/2015 (15 June
2015)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

3192 Series

Mates With

3069 KK Crimp Terminal Housing, 3215 KK
396 PC Board Connector

Electrical

Current - Maximum per Contact	7.0A
Voltage - Maximum	250V

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235

Material Info

Engineering Number	319206A
--------------------	---------

Reference - Drawing Numbers

Packaging Specification	PK-3192-001
Product Specification	PS-99020-0087-001
Sales Drawing	SDAE-3192-N*

This document was generated on 10/22/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION