Zero Smog 4V

Product no.: T0053660699N





- Constant Flow Control (CFC) guarantees automatical air flow regulation for each working place independent of the connected workplaces
- > Electronic filter control with optical and acoustical filter alarm
- > Efficiency test via USB port
- 4 wheels to allow easy movement of the unit
- > Low noise level
- > 4 kits available
- > The fume extraction unit Zero Smog 4V (ZS 4V) is easy to install and operate. It is designed for use as a small central system. A powerful, maintenance-free turbine provides continuous fume extraction at a maximum air extraction rate of 230 m3/h. With setting constant flow control the adjustable turbine speed avoiding unnecessary waste of suction power and saving energy.

For this purpose, we recommend:



Solder fume extractors



Soldering irons



Cleaning



Pre-heating plates



Dimensions L x W x H (mm)	345 x 325 x 505
Dimensions L x W x H (inches)	13.58 x 12.79 x 19.88
Weight (approx.) in kg	19
Voltage	220-240 V (50/60 Hz)
Power	275 VA
Noise level (distance 1 m) dB(A)	< 48
Max. vacuum	
Capacity m³/h	230
Pre-filter	Pre filter mat class F7
Compact filter	Particle filter H13, Wide band gas filter (50 % Active carbon + 50 % Chemisorb)
Max. capacity	1–4 workstations
RS232 interface (remote control)	All system functions can be operated and remotely monitored via the RS232 port.
USB port	on
WX-compatible	on

Owning the bench









Weller Tools GmbH Carl-Benz-Straße 2 74354 Besigheim Germany

Phone: +49 (0) 7143 / 580-0 Fax.: +49 (0) 7143 / 580-108 Email: info@weller-tools.com Web: www.weller-tools.com