



Main

| | |
|------------------------------|--|
| Range of product | Altivar |
| Product or component type | EMC input filter |
| Range compatibility | Altivar Process ATV600 Altivar Process ATV900 |
| Product compatibility | ATV630 wall mount, at 7.5 kW, 380...480 V ATV630 wall mount, at 11 kW, 380...480 V ATV630 wall mount, at 15 kW, 380...480 V ATV630 wall mount, at 4 kW, 200...240 V ATV630 wall mount, at 5.5 kW, 200...240 V ATV630 wall mount, at 7.5 kW, 200...240 V ATV650 wall mount, at 7.5 kW, 380...480 V ATV650 wall mount, at 11 kW, 380...480 V ATV650 wall mount, at 15 kW, 380...480 V ATV930 wall mount, at 7.5 kW, 380...480 V ATV930 wall mount, at 11 kW, 380...480 V ATV930 wall mount, at 15 kW, 380...480 V ATV930 wall mount, at 4 kW, 200...240 V ATV930 wall mount, at 5.5 kW, 200...240 V ATV930 wall mount, at 7.5 kW, 200...240 V ATV950 wall mount, at 7.5 kW, 380...480 V ATV950 wall mount, at 11 kW, 380...480 V ATV950 wall mount, at 15 kW, 380...480 V |
| Product specific application | Radio interference input filter |
| [In] rated current | 35 A |
| Thermal losses | 4.8 W |
| Network number of phases | Three phase |

Complementary

| | |
|-------------------------------|--|
| Electrical connection | Terminal 6 mm ² AWG 8 |
| Motor cable length | <= 150 m shielded motor cable 4 kHz conforming to EN/IEC 61800-3 category C2, 380...480 V <= 300 m shielded motor cable 4 kHz conforming to EN/IEC 61800-3 category C3, 380...480 V <= 150 m shielded motor cable 4 kHz conforming to EN/IEC 61800-3 category C2, 200...240 V <= 300 m shielded motor cable 4 kHz conforming to EN/IEC 61800-3 category C3, 200...240 V <= 50 m shielded motor cable 4 kHz conforming to EN/IEC 61800-3 category C1, 200...240 V <= 50 m shielded motor cable 4 kHz conforming to EN/IEC 61800-3 category C1, 380...480 V |
| Maximum earth leakage current | 7.6 mA at 400 V 50 Hz TN 7.6 mA at 400 V 50 Hz TT |
| Power supply voltage | 200...240 V 380...480 V |

| | |
|-----------------------|--|
| Tolerance | 10 % |
| Mechanical robustness | Shocks conforming to IEC 60721-3-3 class 3M4 Vibrations conforming to IEC 60721-3-3 class 3M4 |
| Width | 80 mm |
| Height | 302 mm |
| Depth | 155 mm |
| Product weight | 4.1 kg |

Environment

| | |
|---------------------------------------|--|
| IP degree of protection | IP20 mounting side by side IP21 with kit VW3A47903 |
| Relative humidity | 5...95 % without condensation conforming to IEC 61800-5-1 |
| Ambient air temperature for operation | 50...60 °C with current derating 1.5 % per °C -10...50 °C without current derating |
| Ambient air temperature for storage | -40...70 °C |
| Operating altitude | 0...1000 m without current derating 1000...4000 m with current derating 1 % per 100 m |
| Standards | EN/IEC 61800-3 |

Offer Sustainability

| | |
|------------------------|---|
| RoHS (date code: YYWW) | Compliant - since 1433 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
|------------------------|---|