

32-Device AC Charging Station Cart for Chromebooks and Laptops, Wall-Mount Option, Black

MODEL NUMBER: **CSC32AC**



Locking steel cart provides AC charging, secure storage and cord management for up to 32 Chromebooks and laptops. Recommended for education, office, commercial, retail, industrial and healthcare environments.

Description

The CSC32AC 32-Device AC Charging Station Cart provides AC charging, secure storage and cord management for up to 32 Chromebooks and laptops. It's recommended for education, office, commercial, retail, industrial and healthcare environments.

32 AC outlets provide convenient charging for Chromebooks and laptops with a screen size up to 15 inches. Their AC adapters plug into the cart's 32 NEMA 5-15R outlets as needed, up to 1,440 total watts. The CSC32AC also charges tablets and other USB devices through their power adapters. A built-in circuit breaker protects against overloads. The 10-foot AC input cord with NEMA 5-15P plug reaches distant outlets to help you place the cart in a convenient location.

The cart promotes comprehensive device protection with steel construction and a black powder-coated finish for long-term durability. It locks with the included keys to help prevent device theft, damage or tampering, and flow-through ventilation helps prevent overheating.

The cart also encourages clutter-reducing organization of devices and cabling. AC outlets, power adapters and cords store out of sight. Toolless trim panels permit quick service access.

When moving devices from room to room, the cart provides convenient mobility. Large swivel casters with non-marking wheels improve the ride over uneven surfaces and lock to help prevent unwanted movement at rest. The reversible wide-grip handle assists cart control.

The cart is easy to configure. It ships ready for quick, easy installation, and the handle and cord wrap attach on either side. The split front doors open 180 degrees for improved device and service access. Rear-panel slots support optional wall-mount installation, and removable shelf dividers accommodate thicker devices.

Features

Convenient Charging Charges 32 Chromebooks and laptops up to 15 in. screen size
Device power

Highlights

- Charges 32 Chromebooks and laptops up to 15 in. screen size
- Secures devices in locking, vented, wall-mountable steel cart
- Protective shelves with removable dividers and cord management
- Wide-grip handle and locking casters with non-marking wheels
- Ships ready for quick, easy installation

Package Includes

- CSC32AC 32-Device AC Charging Station Cart, Black
- Cart handle
- Input cord wrap
- Hex key
- Mounting hardware for handle and cord wrap
- (2) Keys
- Owner's manual



adapters plug into NEMA 5-15R outlets (up to 1,440 watts total) Also charges tablets and other USB devices through their power adapters Built-in circuit breaker protects against overloads 10 ft. AC input cord with NEMA 5-15P plug reaches distant outlets

Comprehensive Protection Sturdy steel construction and powder-coated finish promote long-term durability Doors lock with included keys to help prevent device theft, damage or tampering 3-point locking mechanism latches doors at top, middle and bottom Built-in hasp and user-supplied padlock can replace or supplement built-in lock Rear ports accommodate user-supplied bicycle cable or chain lock Flow-through ventilation helps prevent devices from overheating Protective shelves specially coated to avoid device scratches and scuffs Cord access ports with rubber grommets protect against abrasions Solid top work surface helps avoid accidental drips and spills that could damage devices

Clutter-Reducing Organization AC outlets, power adapters and cords store out of sight Toolless trim panels permit quick access to AC adapters and cords Shelves include charging cord access ports for each device Staggered outlets fit power adapters without blocking adjacent outlets

Effortless Mobility Large swivel casters with non-marking wheels improve ride over uneven surfaces Casters lock to help prevent unwanted movement at rest Reversible wide-grip handle assists cart control Reversible cord wrap keeps input cord out of the way when moving cart Compact cart fits in same space as typical utility cart

Flexible Configuration Ships ready for quick, easy installation—just attach handle and cord wrap Split front doors open 180 degrees for improved device and service access Rear-panel mounting slots support optional wall-mount installation Removable dividers accommodate thicker devices like battery chargers

Specifications

OVERVIEW	
UPC Code	037332191809
OUTPUT	
Charging Ports / Amps	(32) 12A
Charging Method	AC
INPUT	
Voltage Compatibility (VAC)	120
Input Frequency	50 / 60 Hz
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
PHYSICAL	
Shipping Dimensions (hwd / in.)	45.08 x 22.83 x 33.66
Shipping Dimensions (hwd / cm)	114.50 x 57.99 x 85.50
Shipping Weight (lbs.)	166.00
Shipping Weight (kg)	75.30
Unit Dimensions (hwd / in.)	42.3 x 34.8 x 21.6 (with handle installed)
Unit Dimensions (hwd / cm)	106.76 x 88.39 x 54.86 (with handle installed)
Unit Weight (lbs.)	130.67



Unit Weight (kg)	59.27
Color	Black
Slot Dimensions - Top (hwd / in.)	10.5 x 1.5 x 15.4
Slot Dimensions - Top (hwd / mm)	266.7 x 38.2 x 390.5
Slot Dimensions - Bottom (hwd / in.)	10.5 x 1.5 x 15.4
Slot Dimensions - Bottom (hwd / mm)	266.7 x 38.2 x 390.5
Charging Station Form Factor	Mobile Cart
CERTIFICATIONS	
Certifications	Tested to EIA-310-E, FCC & IEC Class B, UL 1363 (Power Component)
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>