

Cisco GLC-LH-SMD Compatible SFP Transceiver Module - 1000BASE-LH

Product ID: SFPG1320C



The SFPG1320C is a Cisco GLC-LH-SMD compatible fiber transceiver module that has been designed, programmed and tested to work with Cisco® brand switches and routers. It delivers dependable 1 GbE connectivity over fiber cable, for 1000BASE-LH compliant networks, with a maximum distance of up to 20 km (12.4 mi).

Technical Specifications:

- **Wavelength:** 1310nm
- **Maximum Data Transfer Rate:** 1.25 Gbps
- **Type:** Single Mode Fiber
- **Connection Type:** LC Connector
- **Maximum Transfer Distance:** 20 km (12.4 mi)
- **MTBF:** 2,722,277 hours
- **Power Consumption:** Less than 1 Watt
- **Digital Diagnostics Monitoring (DDM):** Yes

This SFP fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

StarTech.com SFPs

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility



Applications

- Replacing defective or damaged SFP modules in Cisco switches and routers
- Expand your network to remote segments

Features

- 100% compatibility with Cisco GLC-LH-SMD guaranteed
- StarTech.com SFP modules are backed by a lifetime warranty
- Meets or exceeds OEM specifications and Multi-Source Agreement (MSA) industry standards
- Low power consumption of less than 1 W
- Hot-swappable with fiber-optic modules

Hardware	Warranty	Lifetime
	Compatible Brand	Cisco
	Industry Standards	IEEE 802.3z 1000BASE-LH
	WDM	No
Performance	Compatible Networks	1000 Mbps (1 Gbps)
	DDM	Yes
	Fiber Operating Mode	Half/Full-Duplex
	Max Transfer Distance	20 km (12.4 mi)
	Maximum Data Transfer Rate	1.25 Gbps
	MTBF	2,722,277 hours
	Type	Single Mode
	Wavelength	1310nm
Connector(s)	Local Unit Connectors	1 - Fiber Optic LC Duplex Female
Special Notes / Requirements	Note	For use in Gigabit fiber networking equipment and media converters
	System and Cable Requirements	MSA or Cisco compliant SFP port
Power	Power Consumption (In Watts)	< 1 W
Environmental	Humidity	30~70% RH
	Operating Temperature	0°C to 70°C (32°F to 158°F)
	Storage Temperature	-40°C to 85°C (-40°F to 185°F)
Physical Characteristics	Product Height	10 mm [0.4 in]
	Product Length	60 mm [2.4 in]
	Product Weight	20 g [0.7 oz]
	Product Width	12 mm [0.5 in]
Packaging Information	Shipping (Package) Weight	48 g [1.7 oz]
What's in the Box	Included in Package	1 - 1.25 Gbps Single Mode LC SFP

Product appearance and specifications are subject to change without notice.