

MAX620H340S

- Waterproof and dustproof IP67 certified
- Mil Specs (STANAG 4280, DEF STAN 81-41)
- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Holes for double padlocking
- Stackable interlocking system
- Thick body material
- Fully length hinges
- Nylon pins, corrosion free

Body and handle: polypropylene copolymer

Latches: nylon

Pins: nylon + 30% fiberglass

O-ring: polymer

Wheels: Nylon + Polyurethane

Pin of the wheels: Stainless Steel

COLOURS: black

EXTERNAL DIMENSIONS: 687 x 528 x H36 mm (27.05 x 20.79 x H14.41 inch)

INTERNAL DIMENSIONS: 620 x 460 x H340 mm (24.41 x 18.11 x H13.38 inch)

LID-BOTTOM DEPTH: 60 + 280 mm (2.36 + 11.02 inch)

WEIGHT WITH FOAM: 9.6 Kg – 21.16 lbs.

DIAMETER OF THE WHEELS: 60mm - 2.362 inch

CARTON DIMENSIONS: 720 x 540 x 410mm – 28.35x21.26x16.14 inch

PCS PER CARTON: 1

WEIGHT OF THE FULL CARTON WITH FOAMS: 11.22 kg – 24.73 lbs.

MOULDING: injection molded

RANGE TEMPERATURE: -30 / 90°C (-22 / 194°F)

FEATURES: wheels, extendable handle, IP67, STANAG 4280, DEF STAN 81-41

CUSTOMIZATION: personalized nameplate/resin label

ACCESSORIES: cubed foam

