



Description

- HDPE durAstatic® Bottles are dissipative and are designed to protect your valuable static sensitive printed circuitry
- No migratory additives - reduces the chance for contamination from the bottle
- Embossed with ESD protective symbol, allowing people to immediately know the bottle is ESD protective
- Long lasting dissipative properties:
Rtt: 1×10^4 to $<1 \times 10^{11}$ ohms tested per ANSI/ESD STM11.12
<2 second charge decay, tested per IEC 61340-5-1:1998
- Dispenses approximately 0.2cc of liquid with each pump
- Genuine Menda "dish-type" liquid dispenser pumps and bottle one-handed operation dispensing small amount of liquid into top dish
- Genuine Made in the United States of America Menda pump and bottle - accept no substitutes


"It should be understood that any object, item, material or person could be a source of static electricity in the work environment. Removal of unnecessary nonconductors, replacing nonconductive materials with dissipative or conductive materials and grounding all conductors are the principle methods of controlling static electricity in the workplace, regardless of the activity." (ESD Handbook ESD TR20.20 section 2.4 Sources of Static Electricity)



One-Touch Pump



Note: Printed bottles eliminate the need for additional labels - custom printing available.



6 oz. bottles include measurements on one side to see how much fluid is left in the container



35273

Item	Description	Height*
35273	6 oz. (180mL) Bottle, One-Touch Pump	4.2" (106.7 mm)
35274	6 oz. (180mL) Acetone Printed Bottle, One-Touch Pump	4.2" (106.7 mm)
35275	6 oz. (180mL) IPA Printed Bottle, One-Touch Pump	4.2" (106.7 mm)
35596	6 oz. (180mL) Flux Remover Printed Bottle, One-Touch Pump	4.2" (106.7 mm)

*NOTE: Heights include the bottle with the dispenser

Unless otherwise noted, tolerance $\pm 10\%$

Specifications and procedures subject to change without notice.



Made in the United States of America


durAstatic® Green Dissipative Bottles

3651 WALNUT AVE., CHINO, CA 91710
PHONE: (909) 627-2453
WEBSITE: MendaPump.com

DRAWING NUMBER
35273

DATE:
November
2017

MENDA



One-Touch Pump:

- “One-Touch” one-handed operation frees operator’s hands for use
- Precision machined valves for smooth consistent operation
- Recommended for one-handed dispensing of liquids, solvents, and chemicals
- Stainless-steel construction - No silicone or latex - suitable for ultra clean environments
- Cam-lock hinge keeps lid open and closed, reduces odors
- Compatible with any 38-400 threaded neck container
- Dispenses approximately 0.2cc of liquid with each pump

Pump Material	Stainless-Steel
Locks for Travel	No
Neck Size / Thread	38-400
Lid-Type	Cam-lock hinge lid
Gasket Material	LDPE

Pump Care:

Some types of fluids may leave a residue in the mechanism of the dispenser. Over time, this can reduce the performance of the pump.

Occasional cleaning is recommended to maintain your unit to original efficiency.

Clean by flushing the mechanism thoroughly with warm soapy water. Flush the mechanism again with clean water to remove any soap residue. Do not boil or steam the dispenser. For long periods of inactivity, pumps should be flushed free of liquid and stored inverted in a dry place.

Limited Warranty, Warranty Exclusions, Limit of Liability and RMA Request Instructions:

Before using, users shall determine the suitability of the product for their intended use, and users assume all risk and liability whatsoever in connection therewith. See the Menda Terms and Conditions - Mendapump.com/Terms-And-Conditions.aspx

Specifications and procedures subject to change without notice. Unless otherwise noted, tolerance is ±10%.

ONE-TOUCH, PUMP ONLY, NO STEM

3651 WALNUT AVE., CHINO, CA 91710
PHONE: (909) 627-2453
WEBSITE: MendaPump.com

DRAWING NUMBER
35300

DATE:
Aug.
2016

