



Einhell

EXPERT

GE-DP 5220 LL ECO

Dirt Water Pump
Art.-No.: 4170780
Ident-No.: 11013

The 2in1 combined pump GE-DP 5220 LL ECO is a robust and reliable aid for the quick drainage of ponds, building pits or flooded cellars, and can be used for clear or waste water with up to 2 cm particle size. With its power consumption of just 520 Watt, this powerful submersible pump delivers up to 13,500 litres of water per hour and thereby convinces by its optimum energy efficiency. Quick adjustment of the required pump settings can be reached by means of its patented function- and suction level control. The extremely robust pump housing with high-quality mechanical seal resists even heavy drainage works reliably, and grants a long service life.

Features

- 2in1 combined pump - clear and dirty water with one pump
- Clear water: low level submersible up to 1mm residual water level
- Dirty water: up to 20 mm of particle size in coarse water
- Starting of pump from water level of 10 mm already possible
- Patented suction level control by easy rotational motion
- Infinitely height-adjustable float switch
- High-quality mechanical seal for a long service life
- Ergonomic carrying handle with integrated lifting eye
- Easily reachable hose connection on the pump's topside
- Hose connection approx. 47.8 mm (G 1 1/2) AG
- Universal adapter for 25/32 mm hoses as well as 33.3 mm (G 1)
- Automatic mode for requested water level (float switch)
- Housing made of impact-resistant plastic
- ECO-Power: higher delivery rate, lower power consumption

Technical Data

• Mains supply	230 V 50 Hz
• Power	520 W
• Max. delivery capacity	13500 L/h
• Max. delivery height	7.5 m
• Max. immersion depth	8 m
• Max. water temperature	35 °C
• Max. size of foreign particles	20 mm
• Hose connection	47,8mm (G1 1/2 AG)
• Power cord	11 m H05RN-F



Logistic Data

• Product weight	5.8 kg
• Gross weight single packaging	6.2 kg
• Dimensions single packaging	240 x 240 x 380 mm
• Pieces per export carton	3 Pieces
• Gross weight export carton	22.4 kg
• Dimensions export carton	750 x 270 x 420 mm
• Container quantity (20"/40"/40"HC)	885 1845 2214



Illustrations can contain accessories, which are not included in standard extent of delivery
Illustration similar (in design), production-wise modifications reserved
GS mark belongs to the product itself only, excluded accessory