



# Einhell

# EXPERT

Multifunctional Tool

**TE-MG 300 EQ**

**Item No.: 4465150**

Ident No.: 11016

Bar Code: 4006825614237

The multifunctional tool TE-MG 300 EQ features a powerful 300 W motor, speed electronics for adjusting the tool to the material/application, constant electronics for consistent power and a soft grip for comfortable handling. A quick release helps to change equipment without tools on a tool chuck with 12 settings and a magnetic tool fixation. Also included is a dust extraction device for fitting without any additional tools, plus an adapter and several blades: plunge-cut saw blade (wood, plastic), BIM plunge-cut saw blade (metal), segment saw blade (wood, plastic, soft metal), diamond segment saw blade (tile joints), scraper, triangular grinding/sanding plate and 6 sheets of abrasive paper. Delivery in convenient transport and storage case.

## Features & Benefits

- Quick release for toolless change of equipment
- Comfortable accessory change thanks to magnetic tool fixation
- Powerful 300 Watt motor
- Speed electronics for material and application suitable working
- Thanks to constant electronics no loss of idle speed under load
- Safe and pleasant working thanks to soft grip
- Tool chuck (adjustable to 12 settings)
- Incl. toolless mountable dust extraction device
- Incl. triangular grinding/sanding plate
- Incl. 6x grinding/sanding paper (3\*P60/3\*P120)
- Incl. scraper
- Incl. plunge-cut saw blade for wood and plastic (HCS)
- Incl. BIM plunge-cut saw blade also for metal
- Incl. segment saw blade for wood, plastic and soft metal (HSS)
- Incl. diamond segment saw blade for tile joints
- Incl. convenient dust extraction adapter
- Delivery in convenient transport and storage case



## Technical Data

- |                        |                               |
|------------------------|-------------------------------|
| - Mains supply         | 230-240 V   50 Hz             |
| - Power                | 300 W                         |
| - Oscillating speed    | 22000-40000 min <sup>-1</sup> |
| - Angle of oscillation | 3.2 °                         |
| - Sandpaper size       | 93 x 93 x 93 mm               |

## Logistic Data

- |                                      |                    |
|--------------------------------------|--------------------|
| - Product weight                     | 1.54 kg            |
| - Gross weight single packaging      | 3.2 kg             |
| - Dimensions single packaging        | 348 x 109 x 270 mm |
| - Pieces per export carton           | 5 Pieces           |
| - Gross weight export carton         | 17 kg              |
| - Dimensions export carton           | 585 x 370 x 290 mm |
| - Container quantity (20"/40"/40"HC) | 2150   4450   5225 |



## Available as special accessories



Fliesen-Set  
Multifunctional Tool Accessory  
Item No.: 4465017  
Bar Code: 4006825625523  
Einhell Accessory



Boden- und Einbau-Set  
Multifunctional Tool Accessory  
Item No.: 4465016  
Bar Code: 4006825625516  
Einhell Accessory